







Notes:

- Electrical Specifications:
 - Meets EIA/TIA-568-B.2 Cat.5e Specification
 - Contact Resistance: 20mOhm max.
 - Insulation Resistance: 500MOhm min. @ 100 VDC
 - Current Rating: 1.2A max. at 25° C
 - Working Voltage: 100 VDC
 - DWV: 1000 VDC/60s Contact to Contact, 1500 VDC/60s Contact to Metal Shell
 - Operating Temperature: -40° C to +85° C
- Material and Finish:
 - Receptacle Housing, Metal Cover, Panel Nut: Brass, Nickel Plated
 - Ball Chain: Copper Alloy, Nickel Plated
 - Panel Gasket: Silicone, Color: White
 - Cover Gasket: Silicone, Color: Red
 - RJ45 PCB Jack Metal Shell: Copper Alloy, Nickel Plated
 - RJ45 PCB Jack Plastic Housing: Glass filled PBT UL94 V-0, Color: Black
 - RJ45 PCB Jack Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
- Connector can be front or rear mounted to a maximum panel thickness of 3.2mm.
- RoHS compliant

Directive 2002/95/EC
"RoHS"
Compliant

Description	Part Number
Metal Version Receptacle + Cover with Shielded RJ45 PCB Jack	17-101654
Potted Metal Version Receptacle + Cover with Shielded RJ45 PCB Jack	17-101674

THIS DRAWING MAY NOT BE COPIED, OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°		Scale: 1:2:1	Dim. in mm
	Name	Title	Approval Date				
	2009			Date	Name	Title: Receptacle + Cover Assembly Kit with Cat. 5e RJ45 PCB Jack Metal Version	
	Draw.			Jun. 05	Vincent Ke		
	Appd.			Jun. 05	J. Chaudry		
	Norm						
	D-old						
b			Aug/26/09	Vincent ke	Drawing No.: 17K1A252	DIN A3	
a			original		Part No.: SEE P/N TABLE	Sheet 1/1	
Rev. Changes		Date	Name				



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-101654](#) [17-101674](#)