



LOC	DIST	P	F	REVISIONS		DATE	APPD
				ZONE	LTR		
G	14				D	REVISED PER 0720-0230-93	2/25/94



AMP WIRE RANGE	UL E13288 Listed
22-16 AWG STRANDED	22-16 AWG STRANDED
CS LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928; COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	VOLTAGE RATING: NOT APPLICABLE	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm ² [509-3,260] CIR MILS STRANDED	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
--	---------------------------------------	---	--

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727
---	--	--

DR 2-25-93 TA BRINKMAN	CHK 2-25-93 DA PATTERSON	APPD 2-25-93 DE MILLER	APPD 2-25-93 JL MECKLEY	PRODUCT SPEC -	APPLICATION SPEC -	WEIGHT -
---------------------------	-----------------------------	---------------------------	----------------------------	-------------------	-----------------------	-------------

AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME TERMINAL, HOOK TONGUE, BUDGET		
SIZE C	CAGE CODE 00779	DRAWING NO C-31628
SCALE 10:1	SHEET 1 OF 1	