

MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929






SWITCH-ENCLOSED

CATALOG LISTING
41EN49-6

41EN49-6
M
DRAWING NUMBER
RELEASE NO. PR-19955
REPLACES

REVISIONS
A PR 1985
TSM 25MAR92
B CO 73787-C
II DAW MAY 94

25 MAR 92 CHECK
TSM 25 MAR 92 CHECK
DRAWN TSM
25 MAR 92 CHECK



NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- 3 - CIRCUIT DIAGRAM AND CAT. LIST. ARE SHOWN ON NAMEPLATE
- 4 - UNIT PROVIDES NO SHAFT RESTORING FORCE THE ACTUATING DEVICE MUST CONTROL MOVEMENT OF THE SHAFT
- 5 - DO NOT APPLY MORE THAN 20-25 INCH-POUNDS OF TORQUE WHEN TIGHTENING LOCKING NUT
- 6 - LEADS PARALLEL WITH CENTERLINE OF MOUNTING PINS WITHIN ±5°
- 7 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION

CHARACTERISTICS	ELECTRICAL DATA		SCALE FULL
OPERATING TORQUE — 3 IN LB MAX	CONTACT ARRANGEMENT 2X SPDT		DO NOT SCALE PRINT UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
PRETRAVEL	LOAD		ONE PLACE (.01) ±.030
DIFFERENTIAL TRAVEL	SEA LEVEL	50,000 FT	TWO PLACE (.00) ±.015
OVERTRAVEL			THREE PLACE (.000) ±.005
FREE POSITION			ANGLES ±
SEE DETAIL		WEIGHT 8.6 OZ MAX	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[41EN49-6](#)