


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T5	REVISED PER ECR-17-009545	08AUG2017	AS	RS



- 1

SILVER PLATE PER QQ-S-365
5.08 μm [.000200] MINIMUM THICK.
- 2

TIN-LEAD PLATE PER ASTM-B-545
2.54 μm [.000100] MINIMUM THICK,
WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT.
- 3

GOLD PLATE PER MIL-G-45204
0.76 μm [.000030] MINIMUM THICK.
- 4

MATTE TIN PLATE PER ASTM-B-545
2.54 μm [.000100] MINIMUM THICK,
WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT.
- 5

BRIGHT TIN PLATE PER ASTM-B-545
2.54 μm [.000100] MINIMUM THICK,
WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT.
- 6

328666 REPLACED BY 9-328666-3

	3.05	[.120]	4.55	[.179]	5	9-328666-4
	3.05	[.120]	3.86	[.152]	1	9-328666-3
	3.73	[.147]	4.55	[.179]	4	9-328666-2
	3.05	[.120]	3.86	[.152]	4	9-328666-1
	3.05	[.120]	4.55	[.179]	4	9-328666-0
	3.40	[.134]	4.55	[.179]	2	3-328666-9
	5.03	[.198]	5.51	[.217]	2	3-328666-6
OBSOLETE	3.73	[.147]	4.55	[.179]	2	3-328666-3
	3.05	[.120]	3.86	[.152]	2	2-328666-7
	3.05	[.120]	4.55	[.179]	3	2-328666-6
OBSOLETE	3.05	[.120]	4.55	[.179]	2	2-328666-5
	3.05	[.120]	4.55	[.179]	1	2-328666-3
6 OBSOLETE	3.05	[.120]	3.86	[.152]	1	328666
	B		A		FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL
COPPER ALLOY

FINISH
SEE TABLE

DWN
J. LIPPERT
CHK
R.E.RUTH
APVD
M. SNEED
PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT
0.000000

28MAR01
7/27/90
7/27/90

STE

TE Connectivity

FERRULE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-328666

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 OF 1

REV
T5