




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REVISED PER ECO-16-010704	20JUL2016	SY	SY

- 1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC, COLOR NATURAL OR LIGHT NATURAL.
PIN CONTACTS: PHOSPHOR BRONZE.
GROUND BUSSES: PHOSPHOR BRONZE.
- 2 PIN CONTACTS: 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00063-0.00191[.000025-.000075] TIN-LEAD ON SOLDER TAIL,
ALL OVER 0.00127-0.00254[.000050-.000100] NICKEL ON ENTIRE CONTACT.
- 3 GROUND BUSSES: 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00063-0.00191[.000025-.000075] TIN-LEAD ON SOLDER TAIL,
ALL OVER 0.00127-0.00254[.000050-.000100] NICKEL ON ENTIRE BUS.
- 4 AMP AND DATE CODE MARKED IN AREA INDICATED, ON SAME SIDE AS POSITION NUMBER 2 INDICATOR.
- 5 OBSOLETE
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

125.73[4.950]	99	128.22[5.048]	130.81[5.150]	132.44[5.214]	200	149013-9
113.03[4.450]	89	115.52[4.548]	118.11[4.650]	119.74[4.714]	180	149013-8
100.33[3.950]	79	102.82[4.048]	105.41[4.150]	107.04[4.214]	160	149013-7
87.63[3.450]	69	90.12[3.548]	92.71[3.650]	94.34[3.714]	140	149013-6
74.93[2.950]	59	77.42[3.048]	80.01[3.150]	81.64[3.214]	120	149013-5
62.23[2.450]	49	64.72[2.548]	67.31[2.650]	68.94[2.714]	100	149013-4
49.53[1.950]	39	52.02[2.048]	54.61[2.150]	56.24[2.214]	80	149013-3
36.83[1.450]	29	39.32[1.548]	41.91[1.650]	43.54[1.714]	60	149013-2
24.13[.950]	19	26.62[1.048]	29.21[1.150]	30.84[1.214]	40	149013-1
E	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.GERACE 1-23-95	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK P.MATAR 1-23-95				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.MONK 1-23-95	NAME			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1272	PLUG ASSEMBLY, 18.75 STACK, 3.68 ACTION PIN TAIL, BTB, MICROSTRIP			
MATERIAL		APPLICATION SPEC 114-11005	SIZE A1	CAGE CODE	DRAWING NO 149013	RESTRICTED TO -
FINISH		WEIGHT 0.000000	SCALE 10:1	SHEET 1 OF 1	REV D	
CUSTOMER DRAWING						