

Schottky Barrier Rectifier



Features:

- For Surface Mounted Applications
- Low Profile Package
- Built-In Strain Relief
- Metal Silicon Junction, Majority Carrier Conduction
- High Surge Capability
- Low Power Loss, High Efficiency
- For Use in Low Voltage High Frequency Inverters, Free Wheeling and Polarity Protection Applications
- Guardring for Over Voltage Protection
- High Temperature Soldering Guaranteed: 250°C/10 Seconds at Terminals

Mechanical Data

- Case: JEDEC DO-214AC, Molded Plastic over Passivated Chip
- Terminals: Solder Plated, Solderable per MIL-STD-750, Method 2026
- Polarity: Colour Band Denotes Cathode End
- Weight: 0.002oz, 0.064g

Maximum Ratings and Thermal Characteristics

Ratings at 25°C ambient temperature unless otherwise specified

Characteristic		B340A-13-F	B360A-13-F	Units
Maximum repetitive peak reverse voltage	V _{RRM}	40	60	V
Maximum RMS voltage	V _{RWS}	28	42	V
Maximum DC blocking voltage	V _{DC}	40	60	V
Maximum average forward rectified current at T _L See Fig. 1. (Note 2)	I _{F(AV)}	3		A
Peak forward surge current 8.3ms single half-sine-wave	I _{FSM}	100		A
Maximum instantaneous forward voltage at 3A (Note 1)	V _F	0.5	0.7	V
Maximum DC reverse current T _A =25°C at rated DC blocking voltage T _A =100°C (Note 1)	I _R	0.5 20		mA
Typical thermal resistance (Note 2)	R _{θJA} R _{θJL}	50 10		°C/W
Operating junction and storage temperature range	T _J , T _{STG}	-65 to +125		°C

Notes:

(1) Pulse test: 300 μs pulse width, 1% duty cycle.

(2) PCB mounted with 0.55" $\times$ 0.55" (14 $\times$ 14mm²) copper pad areas.

Schottky Barrier Rectifier

FIG.1 – FORWARD DERATING CURVE




FIG.2– PEAK FORWARD SURGE CURRENT




FIG.3 – TYPICAL FORWARD CHARACTERISTICS





FIG.4 – TYPICAL REVERSE CHARACTERISTICS



Schottky Barrier Rectifier

FIG.5-TYPICAL JUNCTION CAPACITANCE






FIG.6- TYPICAL TRANSIENT THERMAL IMPEDANCE




Package Outline Dimensions



DO-214AC(SMA)		
Dim.	Min.	Max.
A	4.25	4.65
B	2.4	2.8
C	1.85	2.15
D	4.85	5.35
E	0.1	0.3
F	0.9	1.5
G	0.2 Max.	
H	1.9	2.3
I	1.35	1.65

Dimensions : Millimetres

Soldering Footprint



Dimensions : Millimetres

Package Information

Device	Package	Shipping
B340A-13-F & B360A-13-F	DO-214AC(SMA)	5,000 / Tape & Reel

Part Number Table

Description	Part Number
Schottky Barrier Rectifier	B340A-13-F
	B360A-13-F

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.