

MICRO SWITCH Miniature Precision Limit Switches

14CE Series

002387

Issue 5

Datasheet



DESCRIPTION

All MICRO SWITCH™ 14CE Series miniature precision switches incorporate fluorocarbon diaphragm sealing to provide reliable protection, meeting IP65, IP66, IP67, and IP68, as well as NEMA 1, 2, 3, 3R, 4, 6, 6P, and 13 requirements. Versions with a boot seal also meet NEMA 12 requirements (dust, falling dirt, liquid media with solid contaminants). The cable or connector and basic switch terminals are encapsulated in an epoxy sealant, offering excellent resistance in harsh environments. For low temperature applications (down to -40 °C, -40 °F), CE Series switches can be supplied with low temperature seals and lubricant.

The CE Series switches are rugged and versatile switches which can be applied indoors in many harsh factory floor applications, as well as on outdoor equipment in extreme temperatures. A full range of actuators are available, including pin plungers, roller plungers, side rotary, multi-directional wire, and manually operated. The switches are also available with the industry standard, M12 micro-change 4-pin connector. MICRO SWITCH 14CE products meet European and Asian CE requirements.

VALUE TO CUSTOMERS

- Big performance in a small package
- Delivers consistent performance in many demanding environments where petroleum, synthetic, or water based fluids are present
- Product variation within defined nomenclature

FEATURES

- Rugged, miniature construction means minimal real estate on equipment
- NEMA 1, 2, 3, 3R, 4, 6, 6P, 12 (boot seal), 13, and IP65/66/67/68 environmental sealing
- Pre-leaded (Cenelec cable) or supplied with a M12 four-pin connector
- Wide selection of actuators and cable length variations with side and bottom exit cable/connector options
- 25 mm mounting centers engineered with a MICRO SWITCH SM switch for consistent, precise actuation
- Well suited for up to 10 million actuation cycles (Up to 5 million actuation cycles for wobble actuators)
- Gang mounting capability to provide a multi-plunger limit switch
- Low temperature variants available for indoor and outdoor applications
- CE approvals for European and Asian use

POTENTIAL APPLICATIONS

- Machine tools
- Off-road equipment
- Material handling
- Access and mobility solutions
- Textile machinery
- Robotics
- Packaging equipment
- Commercial appliances
- Print trade machinery
- Agricultural machinery

DIFFERENTIATION

- Diaphragm seal between the actuator and the switch cavity for high performance sealing
- CE Series incorporates MICRO SWITCH SM basic switch for consistent, precise actuation
- Side exit termination for space constraints

PORTFOLIO

Honeywell's MICRO SWITCH 14CE limit switch is part of a comprehensive offering of rugged and reliable limit switches. To view the entire product portfolio, click [here](#).

MICRO SWITCH Miniature Precision Limit Switches, 14CE Series

Table 1. Specifications

Characteristic	Parameter
Description	compact enclosed limit switch
Actuators	• Top pin plunger (14CE1-) • Cross roller plunger (14CE3-) • Top pin plunger with boot seal (14CE18-) • Wobble (14CE20-) • Top pin plunger, panel mount (14CE27-) • Top roller plunger, parallel and panel mount (14CE28-) • Top roller plunger, perpendicular, panel mount (14CE29-) • Top roller plunger, parallel and boot sealed (14CE31-) • Top roller plunger, perpendicular, boot seal (14CE55-) • Parallel roller plunger (14CE2-) • Side rotary (14CE16-) • Top adjustable plunger (14CE19-) • Manually operated (14CE22-) • Ball bearing plunger (14CE66-)
Terminations	Harmonized Cenelec PVC sheathed 4 x 0,75 mm ² (18 AWG) cable Connector (dc), 4-pin male, M12 thread (-Q) Connector (ac), 4-pin male, 1/2 in x 20 thread (-Q1)
Switching options	SPDT, snap action contacts (1NC/1NO) Form C
Sealing	IP65, IP66, IP67, IP68* NEMA 1, 2, 3, 3R, 4, 6, 6P, 12 (boot seal), 13
Operating temperature	0 °C to 70 °C [32 °F to 158 °F]; optional -40 °C to 70 °C [-40 °F to 158 °F]
Mechanical life	up to 10 million; up to 5 million (wobble actuators) cycles
Thermal current	1 A, 3 A, 5 A (depending upon model)
Rated insulation voltage (Ui)	250 V
Rated impulse withstand voltage (Uimp)	1.5 kV
Short circuit protection device (SCPD)	Quick blow fuse suitable for rated current of switch
Pollution degree	3
Min. actuation speed	0.003 m/s
Max. actuation speed	0.1 m/s
Max. actuation frequency	ac – 200 Hz; dc – 20 Hz
Shock	50 g – IEC 60068-2-27
Vibration	10 g – IEC 60068-2-6
Approvals	CE
Conforming to standards	EN 60947-5-1; AC-14 D300, DC-13 R300

*IP68 sealing submerged in one meter of water for 24 hours


Table 2. Electrical Ratings (in amperes)

Model example	Contacts	Rating
14CE_ _	Silver contacts	A
14CE_ _G	Gold contacts	B
14CE_ -Q, -AQ, -AQ1	Silver contacts	C with 4-pin connector


Rating code		Make	Break
A	240 Vac, ind.	1.2	0.2
	240 Vac, res.	5	5
	28 Vdc, res.	3	3
	28 Vdc, ind.	3	3
	5 A, 1/10 HP, 125 Vac or 250 Vac	–	–
B	5-25 mA 5-50 Vdc	–	–
C	3 A, 125 Vac or 250 Vac	–	–

MICRO SWITCH Miniature Precision Limit Switches, 14CE Series

SWITCHING AND LEAD IDENTIFICATION




PINOUTS



CONNECTOR VERSIONS

The 14CE Series is available with a 4-pin, M12 size connector in both bottom and side exit versions.



MOUNTING

MICRO SWITCH 14CE Series switches are mounted by using two M5 screws. The mounting holes are counter bored to keep the screw heads within the overall switch housing dimensions.

GANG MOUNT CAPABILITY

The housing on the 14CE Series has been designed to enable the user to build his own multiple plunger switch by gang mounting several switches. All pin plunger and roller plunger types are suitable for gang mounting. There is a 16 mm distance between the plungers. Both Series are very versatile that even a lever-type version could be added at the end of the row.

BOTTOM EXIT OR SIDE EXIT ORIENTATION


The CE Series has been designed with a pre-wired cable or connector fitted in the bottom of the switch housing. Other variations are available with a side-exit cable or connector.

GOLD CONTACT VERSIONS

For low energy applications, gold contact versions of the 14CE switches can be supplied upon request.

MICRO SWITCH Miniature Precision Limit Switches, 14CE Series

GENERAL DIMENSIONS • ALL SWITCHES



PRODUCT NOMENCLATURE

14CE

Switch Type

14CE Series Compact Precision Limit Switch

16

Actuator Type

1	Top pin plunger
2	Top roller plunger, parallel
3	Top roller plunger, perp.
16	Side rotary
18	Top pin plunger w/ boot seal
19	Top adjustable pin plunger
20	Coil wobble
22	Manually oper. nylon button
27	Top pin plunger, panel mount
28	Top roller plunger, parallel panel mount
29	Top roller plunger, perp. panel mount
31	Top roller plunger, parallel boot seal
55	Top roller plunger, perp. boot seal
66	Top ball bearing plunger

3

Cable Length*

1	1 meter
2	2 meters
3	3 meters
4	4 meters
5	5 meters

Options^{1,2}

A	Side entry
B	Elongated mounting holes
D	Halogen-free cable
G	Gold contacts
H	High temp., 150 °C
L	Low temp., -40 °C switch and cable
L1	Low temp., -40 °C, cable not for flexing
P	Top mounting
V	Viton® seals/gasket (side rotary and booted sealed plungers only)

Connectors* (micro type)

Q	dc type single keyway 4-pin male, M12
Q1	ac type two keyways 4-pin male, 1/2-20

OTE: not all combinations of model codes are available. Please contact your Honeywell provider/representative for assistance.

More than one option may be permissible.

Select "Cable Length" or "Connectors"

NOTE: not all combinations of model codes are available.
 Please contact your Honeywell provider/representative for assistance.

¹More than one option may be permissible.

* Select "Cable Length" or "Connectors"

²OPTION K to be discontinued. Replaced with fluorocarbon diaphragm seal, standard switch.

²OPTION KV to be discontinued. Replaced with fluorocarbon diaphragm seal, standard switch.

Bottom exit is standard.

MICRO SWITCH Miniature Precision Limit Switches, 14CE Series



PRODUCT SPECIFICATIONS AND LISTINGS

Contact your Honeywell rep or distributor for additional listings


14CE1 • Pin Plunger 14CE27 • Pin Plunger Panel Mount		Con- tacts	Elec Rating	Cable/ Connector Position	Free Posi- tion (FP)	Operating Position (OP)	Options	Listing
	17,5 15,7 12,7 GRY-BRN GRY-BLK GRY-BLK GRY-BRN 15,8 Pretravel • 1,8 mm [0.071 in] Diff. travel • 0,1 mm [0.004 in] Overtravel • 3,0 mm [0.118 in] Oper. force • 11,8 N [2.65 lb]	Silver	A	Bottom	17,5 mm [0.69 in]	15,7 mm [0.62 in]	–	14CE1-1
		Gold	B	Bottom	17,5 mm [0.69 in]	15,7 mm [0.62 in]	Gold-plated contacts	14CE1-1G
		Silver	A	Side	17,5 mm [0.69 in]	15,7 mm [0.62 in]	Side exit cable	14CE1-1A
		Silver	C	Bottom	17,5 mm [0.69 in]	15,7 mm [0.62 in]	dc-type connector	14CE1-Q
	31,1 29,3 26,3 GRY-BRN GRY-BLK GRY-BLK GRY-BRN 29,4	Silver	A	Bottom	31,1 mm [1.23 in]	29,3 mm [1.15 in]	Panel mount	14CE27-1
14CE18 • Boot Sealed Pin Plunger		Con- tacts	Elec Rating	Cable/ Connector Position	Free Posi- tion (FP)	Operating Position (OP)	Options	Listing
	26,7 24,9 21,9 GRY-BRN GRY-BLK GRY-BLK GRY-BRN 25 Pretravel • 1,8 mm [0.071 in] Diff. travel • 0,1 mm [0.004 in] Overtravel • 3,0 mm [0.118 in] Oper. force • 22,5 N [5.06 lb]	Silver	A	Bottom	26,7 mm [1.05 in]	24,9 mm [0.98 in]	–	14CE18-1
		Silver	A	Side	26,7 mm [1.05 in]	24,9 mm [0.98 in]	Side exit cable	14CE18-1A
		Silver	C	Bottom	26,7 mm [1.05 in]	24,9 mm [0.98 in]	dc-type connector	14CE18-Q
14CE66 • Ball Bearing Plunger		Con- tacts	Elec Rating	Cable/ Connector Position	Free Posi- tion (FP)	Operating Position (OP)	Options	Listing
	26,2 24,4 21,4 GRY-BRN GRY-BLK GRY-BLK GRY-BRN 24,5 Pretravel • 1,8 mm [0.071 in] Diff. travel • 0,1 mm [0.004 in] Overtravel • 3,0 mm [0.118 in] Oper. force • 11,8 N [2.65 lb]	Silver	A	Bottom	26,2 mm [1.03 in]	24,4 mm [0.96 in]	–	14CE66-1
		Silver	A	Side	26,2 mm [1.03 in]	24,4 mm [0.96 in]	Side exit cable	14CE66-1A

MICRO SWITCH Miniature Precision Limit Switches, 14CE Series

14CE2 • Roller Plunger 14CE28 • Roller Plunger Panel Mount





Pretravel • 1,8 mm [0.071 in]
Diff. travel • 0,1 mm [0.004 in]
Overtravel • 3,0 mm [0.118 in]
Oper. force • 11,8 N [2.65 lb]



Con-tacts	Elec Rating	Cable/ Connector Position	Free Position (FP)	Operating Position (OP)	Options	Listing
Silver	A	Bottom	30,3 mm [1.19 in]	28,5 mm [1.12 in]	–	14CE2-1
Gold	B	Bottom	30,3 mm [1.19 in]	28,5 mm [1.12 in]	Gold-plated contacts	14CE2-1G
Silver	C	Bottom	30,3 mm [1.19 in]	28,5 mm [1.12 in]	dc-type connector	14CE2-Q
Silver	A	Side	30,3 mm [1.19 in]	28,5 mm [1.12 in]	Side exit cable	14CE2-1A
Silver	A	Bottom	44,3 mm [1.75 in]	42,5 mm [1.67 in]	Panel mount, 2 m cable	14CE28-2



14CE31 • Boot Sealed Roller Plunger



Pretravel • 1,8 mm [0.071 in]
Diff. travel • 0,1 mm [0.004 in]
Overtravel • 3,0 mm [0.118 in]
Oper. force • 17,5 N [3.93 lb]

Con-tacts	Elec Rating	Cable/ Connector Position	Free Position (FP)	Operating Position (OP)	Options	Listing
Silver	A	Bottom	36,2 mm [1.43 in]	34,4 mm [1.36 in]	–	14CE31-1
Silver	A	Bottom	36,2 mm [1.43 in]	34,4 mm [1.36 in]	Fluorocarbon seals, 6 m cable	14CE31-6V




14CE3 • Cross Roller Plunger



Pretravel • 1,8 mm [0.071 in]
Diff. travel • 0,1 mm [0.004 in]
Overtravel • 3,0 mm [0.118 in]
Oper. force • 11,8 N [2.65 lb]

Con-tacts	Elec Rating	Cable/ Connector Position	Free Position (FP)	Operating Position (OP)	Options	Listing
Silver	A	Bottom	30,3 mm [1.19 in]	28,5 mm [1.12 in]	–	14CE3-1
Silver	A	Side	30,3 mm [1.19 in]	28,5 mm [1.12 in]	3 m of cable, side exit	14CE3-3A
Silver	C	Bottom	30,3 mm [1.19 in]	28,5 mm [1.12 in]	dc-type connector	14CE3-Q

MICRO SWITCH Miniature Precision Limit Switches, 14CE Series

14CE55 • Boot Sealed Cross Roller Plunger		Con-tacts	Elec Rating	Cable/ Connector Position	Free Posi-tion (FP)	Operating Position (OP)	Options	Listing
 ROLLER Ø 12,4 mm x 4,7 mm Ø 0.48 in x 0.020 in BOOT SEAL PT OT OP FP	36,2 34,4 31,4 GRY-BRN GRY-BLK GRY-BLK GRY-BRN 34,5 Pretravel • 1,8 mm [0.071 in] Diff. travel • 0,1 mm [0.004 in] Overtravel • 3,0 mm [0.118 in] Oper. force • 17,5 N [3.93 lb]	Silver	A	Bottom	36,2 mm [1.43 in]	34,4 mm [1.36 in]	3 meters of cable	14CE55-3
14CE16 • Side Rotary		Con-tacts	Elec Rating	Cable/ Connector Position	Free Posi-tion (FP)	Operating Position (OP)	Options	Listing
 PT FP PT OT OT OT Actuator shaft Ø7,22 mm [0.288 in] 18,9 mm [0.74 in]	0° 30° 70° GRY-BRN GRY-BLK GRY-BLK GRY-BRN 27° Pretravel • 30° Diff. travel • 3° Overtravel • 40° Oper. force • 0,34 Nm [3 in-lb]	Silver	A	Bottom	0°	30°	–	14CE16-1¹
		Gold	B	Bottom	0°	30°	Gold-plated contacts, 3 meters of cable	14CE16-3G¹
		Silver	C	Bottom	0°	30°	dc-type connector	14CE16-Q¹
14CE20 • Random Motion Wire Actuator		Con-tacts	Elec Rating	Cable/ Connector Position	Free Posi-tion (FP)	Operating Position (OP)	Options	Listing
 OP ALL DIRECTIONS EXCEPT DIRECT PULL Ø1,8 mm [0.07 in] 335,0 mm max. [13.98 mm max.]	0 28 max. GRY-BRN GRY-BLK GRY-BLK GRY-BRN Oper. position • 28 mm [1.10 in] max. Oper. force • 0,55 N [0.12 lb] max.	Silver	A	Bottom	–	28 mm [1.10 in] max.	–	14CE20-1

¹ Switch operates on clockwise and counterclockwise rotation of lever shaft

Note: Most part numbers are shown with 1 meter of cable. The -X indicates the number of meters of cable provided: 2-meters, 3-meters, 4-meters, and 5-meters. Custom lengths are also available.

MICRO SWITCH Miniature Precision Limit Switches, 14CE Series

Table 3. Levers for Use with 14CE Side Rotary Switches

	Catalog Listing	Roller Material	Roller Dia. mm [in]	Roller Width mm [in]
Fixed length lever; 38,1 mm [1.5 in] radius				
	GLZ51A	Nylon	19,0 [0.75]	6,35 [0.25]
	GLZ51B	Steel	19,0 [0.75]	6,35 [0.25]
	GLZ51C	Nylon	25,4 [1.00]	12,7 [0.50]
	GLZ51E	Bronze	19,0 [0.75]	6,35 [0.25]
	GLZ51T	SST	19,0 [0.75]	9,5 [0.38]
Fixed length offset lever; 38,1 mm [1.5 in] radius				
	GLZ55A	Nylon	19,0 [0.75]	6,35 [0.25]
	GLZ55B	Steel	19,0 [0.75]	6,35 [0.25]
	GLZ55E	Bronze	19,0 [0.75]	6,35 [0.25]
Adjustable 38,1 mm to 89,0 mm [1.5 in to 3.5 in] radius				
	GLZ52A	Nylon	19,0 [0.75]	6,35 [0.25]
	GLZ52B	Steel	19,0 [0.75]	6,35 [0.25]

ADDITIONAL MATERIALS

- Product installation instructions
- Product range guide
- Product nomenclature tree
- Product application-specific information
 - Limit and enclosed switches application information
 - Limit and enclosed switches operating characteristics
 - Limit and enclosed switches reference standards
 - Limit and enclosed switches typical applications
 - Product flyer: CE Family Miniature Limit Switches

WARNING **PERSONAL INJURY**

DO NOT USE these products as safety or emergency stop devices or in any other application where failure of the product could result in personal injury.

Failure to comply with these instructions could result in death or serious injury.

WARNING **MISUSE OF DOCUMENTATION**

- The information presented in this product sheet is for reference only. Do not use this document as a product installation guide.
- Complete installation, operation, and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

Warranty/Remedy

Honeywell warrants goods of its manufacture as being free of defective materials and faulty workmanship during the applicable warranty period. Honeywell's standard product warranty applies unless agreed to otherwise by Honeywell in writing; please refer to your order acknowledgment or consult your local sales office for specific warranty details. If warranted goods are returned to Honeywell during the period of coverage, Honeywell will repair or replace, at its option, without charge those items that Honeywell, in its sole discretion, finds defective. **The foregoing is buyer's sole remedy and is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose. In no event shall Honeywell be liable for consequential, special, or indirect damages.**

While Honeywell may provide application assistance personally, through our literature and the Honeywell web site, it is buyer's sole responsibility to determine the suitability of the product in the application.

Specifications may change without notice. The information we supply is believed to be accurate and reliable as of this writing. However, Honeywell assumes no responsibility for its use.

For more information

Honeywell Sensing and Internet of Things services its customers through a worldwide network of sales offices and distributors. For application assistance, current specifications, pricing or the nearest Authorized Distributor, visit sensing.honeywell.com or call:

Asia Pacific	+65 6355-2828
Europe	+44 1698 481481
USA/Canada	+1-800-537-6945

Honeywell Sensing and Internet of Things

9680 Old Bailes Road
Fort Mill, SC 29707
www.honeywell.com

Viton® is a registered trademark of DuPont Performance Elastomers L.L.C.

002387-5-EN | 5 | 05/19
© 2019 Honeywell International Inc. All rights reserved.

Honeywell

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[14CE1-3AK](#) [14CE1-3AKV](#) [14CE1-3K](#) [14CE1-6KV](#) [14CE2-1K](#) [14CE2-2K](#) [14CE2-2KV](#) [14CE2-3K](#) [14CE2-3KV](#)
[14CE2-6KV](#) [14CE3-1K](#) [14CE3-3K](#) [14CE3-3KV](#) [14CE101-1](#) [14CE101-10](#) [14CE101-2](#) [14CE101-3](#) [14CE101-4](#)
[14CE101-6](#) [14CE102-1](#) [14CE102-12](#) [14CE102-15](#) [14CE102-3](#) [14CE102-3G](#) [14CE102-5](#) [14CE102-6](#) [14CE102-6G](#)
[14CE102-8](#) [14CE103-1](#) [14CE103-3](#) [14CE118-1](#) [14CE118-10](#) [14CE118-6](#) [14CE16-1](#) [14CE1-1](#) [14CE1-1K](#)
[14CE16-3](#) [14CE1-4L1X](#) [14CE316V](#) [14CE9-3JK](#) [14CE1-1A](#) [14CE18-N66](#) [14CE16-3G](#) [14CE2-4GL](#) [14CE1-5K](#)
[14CE1-1AN60](#) [14CE8-5J](#) [14CE16-3N30](#) [14CE1-5KV](#) [14CE3-1J](#) [14CE16-1H](#) [14CE31-10A](#) [14CE16-Q](#) [14CE20-8](#)
[14CE18-N15](#) [14CE66-4G](#) [14CE8-1J](#) [14CE8-5JKE5](#) [14CE1-1G](#) [14CE2-N46](#) [14CE3-10](#) [14CE2-3J](#) [14CE31-N42](#)
[14CE18-6AH](#) [14CE2-5KV](#) [14CE2-3AH](#) [14CE31-2H](#) [14CE16-10](#) [14CE18-Q](#) [14CE1-2B](#) [14CE18-1AN63](#) [14CE16-4](#)
[14CE16-3N28](#) [14CE2-2B](#) [14CE1-1GL1](#) [14CE16-2](#) [14CE1-3AL](#) [14CE31-1](#)