

Safety solutions using Preventa

VARIO enclosed switch disconnectors

(pre-assembled)

Enclosed switch disconnectors for high performance applications

- Marking on operator $\circ \downarrow$.
- 3-pole rotary switch disconnectors from 10 to 140 A
- Padlockable operating handle (padlock not included).
- IP 65 degree of protection enclosures, sealable and lockable.
- Cover lockable in position "I" (ON) up to 63 A rating.

3-pole main and Emergency stop switch disconnectors (1)

Operator Handle	Front plate Dimensions	Ithe A	Power AC-23 at 400 V kW	Incorporated switch body	Possible attachments (2)	Reference	Weight kg
Red, padlockable with up to 3 padlocks (Ø 4 to Ø 8 shank)	Yellow 60 x 60	10	4	V02	2	VCF 02GE	0.500
		16	5.5	V01	2	VCF 01GE	0.500
		20	7.5	V0	2	VCF 0GE	0.500
		25	11	V1	2	VCF 1GE	0.500
		32	15	V2	2	VCF 2GE	0.500
		50	22	V3	3	VCF 3GE	0.930
Red, long padlockable with up to 3 padlocks (Ø 4 to Ø 8 shanks)	Yellow 90 x 90	63	30	V4	3	VCF 4GE	0.930
		100	37	V5	1	VCF 5GE	2.190
		140	45	V6	1	VCF 6GE	2.190

Enclosed switch disconnectors for standard applications

- 3-pole rotary switch disconnectors from 10 to 32 A
- Degree of protection IP 55.

3-pole main and Emergency stop switch disconnectors (1)

Operator Handle	Front plate Dimensions	Ithe A	Power AC-23 at 400 V kW	Incorporated switch body	Possible attachments (2)	Reference	Weight kg
Red, padlockable with 1 padlock (Ø 8 shank) or up to 3 padlocks (Ø 6 shank)	Yellow 60 x 60	10	4	VN 12	2	VCFN 12GE (2)	0.422
		16	5.5	VN 20	2	VCFN 20GE (2)	0.422
		20	7.5	V0	0	VCFN 25GE	0.512
		25	11	V1	0	VCFN 32GE	0.512
		32	15	V2	0	VCFN 40GE	0.512

(1) Switch disconnector characteristics, see pages 23011/2 to 23011/5.

(2) For enclosures VCF and VCFN, see page 23054/2.



VCF 0GE



VCF 3GE



VCFN 12GE

Safety solutions using Preventa

VARIO enclosed switch disconnectors

(assembled by the user)

590574



VCFX GE2

Empty enclosures

IP 65 enclosure with red padlockable handle operator and yellow front plate
(for mounting a main or Emergency stop switch disconnector)

For switch body type	Ithe	Possible attachments (1)	Reference	Weight
A				kg
VN 12, VN 20 V02...V2	10...32	2	VCFX GE1	0.340
V02...V2	10...32	4	VCFX GE4	0.660
V3 and V4	50...63	3	VCFX GE2	0.660
		4	VCFX GDXE	0.660

Switch bodies for standard applications (2)

Description	Rating	Reference	Weight
A			kg
3-pole switch disconnectors	10	VN 12	0.110
	16	VN 20	0.110

Switch bodies for high performance applications (2)

Description	Rating	Reference	Weight
A			kg
3-pole switch disconnectors	10	V02	0.200
	16	V01	0.200
	20	V0	0.200
	25	V1	0.200
	32	V2	0.200
	50	V3	0.200
	63	V4	0.200

590575



V0

(1) See page 23054/2.

(2) Switch disconnector characteristics, see pages 23011/2 to 23011/5.