






LOC	DIST	REVISIONS				
FT	64	REV	LTR	DESCRIPTION	DATE	DWN APVD
		L1	REVISED	PER ECO-11-005027	11MAR11	RK HMR



SECTION A-A
ROTATED 90° CW
SCALE 10:1
FOR -6,-7 & -8 ONLY



1. RECEPTACLE ACCEPTS AN .008—.014 THK. I.C. LEAD.
2. TWO .000030 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
3. TWO .000015 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. TUBE LOADED.



SECTION A-A
ROTATED 90° CW
SCALE 10:1
FOR -1,-2 & -3 ONLY

OBSOLETE	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-643644-3
	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643644-8
OBSOLETE	TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643644-7
SUPSD BY 643644-2	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643644-6
	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643644-4
OBSOLETE	TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643644-3
	TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643644-2
	TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643644-1
	CONTACT FINISH	CONTACT MAT'L	HOUSING MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. CYRUS 7-3-84	 TE Connectivity	
		CHK N. JONES 7-3-84		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± .005 1. PLC ± .005 2. PLC ± .005 3. PLC ± .005 4. PLC ± .005 ANGLES ± .005	APVD J. GRAY 7-10-84	NAME	
		PRODUCT SPEC 108-1066	SOCKET ASSY, SIP, 12 POS, DIPLOMATE DL —	
MATERIAL SEE TABLE	FINISH SEE TABLE	APPLICATION SPEC 114-1049	SIZE CAGE CODE DRAWING NO	
		WEIGHT —	A1 00779 643644	
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 of 1	REV L1