

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By -





ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
—	—		F	END STAND OFF WIDTH INCREASED	07JAN2016	KJK PS


NOTES:

1. TO DETERMINE DIMENSIONS TAKE $2 \times N = \text{NR. OF POS.}$
FOR EXAMPLE: $2 \times 10 \text{ POS.} : N \times 2,54 = 25,4 \text{ mm.}$
FOR ORDER NR. USE BASIC NR. + NR. OF POS.
FOR EXAMPLE: $2 \times 2 \text{ POS.} = 215 \ 310 - 2 \text{ (SHORTEST VERSION)}$
 $2 \times 36 \text{ POS.} = 3 - 215 \ 310 - 6 \text{ (LONGEST VERSION)}$
2. HOUSING MATERIAL: GREEN GLASS FILLED PBT,
UL 94V-0
CONTACT MATERIAL: PHOSPHOR BRONZE.
3. PLATING: $2.5 - 4.0 \mu\text{m}$ TIN OVER $0.5 \mu\text{m}$ NICKEL
4. MATES WITH 0,63 SQUARE/ROUND MODU POSTS.
5. CONTACT-POINT.
6. RECOMMENDED P.C.BOARD-THICKNESS: 1.6 mm
7. PC-BOARD RETENTION FEATURE.
8. HV100 CONNECTOR PACKED IN ANTIS-TATIC BLISTER TRAY.
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

POS. PER ROW 'N'	L	PART NUMBER	
1	5.08	215310	-2
2	7.62	-3	OBSOLETE
3	10.16	-4	
4	12.70	-5	
5	15.24	-6	OBSOLETE
6	17.78	-7	
7	20.32	-8	OBSOLETE
8	22.86	-9	OBSOLETE
9	25.40	1-	-0
10	27.94	1-	-1
11	30.48	1-	-2
12	33.02	1-	-3
13	35.56	1-	-4
14	38.10	1-	-5
15	40.64	1-	-6
16	43.18	1-	-7
17	45.72	1-	-8
18	48.26	1-	-9
19	50.80	2-	-0
20	53.34	2-	-1
21	55.88	2-	-2
22	58.42	2-	-3
23	60.96	2-	-4
24	63.50	2-	-5
25	66.04	2-	-6
26	68.58	2-	-7
27	71.12	2-	-8
28	73.66	2-	-9
29	76.20	3-	-0
30	78.74	3-	-1
31	81.28	3-	-2
32	83.82	3-	-3
33	86.36	3-	-4
34	88.90	3-	-5
35	91.44	3-	-6



P.C.-BOARD HOLE-PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.V.D.HEYDEN	09.07.86	 TE Connectivity			
DIMENSIONS: mm		CHK W.SIMONS	—	NAME HV100 CONN. VERTICAL, 8.5mm TOP ENTRY, DUAL ROW, TIN			
		APVD L.V.SOEST	—				
		PRODUCT SPEC 108—19056					
		APPLICATION SPEC —					
MATERIAL SEE NOTE 2		FINISH SEE NOTE 3		SIZE A3	CAGE CODE 00779	DRAWING NO C-215310	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV F	