



D



C

B

A




RECOMMENDED BOARD LAYOUT



SECTION C-C

- CONTACTS: 0.00076[.000030] MINIMUM GOLD IN CONTACT AREA, 0.00381[.000150] MIN TIN ON SOLDER TAILS, ALL OVER 0.00127[.000050] MINIMUM NICKEL
- CUSTOMER TO PROVIDE CARD GUIDANCE SYSTEM
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- CONNECTOR REQUIRES USE OF 2 - SIZE 2M SCREWS FOR FASTENING TO PRINTED CIRCUIT BOARD



DETAIL A
SCALE 10:1

1, 13, 38, 50	ALL OTHER PINS	25, 26	5120615-1
5.0 [0.197]	4.25 [0.167]	3.5 [0.138]	PART NUMBER
"L" (PIN LENGTH) AND LOCATION			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 12JULY05		TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J. GERACE 12JULY05		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 12JULY05		PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		SIZE	
1 PLC ± -		WEIGHT		CAGE CODE	
2 PLC ± 0.13 [0.005]		CUSTOMER DRAWING		DRAWING NO	
3 PLC ± -		SCALE 4:1		SHEET 1 of 1	
4 PLC ± -		REV P			
ANGLES ± -					
FINISH					
MATERIAL HOUSING: LCP					
CONTACTS: BRASS					