



PANDUIT PART NUMBER	MAXIMUM CABLE DIAMETER	PANEL DIMENSIONS		WEIGHT LBS./100 PCS (g)
		THICKNESS	HOLE SIZE	
SICH25	.25 (6.4)	.03/.10 (0.8/2.5)	.250 (6.4)	.11 (50)

1. SEE CURRENT PRICE SHEET FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE
AND PART COLOR.

										(DIMENSIONS IN PARENTHESIS ARE METRIC)		
										CAD FILENAME/LAYERS		
										GB0239JK_PB_SICH25_00		
										PANDUITCORP. TINLEY PARK, ILLINOIS		
										SNAP-IN CLIP		
										SICH25		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± N/A (.XXX) ± .010 (.25) (.XX) ± .02 (.5) ANGLES ± N/A		
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY LGG		
										DATE 9-4-02		
										MAT'L: NYLON 6/6		
										SCALE 2/1		
R	9-4-02	LGG		INITIAL RELEASE.			GB0239JK	R			DRAWING NO. GB0239JK	
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP	DWG A
												SIZE