






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE:  $X.X = \pm 0.4$   
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 4A @125VAC/28VDC, 2A @250VAC
5. DIELECTRIC STRENGTH: 1KV RMS min. at sea level
6. ELECTRICAL LIFE: 10,000 make-and-break cycles  
at full load.
7. MATERIALS:



CONTACTS: Silver Plated Cu (Q Contact material)  
TERMINALS: GOLD Plated Cu (Q Contact material)  
MOUNTING NUT: Nickel Plated zinc alloy  
CONTACT SPRING: Piano Wire  
KEYS (Z): Brass with code no. A126  
LOCK: Bright Ni plated zinc alloy with NI facing  
TUMBLER Mechanism: 4-disc tumbler cylinder.

## RECOMMENDED PANEL LAYOUT

|                                                                                                                    |         |                   |            |
|--------------------------------------------------------------------------------------------------------------------|---------|-------------------|------------|
| TUMBLER Mechanism: 4-disc tumbler cylinder.                                                                        |         |                   |            |
|                                                                                                                    |         |                   |            |
| B                                                                                                                  | 11401   | REVISED SCHEMATIC | 7/5/01 CJB |
| REV.                                                                                                               | ECN NO. | DESCRIPTION       | DATE CHKD  |
| THE INFORMATION CONTAINED IN THIS DOCUMENT<br>IS PROPRIETARY TO E-SWITCH AND IS<br>NOT TO BE COPIED OR TRANSFERRED |         |                   |            |
| TITLE                                                                                                              |         |                   |            |
| K01300-A126                                                                                                        |         |                   |            |
| SCALE                                                                                                              | DATE    | DR                | DWG        |
| 1.5:1                                                                                                              | 4/10/01 | CJB               | K200224    |
|                                                                                                                    |         |                   | REV        |
|                                                                                                                    |         |                   | B          |