

Distinctive Characteristics

Square, round, rectangular, and round panel seal models available.

Stainless steel clips provide secure mounting with a wide range of panel thicknesses.

Latchdown feature gives indication of circuit status. Audible and tactile feedback with smooth and responsive operation.

Snap-action contact mechanism gives long electrical life and sensitivity of actuation.


Combination solder lug and .110" quick connect terminals are epoxy sealed to prevent entry of flux, dust, and other contaminants.

Panel sealed model meets IP65 of IEC60529 specifications (similar to NEMA 4 & 13).


Compact switch design minimizes behind panel depth.

Matching illuminated models available.

Matching indicators available.



Actual Size



General Specifications

Electrical Capacity (Resistive Load)

Power Level (silver): 3A @ 125V AC or 3A @ 250V AC or 3A @ 30V DC
Logic Level (gold): 0.4VA maximum @ 28V AC/DC maximum
 (Applicable Range 0.1mA ~ 0.1A @ 20mV ~ 28V)
 Note: Find additional explanation in Supplement section.

Other Ratings

Contact Resistance: 50 milliohms maximum for silver; 100 milliohms maximum for gold
Insulation Resistance: 200 megohms minimum @ 500V DC
Dielectric Strength: 1,000V AC minimum between contacts for 1 minute minimum;
 1,500V AC minimum between contacts & case for 1 minute minimum
Mechanical Life: 1,000,000 operations minimum for momentary circuit
 200,000 operations minimum for maintained circuit
Electrical Life: 100,000 operations minimum
Nominal Operating Force: 4.41N
Contact Timing: Nonshorting (break-before-make)
Travel: Pretravel .059" (1.5mm); Overtravel .059" (1.5mm); Total Travel .118" (3.0mm)
 Pretravel .087" (2.2mm); Overtravel .031" (0.8mm); Total Travel .118" (3.0mm)

Materials & Finishes

Housing: Glass fiber reinforced polyamide (UL94V-0)
Snap-in Frame: Stainless steel
Movable Contact: Silver alloy or copper with gold plating
Stationary Contacts: Silver alloy or copper with gold plating
Base: Liquid crystal polymer (UL94V-0)
Terminals: Phosphor bronze with silver or gold plating

Environmental Data

Operating Temp Range: -25°C through +70°C (-13°F through +158°F)
 Note: When used with a polyvinyl chloride splash cover, the lowest limit is 0°C (32°F)
Humidity: 90 ~ 95% humidity for 96 hours @ 40°C (104°F)
Vibration: 10 ~ 55Hz with peak-to-peak amplitude of 1.5mm traversing the frequency range
 & returning in 1 minute; 3 right angled directions for 2 hours
Shock: 50G (490m/s²) acceleration (tested in 6 right angled directions, with 5 shocks in each direction)
Sealing: Not available for snap-in; see next section for panel seal.

Installation

Cap Installation Force: 3.92N maximum downward force on cap
Quick Connect Force: 52.95N maximum downward force on connector
Soldering Time & Temperature: 3 seconds maximum @ 350°C maximum for manual soldering

Standards & Certifications




Flammability Standards: UL94V-0 housing & base
UL Recognized: All models recognized at 3A @ 125V or 250V AC or 0.4VA @ 28V AC/DC maximum;
 UL File No. WOYR2.E44145; add "/U" to end of part number to order UL mark on switch.



CSA Certified: All models certified at 3A @ 125V or 250V AC or 0.4VA @ 28V AC/DC maximum;
 CSA File Nos. 023535-0-000; add "/C" to end of part number to order CSA mark on switch.

TYPICAL SWITCH ORDERING EXAMPLE




IMPORTANT:




Switches are supplied without UL & CSA marking unless specified. Specific models & ratings noted on General Specifications page.

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

LB15SKW01-C



POLES & CIRCUITS


Pole	Model	Plunger Position () = Momentary		Connected Terminals		Throw & Switch/Lamp Schematics
		Normal 	Down 	Normal 	Down 	
SP	LB15 *LB16	ON ON	(ON) ON	1-3	1-2	SPDT 
DP	LB25 *LB26	ON ON	(ON) ON	1-3 4-6	1-2 4-5	DPDT 

* When in latchdown position for the alternate circuit, cap position is .039" (1.0mm) above the built-in bezel.

SHAPES & PANEL CUTOUTS

S

.622" (15.8mm)
Square



Cutout for 1 switch:


.638" x .638" (16.2mm x 16.2mm)

Cutout for 1 switch with barriers:

.638" x .815" (16.2mm x 20.7mm)


C

.854" (21.7mm)
Round



R

.622" x .866" (15.8mm x 22.0mm)
Rectangular



Cutout for 1 switch:

.638" x .882" (16.2mm x 22.4mm)

Cutout for 1 switch with barriers:

.638" x 1.059" (16.2mm x 26.9mm)

Panel Thickness for Switches & Barriers: .039" ~ .157" (1.0 ~ 4.0mm)

Panel Thickness for Protective Guards & Splash Covers: .039" ~ .138" (1.0 ~ 3.5mm)

HOUSING

Housing Colors Available:

K

Black

G

Gray

CONTACT MATERIALS, RATINGS & TERMINALS

W01

Silver Contacts

Power Level
3A @ 125V AC & 250V AC


G01

Gold Contacts

Logic Level
0.4VA max. @ 28V AC/DC max.

Solder Lug/Quick Connect

The .047" x .079" (1mm x 2mm) oblong hole accommodates one solid 18-gauge wire or two solid or stranded 20-gauge wires.



Complete explanation of operating range in Supplement section.

CAPS & CAP COLORS

Color Codes:

A Black

B White

C Red

E Yellow

F Green

G Blue

H Gray

Cap Colors Available:

A

E

H


B

F


C

G


AT484
Square



AT4017
Round



AT4030
Rectangular






Material: Polycarbonate

Finish: Glossy

TYPICAL SWITCH DIMENSIONS

Square

Single & Double Pole






LB15SKW01-C

Single pole models do not have terminals 4, 5, & 6.

Round

Single & Double Pole






LB16CKW01-C

Single pole models do not have terminals 4, 5, & 6.

Rectangular

Single & Double Pole




LB26RGW01-C

Single pole models do not have terminals 4, 5, & 6.


OPTIONAL ACCESSORIES

Barriers


**AT497
End**



**AT498
Center**



Cutouts for More Than 1 Switch







Material: Polyamide

Square
 $A = .752" (19.1\text{mm}) \times \text{Number of Switches} + .051" (1.3\text{mm})$
Rectangular
 $A = .996" (25.3\text{mm}) \times \text{Number of Switches} + .051" (1.3\text{mm})$

Protective Guard

**AT499
Square
Protective Guard**

Opens 90°
Closes manually








Material: Polyamide

Protective Guards reduce depth of switch behind panel by .020" (0.5mm).

Spring Loaded Protective Guard

**AT4171
Square
Protective Guard**


Opens 180°
Closes automatically



(N) = Number of switches * Minimum dimension allows opening of cover to 180°

Materials:

Cover: Clear Polycarbonate
Base: Black GFR Polyamide
Coil Spring: Stainless Steel



Recommended Panel Thickness:
.039" ~ .106" (1.0mm ~ 2.7mm)


OPTIONAL ACCESSORIES

Protective Guard

AT4057

**Rectangular
Protective Guard**

Opens 90°
Closes manually



Material: Polyamide



Protective Guards reduce depth of switch behind panel by .020" (0.5mm).

Spring Loaded Protective Guard

AT4172

**Rectangular
Protective Guard**

Opens 180°
Closes automatically





Materials:

Cover: Clear Polycarbonate

Base: Black GFR Polyamide

Coil Spring: Stainless Steel

Recommended Panel Thickness: .039" ~ .106" (1.0mm ~ 2.7mm)




(N) = Number of switches

* Minimum dimension allows opening of cover to 180°



OPTIONAL ACCESSORIES

Dust Covers



AT4002
Round



AT4001
Square




AT4011
Rectangular




Materials: PVC with polyethylene gasket; PVC loses pliability below 0°C (32°F). Dust Covers reduce depth of switch behind panel by .020" (0.5mm).

PCB Adaptors

AT711 Single Pole • Straight PC Terminals



AT712 Double Pole • Straight PC Terminals



Note: Order adaptors separately.