

SN54F253, SN74F253  
DUAL 1-OF-4 DATA SELECTORS/MUXES  
WITH 3-STATE OUTPUTS

SDF064A – D2032, MARCH 1987 – REVISED OCTOBER 1993

- 3-State Versions of SN54F153 and SN74F153
- Permits Multiplexing From N Lines to One Line
- Performs Parallel-to-Serial Conversion
- Package Options Include Plastic Small-Outline Packages, Ceramic Chip Carriers, and Standard Plastic and Ceramic 300-mil DIPs


### description

These data selectors/multiplexers contain inverters and drivers to supply full binary decoding data selection to the AND-OR gates. Separate output-control inputs are provided for each of the two 4-line sections.


The 3-state outputs can interface with and drive data lines of bus-organized systems. With all but one of the common outputs disabled (at a high-impedance state), the low impedance of the single enabled output will drive the bus line to a high or low logic level. Each output has its own strobe ( $\bar{G}$ ) inputs. The output is disabled when its strobe is high.

The SN54F253 is characterized for operation over the full military temperature range of  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . The SN74F253 is characterized for operation from  $0^{\circ}\text{C}$  to  $70^{\circ}\text{C}$ .

SN54F253 . . . J PACKAGE  
SN74F253 . . . D OR N PACKAGE  
(TOP VIEW)



SN54F253 . . . FK PACKAGE  
(TOP VIEW)



NC – No internal connection

FUNCTION TABLE


		INPUTS				STROBE $\bar{G}$	OUTPUT Y
SELECT		C0	C1	C2	C3		
B	A	X	X	X	X	H	Z
L	L	L	X	X	X	L	L
L	L	H	X	X	X	L	H
L	H	X	L	X	X	L	L
L	H	X	H	X	X	L	H
H	L	X	X	L	X	L	L
H	L	X	X	H	X	L	H
H	H	X	X	X	L	L	L
H	H	X	X	X	H	L	H

Select inputs A and B are common to both sections.

**SN54F253, SN74F253  
DUAL 1-OF-4 DATA SELECTORS/MUXES  
WITH 3-STATE OUTPUTS**


SDF5064A - D2032, MARCH 1987 - REVISED OCTOBER 1993

**logic symbol†**



† This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.  
Pin numbers shown are for the D, J, and N packages.

logic diagram (positive logic)



Pin numbers shown are for the D, J, and N packages.

**SN54F253, SN74F253  
DUAL 1-OF-4 DATA SELECTORS/MUXES  
WITH 3-STATE OUTPUTS**

SDFS064A – D2032, MARCH 1987 – REVISED OCTOBER 1993

**absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>**

Supply voltage range, $V_{CC}$ .....	.....	.....	.....	.....	.....	.....	–0.5 V to 7 V
Input voltage range (see Note 1) .....	.....	.....	.....	.....	.....	.....	–1.2 V to 7 V
Input current range .....	.....	.....	.....	.....	.....	.....	–30 mA to 5 mA
Voltage range applied to any output in the disabled or power-off state .....	.....	.....	.....	.....	.....	.....	–0.5 V to 5.5 V
Voltage range applied to any output in the high state .....	.....	.....	.....	.....	.....	.....	–0.5 V to $V_{CC}$
Current into any output in the low state: SN54F253 .....	.....	.....	.....	.....	.....	.....	40 mA
	SN74F253 .....	.....	.....	.....	.....	.....	48 mA
Operating free-air temperature range: SN54F253 .....	.....	.....	.....	.....	.....	.....	–55°C to 125°C
	SN74F253 .....	.....	.....	.....	.....	.....	0°C to 70°C
Storage temperature range .....	.....	.....	.....	.....	.....	.....	–65°C to 150°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: The input voltage ratings may be exceeded provided the input current ratings are observed.

**recommended operating conditions**

		SN54F253			SN74F253			UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	
$V_{CC}$	Supply voltage	4.5	5	5.5	4.5	5	5.5	V
$V_{IH}$	High-level input voltage	2			2			V
$V_{IL}$	Low-level input voltage			0.8			0.8	V
$I_{IK}$	Input clamp current			–18			–18	mA
$I_{OH}$	High-level output current			–3			–3	mA
$I_{OL}$	Low-level output current			20			24	mA
$T_A$	Operating free-air temperature	–55		125	0		70	°C

SN54F253, SN74F253  
**DUAL 1-OF-4 DATA SELECTORS/MUXES**  
**WITH 3-STATE OUTPUTS**

SDFS064A – D2032, MARCH 1987 – REVISED OCTOBER 1993

**electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)**

PARAMETER	TEST CONDITIONS	SN54F253			SN74F253			UNIT
		MIN	TYP†	MAX	MIN	TYP†	MAX	
$V_{IK}$	$V_{CC} = 4.5 \text{ V}$ , $I_I = -18 \text{ mA}$			-1.2			-1.2	V
$V_{OH}$	$V_{CC} = 4.5 \text{ V}$	$I_{OH} = -1 \text{ mA}$	2.5	3.4	2.5	3.4		V
		$I_{OH} = -3 \text{ mA}$	2.4	3.3	2.4	3.3		
	$V_{CC} = 4.75 \text{ V}$ , $I_{OH} = -1 \text{ mA to } -3 \text{ mA}$					2.7		
$V_{OL}$	$V_{CC} = 4.5 \text{ V}$	$I_{OL} = 20 \text{ mA}$	0.3	0.5			0.35	V
		$I_{OL} = 24 \text{ mA}$					0.5	
$I_{OZH}$	$V_{CC} = 5.5 \text{ V}$ , $V_O = 2.7 \text{ V}$			50			50	$\mu\text{A}$
$I_{OZL}$	$V_{CC} = 5.5 \text{ V}$ , $V_O = 0.5 \text{ V}$			-50			-50	$\mu\text{A}$
$I_I$	$V_{CC} = 5.5 \text{ V}$ , $V_I = 7 \text{ V}$			0.1			0.1	mA
$I_{IH}$	$V_{CC} = 5.5 \text{ V}$ , $V_I = 2.7 \text{ V}$			20			20	$\mu\text{A}$
$I_{IL}$	$V_{CC} = 5.5 \text{ V}$ , $V_I = 0.5 \text{ V}$			-0.6			-0.6	mA
$I_{OS}^‡$	$V_{CC} = 5.5 \text{ V}$ , $V_O = 0$		-60	-150	-60	-150		mA
$I_{CCH}$	$V_{CC} = 5.5 \text{ V}$ , See Note 2	Condition A		11.5	16		11.5	16
$I_{CCL}$		Condition B		16	23		16	23
$I_{CCZ}$		Condition C		16	23		16	23

† All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

‡ Not more than one output should be shorted at a time, and the duration of the short circuit should not exceed one second.

NOTE 2:  $I_{CC}$  is measured with the outputs open under the following conditions:

A. Inputs A, B, 1C3, and 2C3 at 4.5 V, other inputs grounded

B. All inputs grounded

C. Inputs 1G and 2G at 4.5 V, other inputs grounded

**switching characteristics (see Note 3)**

PARAMETER	FROM (INPUT)	TO (OUTPUT)	$V_{CC} = 5 \text{ V}$ , $C_L = 50 \text{ pF}$ , $R1 = 500 \Omega$ , $R2 = 500 \Omega$ , $T_A = 25^\circ\text{C}$	$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$ , $C_L = 50 \text{ pF}$ , $R1 = 500 \Omega$ , $R2 = 500 \Omega$ , $T_A = \text{MIN to MAX}^§$			UNIT	
			'F253			SN54F253	SN74F253	
			MIN	TYP	MAX	MIN	MAX	
$t_{PLH}$	A or B	Any Y	3.7	8.1	11.5	2.7	15	3.7 13
			2.2	6.1	9	1.7	11	2.2 10
$t_{PHL}$	Any C	Any Y	2.2	5.1	7	1.7	9	2.2 8
			1.7	4.1	6	1.7	8	1.7 7
$t_{PZH}$	$\bar{G}$	Any Y	2.2	5.6	8	1.7	10	2.2 9
			2.2	5.6	8	1.7	10	2.2 9
$t_{PZL}$	$\bar{G}$	Any Y	1.2	3.3	5	1.2	6.5	1.2 6
			1.2	4	6	1.2	8	1.2 7

§ For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

NOTE 3: Load circuit and waveforms are shown in Section 1.



### **IMPORTANT NOTICE**

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

**CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.**

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 1998, Texas Instruments Incorporated