




RT134009 Product Details



RT134009
(2-1393239-5)

TE Internal Number: 2-1393239-5



[Contact Product Information Center](#)

Industrial Relays (General Purpose)



Product Highlights:

- Relay Type = Miniature Power PCB Relay
- Relay Style = PCB
- RT Series
- Contact - Arrangement = 1 Form A, SPST-NO, 1 N/O
- Contact - Rated Current = 12 A

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)



Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Schematic](#)
- [PCB Layout](#)
- [Wiring Diagram](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Series](#) = RT
- [Termination Type](#) = Through Hole

Electrical Characteristics:

- [Contact - Rated Current \(A\)](#) = 12
- [Coil - Resistance \(\$\Omega\$ \)](#) = 202
- [Coil - Rated Power, DC \(mW\)](#) = 400
- [Actuating System](#) = DC
- [Input Voltage \(VDC\)](#) = 9
- Insulation - Special Features = None
- Coil Rating = Sensitive

Body Features:

- Polarized = No

Contact Features:

- Relay Type = Miniature Power PCB Relay
- [Mounting Options](#) = PC Board
- [Enclosure Type](#) = Flux-Tight
- [Contact Base Material](#) = Silver Nickel Alloy
- Approx. Dimensions (L x W x H) (mm [in]) = 29.00 x 12.70 x 15.70 [1.142 x .500 x .618]
- Terminal Assignment = Code 1

Configuration Features:

- Relay Style = PCB
- [Contact - Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Coil - Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive
- Approved Standards = UL Recognized, CSA Certified, VDE Component Mark

Other:

- Brand = Schrack

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

