




Features

- Multiturn / Cermet / Industrial / Sealed
- Low temperature coefficient: ± 100 ppm/ $^{\circ}\text{C}$
- Stable, infinite resolution cermet element
- CRV 1.0 % or 1 ohm
- Panel mount option available
- RoHS compliant* version available

3009 - 3/4 " Rectangular Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range10 to 2 megohms
(see standard resistance table)
Resistance Tolerance ± 10 % std.
(tighter tolerance available)
Absolute Minimum Resistance1.0 % or 2 ohms max.
(whichever is greater)
Contact Resistance Variation1.0 % or 1 ohm max.
(whichever is greater)
Adjustability
Voltage ± 0.01 %
Resistance ± 0.05 %
ResolutionInfinite
Insulation Resistance500 vdc
100 megohms min.
Dielectric Strength
Sea Level1,000 vac
80,000 Feet250 vac
Adjustment Angle15 turns nom.



Environmental Characteristics

Power Rating (400 volts max.)
70 $^{\circ}\text{C}$ 0.75 watt
150 $^{\circ}\text{C}$ 0 watt
Temperature Range-55 $^{\circ}\text{C}$ to +150 $^{\circ}\text{C}$
Temperature Coefficient ± 100 ppm/ $^{\circ}\text{C}$
Seal Test85 $^{\circ}\text{C}$ Fluorinert[†]
HumidityMIL-STD-202 Method 103
96 hours
(3 % ΔTR , 20 megohms IR)
Vibration20 G (2 % ΔTR ; 2 % ΔVR)
Shock50 G (2 % ΔTR ; 2 % ΔVR)
Load Life1,000 hours, 0.75 watt @ 70 $^{\circ}\text{C}$
(4 % ΔTR)
Rotational Life200 cycles
(3 % ΔTR ; 1 % or 1 ohm, whichever is greater, CRV)


Physical Characteristics

Torque5.0 oz-in. max.
Mechanical StopsWiper idles
TerminalsSolderable pins
Weight0.05 oz.
MarkingManufacturer's trademark, resistance code, terminal numbers, date code, manufacturer's model number and style
Standard Packaging25 pcs. per tube

Product Dimensions



TOLERANCES: $\pm .25$ ($\pm .010$) EXCEPT WHERE NOTED
DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$



Standard Resistance Table

Resistance (Ohms)	Resistance Code
10	100
20	200
50	500
100	101
200	201
500	501
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
25,000	253
50,000	503
100,000	104
200,000	204
250,000	254
500,000	504
1,000,000	105
2,000,000	205

How To Order

3009 P - 1 - 103 Z LF

Model _____
Style _____
Standard or Modified Product Indicator _____
-1 = Standard Product
-11 = 5 % Resistance Tolerance
Resistance Code _____
Optional Suffix Letter _____
Z = Panel Mount (Factory Installed)
Terminations _____
LF = 100 % Tin-plated (RoHS compliant)
Blank = 90 % Tin / 10 % Lead-plated (Standard)

Consult factory for other available options.