



# **3.3V CMOS 16-BIT BUS TRANSCEIVER WITH 5 VOLT TOLERANT I/O AND BUS-HOLD**

**IDT74LVCH162245A**

## FEATURES:

- Typical  $t_{sk(\phi)}$  (Output Skew) < 250ps
- ESD > 2000V per MIL-STD-883, Method 3015;  
> 200V using machine model ( $C = 200\text{pF}$ ,  $R = 0$ )
- 0.635mm pitch SSOP, 0.50mm pitch TSSOP  
and 0.40mm pitch TVSOP packages
- Extended commercial range of  $-40^\circ\text{C}$  to  $+85^\circ\text{C}$
- $V_{CC} = 3.3\text{V} \pm 0.3\text{V}$ , Normal Range
- $V_{CC} = 2.7\text{V}$  to  $3.6\text{V}$ , Extended Range
- CMOS power levels ( $0.4\mu\text{W}$  typ. static)
- All inputs, outputs and I/O are 5 Volt tolerant
- Supports hot insertion

## Drive Features for LVCH162245A:

- Balanced Output Drivers:  $\pm 12$  mA (A port)
- High Output Drivers:  $\pm 24$  mA (B port)

## APPLICATIONS:

- 5V and 3.3V mixed voltage systems
- Data communication and telecommunication systems

## **DESCRIPTION:**

This 16-bit bus transceiver is built using advanced dual metal CMOS technology. This high-speed, low power transceiver is ideal for asynchronous communication between two busses (A and B). The Direction and Output Enable controls are designed to operate this device as either two independent 8-bit transceivers or one 16-bit transceiver. The direction control pin (DIR) controls the direction of data flow. The output enable pin (OE) overrides the direction control and disables both ports. All inputs are designed with hysteresis for improved noise margin.


All pins can be driven from either 3.3V or 5V devices. This feature allows the use of this device as a translator in a mixed 3.3V/5V supply system.

The LVCH162245A (B port) has been designed with a  $\pm 24\text{mA}$  output driver. This driver is capable of driving a moderate to heavy load while maintaining speed performance.

The LVCH162245 (A port) has series resistors in the device output structure which will significantly reduce line noise when used with light loads. The driver has been designed to drive  $\pm 12\text{mA}$  at the designated threshold levels.

The LVCH162245A has "bus-hold" which retains the inputs' last state whenever the input goes to a high impedance. This prevents floating inputs and eliminates the need for pull-up/down resistors.

## Functional Block Diagram



## **EXTENDED COMMERCIAL TEMPERATURE RANGE**

**MARCH 1999**

## PIN CONFIGURATION

1DIR	1	48	1OE
1B1	2	47	1A1
1B2	3	46	1A2
GND	4	45	GND
1B3	5	44	1A3
1B4	6	43	1A4
Vcc	7	42	Vcc
1B5	8	41	1A5
1B6	9	40	1A6
GND	10	39	GND
1B7	11	38	1A7
1B8	12	37	1A8
2B1	13	SO48-1	SO48-2
		36	SO48-3
2B2	14	35	2A1
GND	15	34	2A2
2B3	16	33	GND
2B4	17	32	2A3
Vcc	18	31	2A4
2B5	19	30	Vcc
2B6	20	29	2A5
GND	21	28	2A6
2B7	22	27	GND
2B8	23	26	2A7
2DIR	24	25	2A8
			2OE

SSOP/ TSSOP/ TVSOP  
TOP VIEW

## ABSOLUTE MAXIMUM RATINGS (1)

Symbol	Description	Max.	Unit
V <sub>TERM(2)</sub>	Terminal Voltage with Respect to GND	- 0.5 to +6.5	V
V <sub>TERM(3)</sub>	Terminal Voltage with Respect to GND	- 0.5 to +6.5	V
T <sub>STG</sub>	Storage Temperature	- 65 to +150	°C
I <sub>OUT</sub>	DC Output Current	- 50 to +50	mA
I <sub>lk</sub>	Continuous Clamp Current, V <sub>i</sub> < 0 or V <sub>o</sub> < 0	- 50	mA
I <sub>cc</sub>	Continuous Current through each V <sub>cc</sub> or GND	±100	mA
I <sub>ss</sub>			

LVC Link

### NOTES:

1. Stresses greater than those listed under ABSOLUTE MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.
2. V<sub>cc</sub> terminals.
3. All terminals except V<sub>cc</sub>.

## CAPACITANCE (T<sub>A</sub> = +25°C, f = 1.0MHz)

Symbol	Parameter <sup>(1)</sup>	Conditions	Typ.	Max.	Unit
C <sub>IN</sub>	Input Capacitance	V <sub>IN</sub> = 0V	4.5	6	pF
C <sub>OUT</sub>	Output Capacitance	V <sub>OUT</sub> = 0V	6.5	8	pF
C <sub>I/O</sub>	I/O Port Capacitance	V <sub>IN</sub> = 0V	6.5	8	pF

LVC Link

### NOTE:

1. As applicable to the device type.

## PIN DESCRIPTION

Pin Names	Description
x <sub>OE</sub>	Output Enable Inputs (Active LOW)
x <sub>DIR</sub>	Direction Control Inputs
x <sub>Ax</sub>	Side A Inputs or 3-State Outputs <sup>(1)</sup>
x <sub>Bx</sub>	Side B Inputs or 3-State Outputs <sup>(1)</sup>

### NOTE:

1. These pins have "Bus-hold". All other pins are standard inputs, outputs, or I/Os.

## FUNCTION TABLE (1)

Inputs		Outputs
x <sub>OE</sub>	x <sub>DIR</sub>	
L	L	Bus B Data to Bus A
L	H	Bus A Data to Bus B
H	X	High Z State

### NOTE:

1. H = HIGH Voltage Level  
L = LOW Voltage Level  
X = Don't Care  
Z = High-Impedance

## DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE

Following Conditions Apply Unless Otherwise Specified:

Operating Condition:  $T_A = -40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$

Symbol	Parameter	Test Conditions		Min.	Typ. <sup>(1)</sup>	Max.	Unit
V <sub>IH</sub>	Input HIGH Voltage Level	V <sub>CC</sub> = 2.3V to 2.7V		1.7	—	—	V
		V <sub>CC</sub> = 2.7V to 3.6V		2	—	—	
V <sub>IL</sub>	Input LOW Voltage Level	V <sub>CC</sub> = 2.3V to 2.7V		—	—	0.7	V
		V <sub>CC</sub> = 2.7V to 3.6V		—	—	0.8	
I <sub>IH</sub> I <sub>IL</sub>	Input Leakage Current	V <sub>CC</sub> = 3.6V	V <sub>I</sub> = 0 to 5.5V	—	—	$\pm 5$	$\mu\text{A}$
I <sub>OZH</sub> I <sub>OZL</sub>	High Impedance Output Current (3-State Output pins)	V <sub>CC</sub> = 3.6V	V <sub>O</sub> = 0 to 5.5V	—	—	$\pm 10$	$\mu\text{A}$
I <sub>OFF</sub>	Input/Output Power Off Leakage	V <sub>CC</sub> = 0V, V <sub>IN</sub> or V <sub>O</sub> $\leq$ 5.5V		—	—	$\pm 50$	$\mu\text{A}$
V <sub>IK</sub>	Clamp Diode Voltage	V <sub>CC</sub> = 2.3V, I <sub>IN</sub> = -18mA		—	-0.7	-1.2	V
V <sub>H</sub>	Input Hysteresis	V <sub>CC</sub> = 3.3V		—	100	—	mV
I <sub>ICL</sub> I <sub>ICCH</sub> I <sub>ICCZ</sub>	Quiescent Power Supply Current	V <sub>CC</sub> = 3.6V	V <sub>IN</sub> = GND or V <sub>CC</sub>	—	—	10	$\mu\text{A}$
			3.6 $\leq$ V <sub>IN</sub> $\leq$ 5.5V <sup>(2)</sup>	—	—	10	
$\Delta I_{CC}$	Quiescent Power Supply Current Variation	One input at V <sub>CC</sub> - 0.6V other inputs at V <sub>CC</sub> or GND		—	—	500	$\mu\text{A}$

LVC Link

### NOTES:

1. Typical values are at V<sub>CC</sub> = 3.3V, +25°C ambient.

2. This applies in the disabled state only.

## BUS-HOLD CHARACTERISTICS

Symbol	Parameter <sup>(1)</sup>	Test Conditions		Min.	Typ. <sup>(2)</sup>	Max.	Unit
I <sub>BHH</sub> I <sub>BHL</sub>	Bus-Hold Input Sustain Current	V <sub>CC</sub> = 3.0V	V <sub>I</sub> = 2.0V	-75	—	—	$\mu\text{A}$
			V <sub>I</sub> = 0.8V	75	—	—	
I <sub>BHH</sub> I <sub>BHL</sub>	Bus-Hold Input Sustain Current	V <sub>CC</sub> = 2.3V	V <sub>I</sub> = 1.7V	—	—	—	$\mu\text{A}$
			V <sub>I</sub> = 0.7V	—	—	—	
I <sub>BHHO</sub> I <sub>BHLO</sub>	Bus-Hold Input Overdrive Current	V <sub>CC</sub> = 3.6V	V <sub>I</sub> = 0 to 3.6V	—	—	$\pm 500$	$\mu\text{A}$
				—	—	$\pm 500$	

LVC Link

### NOTES:

1. Pins with Bus-hold are identified in the pin description.

2. Typical values are at V<sub>CC</sub> = 3.3V, +25°C ambient.

## OUTPUT DRIVE CHARACTERISTICS (A PORT)

Symbol	Parameter	Test Conditions <sup>(1)</sup>		Min.	Max.	Unit
VOH	Output HIGH Voltage	VCC = 2.3V to 3.6V	IOH = - 0.1mA	VCC - 0.2	—	V
		VCC = 2.3V	IOH = - 4mA	1.9	—	
			IOH = - 6mA	1.7	—	
		VCC = 2.7V	IOH = - 4mA	2.2	—	
			IOH = - 8mA	2	—	
		VCC = 3.0V	IOH = - 6mA	2.4	—	
			IOH = - 12mA	2	—	
VOL	Output LOW Voltage	VCC = 2.3V to 3.6V	IOL = 0.1mA	—	0.2	V
		VCC = 2.3V	IOL = 4mA	—	0.4	
			IOL = 6mA	—	0.55	
		VCC = 2.7V	IOL = 4mA	—	0.4	
			IOL = 8mA	—	0.6	
		VCC = 3.0V	IOL = 6mA	—	0.55	
			IOL = 12mA	—	0.8	

**NOTE:**

1. VIH and Vil must be within the min. or max. range shown in the DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE table for the appropriate Vcc range. TA = -40°C to +85°C.

## OUTPUT DRIVE CHARACTERISTICS (B PORT)

Symbol	Parameter	Test Conditions <sup>(1)</sup>		Min.	Max.	Unit
VOH	Output HIGH Voltage	VCC = 2.3V to 3.6V	IOH = - 0.1mA	VCC - 0.2	—	V
		VCC = 2.3V	IOH = - 6mA	2	—	
		VCC = 2.3V	IOH = - 12mA	1.7	—	
		VCC = 2.7V		2.2	—	
		VCC = 3.0V		2.4	—	
		VCC = 3.0V	IOH = - 24mA	2.2	—	
VOL	Output LOW Voltage	VCC = 2.3V to 3.6V	IOL = 0.1mA	—	0.2	V
		VCC = 2.3V	IOL = 6mA	—	0.4	
			IOL = 12mA	—	0.7	
		VCC = 2.7V	IOL = 12mA	—	0.4	
		VCC = 3.0V	IOL = 24mA	—	0.55	

**NOTE:**

1. VIH and Vil must be within the min. or max. range shown in the DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE table for the appropriate Vcc range. TA = -40°C to +85°C.

**OPERATING CHARACTERISTICS,  $V_{CC} = 3.3V \pm 0.3V$ ,  $T_A = 25^\circ C$** 

Symbol	Parameter	Test Conditions	Typical	Unit
CPD	Power Dissipation Capacitance per Transceiver Outputs enabled	$C_L = 0pF, f = 10Mhz$	39	pF
CPD	Power Dissipation Capacitance per Transceiver Outputs disabled		4	pF

**SWITCHING CHARACTERISTICS, (A PORT) (1)**

Symbol	Parameter	$V_{CC} = 2.7V$		$V_{CC} = 3.3V \pm 0.3V$		Unit
		Min.	Max.	Min.	Max.	
$t_{PLH}$	Propagation Delay $x_{Bx}$ to $x_{Ax}$	1.5	5.7	1.5	4.8	ns
$t_{PHL}$	Output Enable Time $x_{\overline{OE}}$ to $x_{Ax}$	1.5	7.9	1.5	6.3	ns
$t_{PHZ}$	Output Disable Time $x_{\overline{OE}}$ to $x_{Ax}$	1.5	8.3	2.2	7.4	ns
$t_{PLZ}$		—	—	—	500	ps
$t_{SK(o)}$	Output Skew <sup>(2)</sup>	—	—	—	500	ps

**SWITCHING CHARACTERISTICS, (B PORT) (1)**

Symbol	Parameter	$V_{CC} = 2.7V$		$V_{CC} = 3.3V \pm 0.3V$		Unit
		Min.	Max.	Min.	Max.	
$t_{PLH}$	Propagation Delay $x_{Ax}$ to $x_{Bx}$	1.5	4.7	1	4	ns
$t_{PHL}$	Output Enable Time $x_{\overline{OE}}$ to $x_{Bx}$	1.5	6.7	1.5	5.5	ns
$t_{PHZ}$	Output Disable Time $x_{\overline{OE}}$ to $x_{Bx}$	1.5	7.1	1.5	6.6	ns
$t_{PLZ}$		—	—	—	500	ps
$t_{SK(o)}$	Output Skew <sup>(2)</sup>	—	—	—	500	ps

**NOTES:**


1. See test circuits and waveforms.  $T_A = -40^\circ C$  to  $+85^\circ C$ .
2. Skew between any two outputs of the same package and switching in the same direction.

## TEST CIRCUITS AND WAVEFORMS

### TEST CONDITIONS

Symbol	$V_{CC(1)} = 3.3V \pm 0.3V$	$V_{CC(1)} = 2.7V$	$V_{CC(2)} = 2.5V \pm 0.2V$	Unit
$V_{LOAD}$	6	6	$2 \times V_{CC}$	V
$V_{IH}$	2.7	2.7	$V_{CC}$	V
$V_T$	1.5	1.5	$V_{CC} / 2$	V
$V_{LZ}$	300	300	150	mV
$V_{HZ}$	300	300	150	mV
$C_L$	50	50	30	pF

### TEST CIRCUITS FOR ALL OUTPUTS



#### DEFINITIONS:

$C_L$  = Load capacitance: includes jig and probe capacitance.  
 $R_T$  = Termination resistance: should be equal to  $Z_{OUT}$  of the Pulse Generator.

#### NOTE:


1. Pulse Generator for All Pulses: Rate  $\leq 10$ MHz;  $t_F \leq 2.5$ ns;  $t_R \leq 2.5$ ns.
2. Pulse Generator for All Pulses: Rate  $\leq 10$ MHz;  $t_F \leq 2$ ns;  $t_R \leq 2$ ns.

### SWITCH POSITION

Test	Switch
Open Drain	$V_{LOAD}$
Disable Low	
Enable Low	
Disable High	GND
Enable High	
All Other tests	Open

LVC Link

### OUTPUT SKEW - $t_{SK}(x)$




$$tsk(x) = |tPLH2 - tPLH1| \text{ or } |tPHL2 - tPHL1|$$

LVC Link


#### NOTES:

1. For  $tsk(o)$  OUTPUT1 and OUTPUT2 are any two outputs.
2. For  $tsk(b)$  OUTPUT1 and OUTPUT2 are in the same bank.

### PROPAGATION DELAY




### ENABLE AND DISABLE TIMES




#### NOTE:

1. Diagram shown for input Control Enable-LOW and input Control Disable-HIGH.

### SET-UP, HOLD, AND RELEASE TIMES




### PULSE WIDTH



## **ORDERING INFORMATION**

IDT	XX	LVC	X	XX	XXXX	XX
Temp. Range	Bus-Hold	Family	Device Type	Package		



## **CORPORATE HEADQUARTERS**

2975 Stender Way  
Santa Clara, CA 95054

*for SALES:*

800-345-7015 or 408-727-6116  
fax: 408-492-8674  
[www.idt.com](http://www.idt.com)\*

*\*To search for sales office near you, please click the sales button found on our home page or dial the 800# above and press 2.  
The IDT logo is a registered trademark of Integrated Device Technology, Inc.*