


MATERIALS

BODY	BRASS NICKEL PLATED
CONTACT	GOLD PLATED
INSULATOR	PTFE



SPECIFICATIONS

FREQUENCY RANGE: DC TO 2,000 MHz

ATTENUATION: 6 dB

IMPEDANCE: 50 OHMS

ACCURACY: 1,000 MHz, ± 5 dB

2,000 MHz, ± 8 dB

VSWR: 1,000 MHz, 1.20:1 MAXIMUM

2,000 MHz, 1.40:1 MAXIMUM

AVG. POWER HANDLING CAPABILITY: 1 WATT



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7003-6

DES.

TNC ATTENUATOR, MALE TO FEMALE
FREQUENCY RANGE: DC TO 2,000 MHz

SIZE A

FSCM NO. 53919

CAD FILE 092305

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.