



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
		L		REVISED PER 0G3B-0170-05	4/11/05	SS	GS



- ① NYLON, UL 94-V0 RATED, RED.
- ② PHOSPHOR BRONZE.
- ③ 3.81um [.000150] MIN TIN-LEAD OVER 1.27um [.000050] MIN NICKEL.
- ④ 0.76um [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- ⑤ 3.81um [.000150] MIN TIN OVER 1.27um [.000050] MIN NICKEL.
- ⑥ 0.76um [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

RECOMMENDED LAYOUT

CONTACT FINISH	MOUNTING TABS	PART NUMBER
⑥	NO	1-207496-0
⑥	YES	207496-9
⑤	NO	207496-8
⑤	YES	207496-7
④	NO	207496-4
④	YES	207496-3
③	NO	207496-2
③	YES	207496-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	L.SIPE	03/17/92	Tyco Electronics Corporation Harrisburg, Pa 17105-3608
CHK	R.STONE	3-25-92	
DIMENSIONS: mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -			NAME PRODUCT SPEC 108-10033 APPLICATION SPEC
MATERIAL HOUSING: 1 CONTACT: SEE TABLE			
CUSTOMER DRAWING			SCALE 4:1 SHEET 1 OF 1 REV L