


Technical drawing of a mechanical part showing a cross-section. The drawing includes two dimension lines with arrows indicating measurements from the top surface of the part. The first dimension is 6.22[.245], and the second dimension is 0.76[.030]. The part features a central circular hole, a rectangular slot, and a complex, multi-faceted right side.

SECTION A-A



SECTION B-B

TIN PLATE	PHOS. BRONZE	154740-2
NONE	PHOS. BRONZE	154740-1
FINISH	MATERIAL	PART NUMBER

DIMENSIONS:		DWN	RAVI S	04JAN2017	MATERIAL		SEE TABLE	FINISH		SEE TABLE
mm [INCHES]		CHK	LI DAISY	04JAN2017	TE Connectivity					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	DING TIM	04JAN2017						
		PRODUCT SPEC		NAME						
0 PLC	± -	—			.177 (4.50) DIA. RIGHT ANGLE PIN RECEPTACLE					
1 PLC	± -									
2 PLC	± 0.40[.015]	APPLICATION SPEC			SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
3 PLC	± 0.40[.015]				A4		00779	©-154740		
4 PLC	± -	WEIGHT			SCALE		SHEET	1 OF 1	REV	
ANGLES	± -				CUSTOMER DRAWING		4:1		A1	
