












NIL	AVAILABLE		DRAM 3.3V	144	3-390113-1 
3-390113-1	NOT AVAILABLE		DRAM 3.3V	144	3-390113-4 
NIL	AVAILABLE		DRAM 3.3V	144	3-390113-1 
390113-1	NOT AVAILABLE		DRAM 3.3V	144	390113-4
NIL	AVAILABLE		DRAM 3.3V	144	390113-1
SUPERSEDED BY	REMARKS	FINISH	POWER SUPPLY	POS	PART NUMBER

 TE Connectivity	
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ± FINISH SEE TABLE
MATERIAL 	DWN. W. SORAH 6-20-97 CHK. R. TALLEY 6-20-97 APVD. SF LEONG PRODUCT SPEC 108-1739 APPLICATION SPEC 114-1114 WEIGHT - CUSTOMER DRAWING
NAME S.O. DIMM SOCKET, 0.8mm PITCH, 3.3V, 144 POSITION, STD PROFILE FOR SDRAM TYPE MODULE SIZE A CAGE CODE 00779 DRAWING NO. 390113 RESTRICTED TO - SCALE 4:1 SHEET 1 of 2 REV M1	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DY	-						
			-	SEE SHEET 1	-	-	-



RECOMMENDED P.C. BOARD PATTERN LAYOUT
(CONNECTOR MOUNTING SIDE)

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN W. SORAH 6-20-97		CHK R. TALLEY 6-20-97		APVD SF LEONG		NAME S.O. DIMM SOCKET, 0.8mm PITCH, 3.3V, 144 POSITION, STD PROFILE FOR SDRAM TYPE MODULE	
mm		0 PLC ±0.2		PRODUCT SPEC		APPLICATION SPEC		SIZE		RESTRICTED TO	
MATERIAL		FINISH		SEE TABLE		WEIGHT		CAGE CODE		DRAWING NO	
								00779		C=390113	
								CUSTOMER DRAWING		SCALE 4:1	
								SHEET 2 OF 2		REV	