















Axiall fter
Axial Fans
Ventilateur Axial




D241, D243, D244 6 V DC




D241, D243, D244 12 V DC



D241Q, D243Q, D244Q 6 V DC



D241Q, D243Q, D244Q 12 V DC



D240	mm	inch
D1	24	0.945
D2	22	0.866
L1	30	1.181
L2	15	0.590
L3	3	0.118
L4	35	1.380
B	2.6	0.102
Q1	28	1.102
Q2	22	0.866
R	2	0.079

D240

Die D240Q-Baureihe ist mit elektronischem Motor, inklusive MICRONEL ASIC ausger stet (3 Litzen)
- sehr lange Laufzeit
- Spannungsbereich 5 - 16 V DC
- Tachosignal
- PWM (V DC unabh ngige Rpm)
- Strombegrenzung
Option: 10 Litzen Ausgang mit weiteren Funktionen

The serie D240Q ist equipped with an electronic motor, including MICRONEL ASIC (3 leads)
- Long life
- voltage range 5 - 16 V DC
- tach signal (speed indicator)
- PWM (Rpm independent of V DC)
- current limitation
Option: 10 leads-version with further functions

La s rie D240Q est  quip e d'un motor  lectronique, ASIC MICRONEL inclus (3 fils)
- Usage longue vie
- gamme de tension 5 - 16 V DC
- signal tachometer
- PWM (Rpm ind pendant du V DC)
- limite de courant
Option: version 10 fils avec fonctions suppl mentaires

Types	-1	-3	-4	D241/D243/D244	D241Q-5/D243Q-5/D244Q-5
U	U _N	V		6	12
U	U	V		4.5...7.5	9...15
I	I _N	mA		32	22
I	I _{max}	mA		40	28
I	I _{block}	A		0.22	0.14
P	P _N	W		0.19	0.26
rpm	n	min ⁻¹		12 100	14 400
V	V	l/min; CFM		50/1.77	60/2.12
p	p	Pa		52	75
LpA	LpA	dB(A)		33	38
MTTF	MTTF	hr		4000	30 000
T	T	�C/F		-20...+65 / -5...+150	-20...+65 / -5...+150
m	m	g/oz.		15/0.53	23/0.81
L/M	L/M	mm/inch		200/7.874	160/6.30
PPO	PPO	UL-94V-1		o.k.	o.k.
Aluminium	Aluminium			-	-
				o.k.	o.k.
				-	-
CLL	CLL			-	-
				-	o.k.
				-	-
				-	-

