




DESCRIPTION: PLASTIC FLAT RIBBON CONNECTOR



	A	B	C
9	1.213 30.81	.984 25.00	.843 21.40
15	1.541 39.14	1.312 33.33	.843 21.40
25	2.088 53.04	1.852 47.04	.843 21.40
37	2.729 69.32	2.500 63.50	.843 21.40

SERIES
POSITIONS
009
015
025
037
050

GENDER
1 = MALE
2 = FEMALE

TERMINATION
9 = IDC

SHELL PLATING
2 = TIN

HARDWARE OPTIONS
00 = NO HARDWARE
55 = 4-40 INSERTS

PLATING OPTIONS
01 = GOLD FLASH

186-XXX-292LXX1

SPECIFICATIONS:

MATERIALS:

INSULATOR: UL 94V-0 RATED PBT
+30% FIBER-GLASS OR NYLON-66
SHELL: TIN PLATED
CONTACTS: PHOSPHOR BRONZE
RoHS COMPLIANT

ELECTRICALS:

CURRENT RATING: 1 AMP
CONTACT RESISTANCE: 15 mOHMS MAX
INSULTOR RESISTANCE: 1000 MOHMS MIN
VOLTAGE: 500V AC FOR 1 MINUTE
TEMPERATURE: -55°C TO +100°C

FOR USE WITH 26/28 AWG STRANDED .050 CENTER FLAT CABLE

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: WAYNE ROBBINS		DATE: 9-16-05	
		CHECKED:		DATE:	
NorComp		SCALE: 1:1	SHEET 1 OF 1		REV 1
		DWG NO. 186-XXX-292LXX1			