

3kVrms DC/DC Converter

6 pin "Lead Free" Isolation Modules

HALO
ELECTRONICS, INC.



Product Features:

- Provides the isolation and voltage outputs required for low cost DC/DC converter circuits.
- Designed specifically for use with the Maxim™ MAX253, MAX845, and MAX3535 drivers.
- Isolation voltage is 3,000Vrms and working voltage up to 300V. Other packages are available with isolation voltages ranging from 500V to 5KVrms.
- UL60950, EN60950 and DEMKO recognized
- Temperature Range: -40 to +85°C

Part Number	Turns Ratio $\pm 3\%$ PRI : SEC	OCL (μH Typical)	PRI DCR (Ω Max)	PRI ET Constant (V- μs Min.)
TGMR-310V6LF	1CT:0.5CT	500	0.8	18
TGMR-320V6LF	1CT:0.375CT	500	0.8	18
TGMR-330V6LF	1CT:0.75CT	500	0.8	18
TGMR-340V6LF	1CT:1.33CT	800	0.9	22
TGMR-350V6LF	1CT:1CT	800	0.9	22
TGMR-355V6LF	1CT:1.5CT	800	0.9	22
TGMR-360V6LF	1CT:2CT	800	0.9	22
TGMR-370V6LF	1CT:1.6CT	800	0.9	22
TGMR-380V6LF	1CT:2.66CT	800	0.9	22


Notes:

Primary Pins are 1-3.

For more information, pertaining to the Maxim drivers please contact Maxim at (408) 737-7600.




Maxim is a registered trademark of Maxim Integrated Products.

Schematic




6 Pin, 3kVrms "Lead Free" DC/DC Converter Isolation Module

V6 Package



Dimensions: inches [mm]
Co-Planarity: 0.004 [0.10]



Recommended
Solder Pad Dimensions



2880 Lakeside Drive #116
Santa Clara, CA 95054
(650) 903-3800
www.halo-electronics.com

HALO® Electronics is a leading supplier of high quality communication magnetics including signal transformers, filters, CMR chokes, PoE power transformers, DC/DC converters, and integrated Ethernet connectors. HALO's leading edge technology solutions are manufactured in ISO9001 and ISO14001 factories offering high quality products at a competitive price.

3kVrms DC/DC Converter

6 pin SMD RoHS Compliant Isolation Modules

HALO
ELECTRONICS, INC.



Product Features:

- Provides the isolation and voltage outputs required for low cost DC/DC converter circuits.
- Designed specifically for use with the Maxim™ MAX253, MAX845, and MAX3535 drivers.
- Isolation voltage is 3,000Vrms. Other packages are available with isolation voltages ranging from 500Vrms to 5KVrms.
- UL60950, EN60950 recognized
- Temperature Range: -40 to +85°C

SMD Part Number	Turns Ratio $\pm 3\%$ PRI : SEC	PRI OCL (μH Typical)	PRI DCR (Ω Max.)	PRI ET Constant (V- μs Min.)
TGM-310NARL	1CT:0.5CT	570	0.8	11
TGM-320NARL	1CT:0.375CT	570	0.8	11
TGM-330NARL	1CT:0.75CT	570	0.8	11
TGM-340NARL	1CT:1.33CT	400	0.8	11
TGM-350NARL	1CT:1CT	400	0.8	11
TGM-360NARL	1CT:2CT	400	0.8	11
TGM-380NARL	1CT:2.66CT	400	0.5	11


Notes:

Primary Pins are 1-3.

For more information, pertaining to the Maxim drivers please contact Maxim at (408) 737-7600.


Maxim is a registered trademark of Maxim Integrated Products.

Schematic



6 Pin, 3kVrms RoHS Compliant DC/DC Converter Isolation Module

TGM-NA SMD Package



Dimensions: inches [mm]
Co-Planarity: 0.004 [0.10]

US Patent Numbers for SMD Devices
5,656,985 6,297,721 B1
6,297,720 B1 6,320,489 B1
6,344,785 B1 6,662,431 B1



2880 Lakeside Drive #116
Santa Clara, CA 95054
(650) 903-3800
www.haloelectronics.com

HALO® Electronics is a leading supplier of high quality communication magnetics including signal transformers, filters, CMR chokes, PoE power transformers, DC/DC converters, and integrated Ethernet connectors. HALO's leading edge technology solutions are manufactured in ISO9001 and ISO14001 factories offering high quality products at a competitive price.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HALO Electronics:

[TGMR-310V6LF](#) [TGMR-320V6LF](#) [TGMR-360V6LF](#) [TGMR-330V6LF](#) [TGMR-370V6LF](#) [TGMR-340V6LF](#) [TGMR-350V6LF](#) [TGMR-355V6LF](#) [TGMR-380V6LF](#) [TGMR-360V6LFTR](#) [TGMR-370V6LFTR](#) [TGMR-330V6LFTR](#) [TGMR-320V6LFTR](#) [TGMR-350V6LFTR](#) [TGMR-355V6LFTR](#) [TGMR-380V6LFTR](#) [TGMR-310V6LFTR](#) [TGMR-340V6LFTR](#) [TGM-360NARL](#) [TDM-340NARL](#) [TDM-330NARL](#) [TGM-380NARL](#) [TDM-320NARL](#) [TDM-360NARL](#) [TDM-380NARL](#) [TDM-310NARL](#) [TDM-350NARL](#) [TGMR-340NA5RL](#) [TGMR-310NA5RLTR](#) [TGMR-330NA5RLTR](#) [TGMR-350NA5RLTR](#) [TGMR-330NA5RL](#) [TGMR-310NA5RL](#) [TGMR-320NA5RL](#) [TGMR-320NA5RLTR](#) [TGMR-340NA5RLTR](#) [TGMR-350NA5RL](#)