



# TLV2544, TLV2548

## 2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

- Maximum Throughput 200-KSPS
- Built-In Reference, Conversion Clock and 8× FIFO
- Differential/Integral Nonlinearity Error:  $\pm 1$  LSB
- Signal-to-Noise and Distortion Ratio: 70 dB,  $f_i = 12$ -kHz
- Spurious Free Dynamic Range: 75 dB,  $f_i = 12$ -kHz
- SPI (CPOL = 0, CPHA = 0)/DSP-Compatible Serial Interfaces With SCLK up to 20-MHz
- Single Wide Range Supply 2.7 Vdc to 5.5 Vdc
- Analog Input Range 0-V to Supply Voltage With 500 kHz BW
- Hardware Controlled and Programmable Sampling Period
- Low Operating Current (1.0-mA at 3.3-V, 1.1-mA at 5.5-V With External Ref)
- Power Down: Software/Hardware Power-Down Mode (1  $\mu$ A Max, Ext Ref), Autopower-Down Mode (1  $\mu$ A, Ext Ref)
- Programmable Auto-Channel Sweep



### description

The TLV2548 and TLV2544 are a family of high performance, 12-bit low power, 3.86  $\mu$ s, CMOS analog-to-digital converters (ADC) which operate from a single 2.7-V to 5.5-V power supply. These devices have three digital inputs and a 3-state output [chip select ( $\overline{\text{CS}}$ ), serial input-output clock (SCLK), serial data input (SDI), and serial data output (SDO)] that provide a direct 4-wire interface to the serial port of most popular host microprocessors (SPI interface). When interfaced with a TI DSP, a frame sync (FS) signal is used to indicate the start of a serial data frame.

In addition to a high-speed A/D converter and versatile control capability, these devices have an on-chip analog multiplexer that can select any analog inputs or one of three internal self-test voltages. The sample-and-hold function is automatically started after the fourth SCLK edge (normal sampling) or can be controlled by a special pin, CSTART, to extend the sampling period (extended sampling). The normal sampling period can also be programmed as short (12 SCLKs) or as long (24 SCLKs) to accommodate faster SCLK operation popular among high-performance signal processors. The TLV2548 and TLV2544 are designed to operate with very low power consumption. The power-saving feature is further enhanced with software/hardware/autopower-down modes and programmable conversion speeds. The conversion clock (OSC) and reference are built-in. The converter can use the external SCLK as the source of the conversion clock to achieve higher (up to 2.8  $\mu$ s when a 20 MHz SCLK is used) conversion speed. Two different internal reference voltages are available. An optional external reference can also be used to achieve maximum flexibility.

The TLV2544C and the TLV2548C are characterized for operation from 0°C to 70°C. The TLV2544I and the TLV2548I are characterized for operation from –40°C to 85°C.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

**PRODUCTION DATA** information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1999 – 2003, Texas Instruments Incorporated  
On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.


TLV2544, TLV2548

2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER

SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

functional block diagram



| AVAILABLE OPTIONS |                  |              |             |               |             |              |
|-------------------|------------------|--------------|-------------|---------------|-------------|--------------|
| T <sub>A</sub>    | PACKAGED DEVICES |              |             |               |             |              |
|                   | 20-TSSOP (PW)    | 20-SOIC (DW) | 16-SOIC (D) | 16-TSSOP (PW) | 20-CDIP (J) | 20-LCCC (FK) |
| 0°C to 70°C       | TLV2548CPW       | TLV2548CDW   | TLV2544CD   | TLV2544CPW    | —           | —            |
| –40°C to 85°C     | TLV2548IPW       | TLV2548IDW   | TLV2544ID   | TLV2544IPW    | —           | —            |

**TLV2544, TLV2548**

**2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER  
SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

### Terminal Functions

| TERMINAL                                                 |                                                      |                                                      |   | I/O                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | DESCRIPTION |
|----------------------------------------------------------|------------------------------------------------------|------------------------------------------------------|---|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| NAME                                                     | NO.                                                  |                                                      |   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |             |
|                                                          | TLV2544                                              | TLV2548                                              |   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |             |
| A0 A0<br>A1 A1<br>A2 A2<br>A3 A3<br>A4<br>A5<br>A6<br>A7 | 6<br>7<br>8<br>9<br><br><br><br>10<br>11<br>12<br>13 | 6<br>7<br>8<br>9<br><br><br><br>10<br>11<br>12<br>13 | I | Analog signal inputs. The analog inputs are applied to these terminals and are internally multiplexed. The driving source impedance should be less than or equal to 1 kΩ.<br><br>For a source impedance greater than 1 kΩ, use the asynchronous conversion start signal $\overline{\text{CSTART}}$ ( $\overline{\text{CSTART}}$ low time controls the sampling period) or program long sampling period to increase the sampling time.                                                                                                                                                                                                                                                                                                                                                                                         |             |
| $\overline{\text{CS}}$                                   | 16                                                   | 20                                                   | I | Chip select. A high-to-low transition on the $\overline{\text{CS}}$ input resets the internal 4-bit counter, enables SDI, and removes SDO from 3-state within a maximum setup time. SDI is disabled within a setup time after the 4-bit counter counts to 16 (clock edges) or a low-to-high transition of $\overline{\text{CS}}$ whichever happens first.<br>NOTE: $\overline{\text{CS}}$ falling and rising edges need to happen when SCLK is low for a microprocessor interface such as SPI.                                                                                                                                                                                                                                                                                                                                |             |
| $\overline{\text{CSTART}}$                               | 10                                                   | 14                                                   | I | This terminal controls the start of sampling of the analog input from a selected multiplex channel. Sampling time starts with the falling edge of $\overline{\text{CSTART}}$ and ends with the rising edge of $\overline{\text{CSTART}}$ as long as $\overline{\text{CS}}$ is held high. In mode 01, select cycle, $\overline{\text{CSTART}}$ can be issued as soon as CHANNEL is selected which means the fifth SCLK during the select cycle, but the effective sampling time is not started until $\overline{\text{CS}}$ goes to high. The rising edge of $\overline{\text{CSTART}}$ (when $\overline{\text{CS}} = 1$ ) also starts the conversion. Tie this terminal to $\text{V}_{\text{CC}}$ if not used.                                                                                                                |             |
| $\text{EOC}/(\overline{\text{INT}})$                     | 4                                                    | 4                                                    | O | End of conversion or interrupt to host processor.<br>[PROGRAMMED AS EOC]: This output goes from a high-to-low logic level at the end of the sampling period and remains low until the conversion is complete and data are ready for transfer. EOC is used in conversion mode 00 only.<br><br>[PROGRAMMED AS $\overline{\text{INT}}$ ]: This pin can also be programmed as an interrupt output signal to the host processor. The falling edge of $\overline{\text{INT}}$ indicates data are ready for output. The following $\overline{\text{CS}}\downarrow$ or $\overline{\text{FS}}$ clears $\overline{\text{INT}}$ .                                                                                                                                                                                                        |             |
| FS                                                       | 13                                                   | 17                                                   | I | DSP frame sync input. Indication of the start of a serial data frame in or out of the device. If FS remains low after the falling edge of $\overline{\text{CS}}$ , SDI is not enabled until an active FS is presented. A high-to-low transition on the FS input resets the internal 4-bit counter and enables SDI within a maximum setup time. SDI is disabled within a setup time after the 4-bit counter counts to 16 (clock edges) or a low-to-high transition of $\overline{\text{CS}}$ whichever happens first.<br><br>Tie this terminal to $\text{V}_{\text{CC}}$ if not used. See the date code information section, item (1).                                                                                                                                                                                         |             |
| GND                                                      | 11                                                   | 15                                                   | I | Ground return for the internal circuitry. Unless otherwise noted, all voltage measurements are with respect to GND.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |             |
| $\overline{\text{PWDN}}$                                 | 12                                                   | 16                                                   | I | Both analog and reference circuits are powered down when this pin is at logic zero. The device can be restarted by active $\overline{\text{CS}}$ , $\overline{\text{FS}}$ or $\overline{\text{CSTART}}$ after this pin is pulled back to logic one.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |             |
| SCLK                                                     | 3                                                    | 3                                                    | I | Input serial clock. This terminal receives the serial SCLK from the host processor. SCLK is used to clock the input SDI to the input register. When programmed, it may also be used as the source of the conversion clock.<br><br>NOTE: This device supports CPOL (clock polarity) = 0, which is SCLK returns to zero when idling for SPI compatible interface.                                                                                                                                                                                                                                                                                                                                                                                                                                                               |             |
| SDI                                                      | 2                                                    | 2                                                    | I | Serial data input. The input data is presented with the MSB (D15) first. The first 4-bit MSBs, D(15–12) are decoded as one of the 16 commands (12 only for the TLV2544). The configure write commands require an additional 12 bits of data.<br>When FS is not used ( $\overline{\text{FS}} = 1$ ), the first MSB (D15) is expected after the falling edge of $\overline{\text{CS}}$ and is latched in on the rising edges of SCLK (after $\overline{\text{CS}}\downarrow$ ).<br>When FS is used (typical with an active FS from a DSP) the first MSB (D15) is expected after the falling edge of FS and is latched in on the falling edges of SCLK.<br>SDI is disabled within a setup time after the 4-bit counter counts to 16 (clock edges) or a low-to-high transition of $\overline{\text{CS}}$ whichever happens first. |             |



**TLV2544, TLV2548**  
**2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER**  
**SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

**Terminal Functions (Continued)**

| TERMINAL |         |         | I/O | DESCRIPTION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|----------|---------|---------|-----|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME     | NO.     |         |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|          | TLV2544 | TLV2548 |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| SDO      | 1       | 1       | O   | <p>The 3-state serial output for the A/D conversion result. SDO is kept in the high-impedance state when <math>\overline{CS}</math> is high and after the <math>\overline{CS}</math> falling edge and until the MSB is presented. The output format is MSB first.</p> <p>When <math>\overline{FS}</math> is not used (<math>FS = 1</math> at the falling edge of <math>\overline{CS}</math>), the MSB is presented to the SDO pin after the <math>\overline{CS}</math> falling edge, and successive data are available at the rising edge of SCLK and changed on the falling edge.</p> <p>When <math>FS</math> is used (<math>FS = 0</math> at the falling edge of <math>\overline{CS}</math>), the MSB is presented to SDO after the falling edge of <math>\overline{CS}</math> and <math>FS = 0</math> is detected. Successive data are available at the falling edge of SCLK and changed on the rising edge. (This is typically used with an active <math>FS</math> from a DSP.)</p> <p>For conversion and FIFO read cycles, the first 12 bits are result from previous conversion (data) followed by 4 don't care bits. The first four bits from SDO for CFR read cycles should be ignored. The register content is in the last 12 bits. SDO is 3-state (float) after the 16th bit. See the date code information section, item (2).</p> |
| REFM     | 14      | 18      | I   | External reference input or internal reference decoupling. Tie this pin to analog ground if internal reference is used.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| REFP     | 15      | 19      | I   | External reference input or internal reference decoupling. (Shunt capacitors of 10 $\mu F$ and 0.1 $\mu F$ between REFP and REFM.) The maximum input voltage range is determined by the difference between the voltage applied to this terminal and the REFM terminal when an external reference is used.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| VCC      | 5       | 5       | I   | Positive supply voltage                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |

**detailed description**

**analog inputs and internal test voltages**


The 4/8 analog inputs and three internal test inputs are selected by the analog multiplexer depending on the command entered. The input multiplexer is a break-before-make type to reduce input-to-input noise injection resulting from channel switching.

**converter**

The TLV2544/48 uses a 12-bit successive approximation ADC utilizing a charge redistribution DAC. Figure 1 shows a simplified version of the ADC.

The sampling capacitor acquires the signal on Ain during the sampling period. When the conversion process starts, the SAR control logic and charge redistribution DAC are used to add and subtract fixed amounts of charge from the sampling capacitor to bring the comparator into a balanced condition. When the comparator is balanced, the conversion is complete and the ADC output code is generated.

detailed description (continued)



**Figure 1. Simplified Model of the Successive-Approximation System**

serial interface

| INPUT DATA FORMAT |                                   |
|-------------------|-----------------------------------|
| MSB               | LSB                               |
| D15–D12           | D11–D0                            |
| Command ID[15:12] | Configuration data field ID[11:0] |

Input data is binary. All trailing blanks can be filled with zeros.

| OUTPUT DATA FORMAT READ CFR/FIFO READ |                                           |
|---------------------------------------|-------------------------------------------|
| MSB                                   | LSB                                       |
| D15–D12                               | D11–D0                                    |
| Don't care                            | Register content or FIFO content OD[11:0] |

| OUTPUT DATA FORMAT CONVERSION |            |
|-------------------------------|------------|
| MSB                           | LSB        |
| D15–D4                        | D3–D0      |
| Conversion result OD[11:0]    | Don't care |

The output data format is binary (unipolar straight binary).

**binary**

Zero scale code = 000h, Vcode = VREFM

Full scale code = FFFh, Vcode = VREFP – 1 LSB

# TLV2544, TLV2548

## 2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

### control and timing

#### power up and initialization requirements

- Determine processor type by writing A000h to the TLV2544/48 ( $\overline{CS}$  must be toggled)
- Configure the device ( $\overline{CS}$  must make a high-to-low transition, then can be held low if in DSP mode; i.e., active FS.)

The first conversion after power up or resuming from power down is not valid.

#### start of the cycle:

- When FS is not used (FS = 1 at the falling edge of  $\overline{CS}$ ), the falling edge of  $\overline{CS}$  is the start of the cycle.
- When FS is used (FS is an active signal from a DSP), the falling edge of FS is the start of the cycle.

#### first 4-MSBs: the command register (CMR)

The TLV2544/TLV2548 have a 4-bit command set (see Table 1) plus a 12-bit configuration data field. Most of the commands require only the first 4 MSBs, i.e., without the 12-bit data field.

The valid commands are listed in Table 1.

**Table 1. TLV2544/TLV2548 Command Set**

| SDI D(15–12) BINARY |              | TLV2548 COMMAND                                                                                                                 | TLV2544 COMMAND               |
|---------------------|--------------|---------------------------------------------------------------------------------------------------------------------------------|-------------------------------|
| 0000b               | 0h           | Select analog input channel 0                                                                                                   | Select analog input channel 0 |
| 0001b               | 1h           | Select analog input channel 1                                                                                                   | N/A                           |
| 0010b               | 2h           | Select analog input channel 2                                                                                                   | Select analog input channel 1 |
| 0011b               | 3h           | Select analog input channel 3                                                                                                   | N/A                           |
| 0100b               | 4h           | Select analog input channel 4                                                                                                   | Select analog input channel 2 |
| 0101b               | 5h           | Select analog input channel 5                                                                                                   | N/A                           |
| 0110b               | 6h           | Select analog input channel 6                                                                                                   | Select analog input channel 3 |
| 0111b               | 7h           | Select analog input channel 7                                                                                                   | N/A                           |
| 1000b               | 8h           | SW power down (analog + reference)                                                                                              |                               |
| 1001b               | 9h           | Read CFR register data shown as SDO D(11–0)                                                                                     |                               |
| 1010b               | Ah plus data | Write CFR followed by 12-bit data, e.g., 0A100h means external reference, short sampling, SCLK/4, single shot, $\overline{INT}$ |                               |
| 1011b               | Bh           | Select test, voltage = (REFP+REFM)/2                                                                                            |                               |
| 1100b               | Ch           | Select test, voltage = REFM                                                                                                     |                               |
| 1101b               | Dh           | Select test, voltage = REFP                                                                                                     |                               |
| 1110b               | Eh           | FIFO read, FIFO contents shown as SDO D(15–4), D(3–0) = 0000                                                                    |                               |
| 1111b               | Fh plus data | Reserved                                                                                                                        |                               |

NOTE: The status of the CFR can be read with a read CFR command when the device is programmed for one-shot conversion mode (CFR D[6,5] = 00).

**TLV2544, TLV2548**

**2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER  
SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

## control and timing (continued)

### configuration

Configuration data is stored in one 12-bit configuration register (CFR) (see Table 2 for CFR bit definitions). Once configured after first power up, the information is retained in the H/W or S/W power down state. When the device is being configured, a write CFR cycle is issued by the host processor. This is a 16-bit write. If the SCLK stops after the first 8 bits are entered, then the next eight bits can be taken after the SCLK is resumed.

**Table 2. TLV2544/TLV2548 Configuration Register (CFR) Bit Definitions**

| BIT                 | DEFINITION                                                                                                                                                                                                                                                                                                                                          |                                                                                                            |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------|
| D11                 | Reference select<br>0: External<br>1: Internal (Tie REFM to analog ground if the Internal reference is selected.)                                                                                                                                                                                                                                   |                                                                                                            |
| D10                 | Internal reference voltage select<br>0: Internal ref = 4 V<br>1: internal ref = 2 V                                                                                                                                                                                                                                                                 |                                                                                                            |
| D9                  | Sample period select<br>0: Short sampling 12 SCLKs (1x sampling time)<br>1: Long sampling 24 SCLKs (2x sampling time)                                                                                                                                                                                                                               |                                                                                                            |
| D(8,7)              | Conversion clock source select<br>00: Conversion clock = internal OSC<br>01: Conversion clock = SCLK<br>10: Conversion clock = SCLK/4<br>11: Conversion clock = SCLK/2                                                                                                                                                                              |                                                                                                            |
| D(6,5)              | Conversion mode select<br>00: Single shot mode [FIFO not used, D(1,0) has no effect.]<br>01: Repeat mode<br>10: Sweep mode<br>11: Repeat sweep mode                                                                                                                                                                                                 |                                                                                                            |
| D(4,3) <sup>†</sup> | <b>TLV2548</b>                                                                                                                                                                                                                                                                                                                                      | <b>TLV2544</b>                                                                                             |
|                     | Sweep auto sequence select<br>00: 0-1-2-3-4-5-6-7<br>01: 0-2-4-6-0-2-4-6<br>10: 0-0-2-2-4-4-6-6<br>11: 0-2-0-2-0-2-0-2                                                                                                                                                                                                                              | Sweep auto sequence select<br>00: N/A<br>01: 0-1-2-3-0-1-2-3<br>10: 0-0-1-1-2-2-3-3<br>11: 0-1-0-1-0-1-0-1 |
| D2                  | EOC/ $\overline{\text{INT}}$ – pin function select<br>0: Pin used as $\overline{\text{INT}}$<br>1: Pin used as EOC                                                                                                                                                                                                                                  |                                                                                                            |
| D(1,0)              | FIFO trigger level (sweep sequence length)<br>00: Full ( $\overline{\text{INT}}$ generated after FIFO level 7 filled)<br>01: 3/4 ( $\overline{\text{INT}}$ generated after FIFO level 5 filled)<br>10: 1/2 ( $\overline{\text{INT}}$ generated after FIFO level 3 filled)<br>11: 1/4 ( $\overline{\text{INT}}$ generated after FIFO level 1 filled) |                                                                                                            |

<sup>†</sup> These bits only take effect in conversion modes 10 and 11.

### sampling

The sampling period starts after the first 4 input data are shifted in if they are decoded as one of the conversion commands. These are select analog input (channel 0 through 7) and select test (channel 1 through 3).



# TLV2544, TLV2548

## 2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

### normal sampling

When the converter is using normal sampling, the sampling period is programmable. It can be 12 SCLKs (short sampling) or 24 SCLKs (long sampling). Long sampling helps when SCLK is faster than 10 MHz or when input source resistance is high.

### extended sampling

**CSTART** – An asynchronous (to the SCLK) signal, via dedicated hardware pin, **CSTART**, can be used in order to have total control of the sampling period and the start of a conversion. This extended sampling is user-defined and is totally independent of SCLK. While **CS** is high, the falling edge of **CSTART** is the start of the sampling period and is controlled by the low time of **CSTART**. The minimum low time for **CSTART** should be at least equal to the minimum  $t_{\text{SAMPLE}}$ . In a select cycle used in mode 01 (REPEAT MODE), **CSTART** can be started as soon as the channel is selected (after the fifth SCLK). In this case the sampling period is not started until **CS** has become inactive. Therefore the nonoverlapped **CSTART** low time must meet the minimum sampling time requirement. The low-to-high transition of **CSTART** terminates the sampling period and starts the conversion period. The conversion clock can also be configured to use either internal OSC or external SCLK. This function is useful for an application that requires:

- The use of an extended sampling period to accommodate different input source impedance
- The use of a faster I/O clock on the serial port but not enough sampling time is available due to the fixed number of SCLKs. This could be due to a high input source impedance or due to higher MUX ON resistance at lower supply voltage.

Once the conversion is complete, the processor can initiate a read cycle by using either the read FIFO command to read the conversion result or by simply selecting the next channel number for conversion. Since the device has a valid conversion result in the output buffer, the conversion result is simply presented at the serial data output. To completely get out of the extended sampling mode, **CS** must be toggled twice from a high-to-low transition while **CSTART** is high. The read cycle mentioned above followed by another configuration cycle of the ADC qualifies this condition and successfully puts the ADC back to its normal sampling mode. This can be viewed in Figure 9.

**Table 3. Sample and Convert Conditions**

|               | CONDITIONS                               | SAMPLE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | CONVERT                                                                                                                                                                                                                                           |
|---------------|------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>CSTART</b> | <b>CS</b> = 1<br>(see Figures 11 and 18) | <b>No sampling clock (SCLK) required.</b> Sampling period is totally controlled by the low time of <b>CSTART</b> . The high-to-low transition of <b>CSTART</b> (when <b>CS</b> =1) starts the sampling of the analog input signal. The low time of <b>CSTART</b> dictates the sampling period. The low-to-high transition of <b>CSTART</b> ends sampling period and begins the conversion cycle. (Note: this trigger only works when internal reference is selected for conversion modes 01, 10, and 11.)                                                                                                                                                      |                                                                                                                                                                                                                                                   |
| <b>CS</b>     | <b>CSTART</b> = 1<br><b>FS</b> = 1       | <b>SCLK is required.</b> Sampling period is programmable under normal sampling. When programmed to sample under short sampling, 12 SCLKs are generated to complete sampling period. 24 SCLKs are generated when programmed for long sampling. A command set to configure the device requires 4 SCLKs thereby extending to 16 or 28 SCLKs respectively before conversion takes place. (Note: Because the ADC only bypasses a valid channel select command, the user can use <i>select channel 0, 0000b</i> , as the SDI input when either <b>CS</b> or <b>FS</b> is used as trigger for conversion. The ADC responds to commands such as SW power-down, 1000b.) | 1) If the internal clock OSC is selected a maximum conversion time of 3.86 $\mu$ s can be achieved.<br>2) If external SCLK is selected, conversion time is $t_{\text{conv}} = 14 \times \text{DIV}/f(\text{SCLK})$ , where DIV can be 1, 2, or 4. |
| <b>FS</b>     | <b>CSTART</b> = 1<br><b>CS</b> = 0       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                                                                                                                                                                                                                                                   |

## TLV2544/TLV2548 conversion modes

The TLV2544 and TLV2548 have four different conversion modes (mode 00, 01, 10, 11). The operation of each mode is slightly different, depending on how the converter performs the sampling and which host interface is used. The trigger for a conversion can be an active  $\overline{\text{CSTART}}$  (extended sampling),  $\overline{\text{CS}}$  (normal sampling, SPI interface), or FS (normal sampling, TMS320 DSP interface). When FS is used as the trigger,  $\overline{\text{CS}}$  can be held active, i.e.  $\overline{\text{CS}}$  does not need to be toggled through the trigger sequence. SDI can be one of the channel select commands, such as SELECT CHANNEL 0. Different types of triggers should not be mixed throughout the repeat and sweep operations. When  $\overline{\text{CSTART}}$  is used as the trigger, the conversion starts on the rising edge of  $\overline{\text{CSTART}}$ . The minimum low time for  $\overline{\text{CSTART}}$  is equal to  $t_{\text{SAMPLE}}$ . If an active  $\overline{\text{CS}}$  or FS is used as the trigger, the conversion is started after the 16th or 28th SCLK edge. Enough time (for conversion) should be allowed between consecutive triggers so that no conversion is terminated prematurely.

### one shot mode (mode 00)

One shot mode (mode 00) does not use the FIFO, and the EOC is generated as the conversion is in progress (or  $\overline{\text{INT}}$  is generated after the conversion is done).

### repeat mode (mode 01)

Repeat mode (mode 01) uses the FIFO. This mode setup requires configuration cycle and channel select cycle. Once the programmed FIFO threshold is reached, the FIFO must be read, or the data is lost when the sequence starts over again with the SELECT cycle and series of triggers. No configuration is required except for reselecting the channel unless the operation mode is changed. This allows the host to set up the converter and continue monitoring a fixed input and come back to get a set of samples when preferred.

Triggered by  $\overline{\text{CSTART}}$ : The first conversion can be started with a select cycle or  $\overline{\text{CSTART}}$ . To do so, the user can issue  $\overline{\text{CSTART}}$  during the select cycle, immediately after the four-bit channel select command. The first sample started as soon as the select cycle is finished (i.e.,  $\overline{\text{CS}}$  returns to 1). If there is enough time (2  $\mu\text{s}$ ) left between the SELECT cycle and the following  $\overline{\text{CSTART}}$ , a conversion is carried out. In this case, you need one less trigger to fill the FIFO. Succeeding samples are triggered by  $\overline{\text{CSTART}}$ .

### sweep mode (mode 10)

Sweep mode (mode 10) also uses the FIFO. Once it is programmed in this mode, all of the channels listed in the selected sweep sequence are visited in sequence. The results are converted and stored in the FIFO. This sweep sequence may not be completed if the FIFO threshold is reached before the list is completed. This allows the system designer to change the sweep sequence length. Once the FIFO has reached its programmed threshold, an interrupt ( $\overline{\text{INT}}$ ) is generated. The host must issue a read FIFO command to read and clear the FIFO before the next sweep can start.

### repeat sweep mode (mode 11)

Repeat sweep mode (mode 11) works the same way as mode 10 except the operation has an option to continue even if the FIFO threshold is reached. Once the FIFO has reached its programmed threshold, an interrupt ( $\overline{\text{INT}}$ ) is generated. Then two things may happen:

1. The host may choose to act on it (read the FIFO) or ignore it. If the next cycle is a read FIFO cycle, all of the data stored in the FIFO is retained until it has been read in order.
2. If the next cycle is not a read FIFO cycle, or another  $\overline{\text{CSTART}}$  is generated, all of the content stored in the FIFO is cleared before the next conversion result is stored in the FIFO, and the sweep is continued.

## TLV2544/TLV2548 conversion modes (continued)

Table 4. TLV2544/TLV2548 Conversion Mode

| CONVERSION MODE | CFR D(6,5) | SAMPLING TYPE | OPERATION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-----------------|------------|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| One shot        | 00         | Normal        | <ul style="list-style-type: none"> <li>Single conversion from a selected channel</li> <li><math>\overline{CS}</math> or <math>\overline{FS}</math> to start select/sampling/conversion/read</li> <li>One <math>\overline{INT}</math> or <math>\overline{EOC}</math> generated after each conversion</li> <li>Host must serve <math>\overline{INT}</math> by selecting channel, and converting and reading the previous output.</li> </ul>                                                                                                                                                                                                      |
|                 |            | Extended      | <ul style="list-style-type: none"> <li>Single conversion from a selected channel</li> <li><math>\overline{CS}</math> to select/read</li> <li><math>\overline{CSTART}</math> to start sampling and conversion</li> <li>One <math>\overline{INT}</math> or <math>\overline{EOC}</math> generated after each conversion</li> <li>Host must serve <math>\overline{INT}</math> by selecting next channel and reading the previous output.</li> </ul>                                                                                                                                                                                                |
| Repeat          | 01         | Normal        | <ul style="list-style-type: none"> <li>Repeated conversions from a selected channel</li> <li><math>\overline{CS}</math> or <math>\overline{FS}</math> to start sampling/conversion</li> <li>One <math>\overline{INT}</math> generated after FIFO is filled up to the threshold</li> <li>Host must serve <math>\overline{INT}</math> by either 1) (FIFO read) reading out all of the FIFO contents up to the threshold, then repeat conversions from the same selected channel or 2) writing another command(s) to change the conversion mode. If the FIFO is not read when <math>\overline{INT}</math> is served, it is cleared.</li> </ul>    |
|                 |            | Extended      | <ul style="list-style-type: none"> <li>Same as normal sampling except <math>\overline{CSTART}</math> starts each sampling and conversion when <math>\overline{CS}</math> is high.</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Sweep           | 10         | Normal        | <ul style="list-style-type: none"> <li>One conversion per channel from a sequence of channels</li> <li><math>\overline{CS}</math> or <math>\overline{FS}</math> to start sampling/conversion</li> <li>One <math>\overline{INT}</math> generated after FIFO is filled up to the threshold</li> <li>Host must serve <math>\overline{INT}</math> by (FIFO read) reading out all of the FIFO contents up to the threshold, then write another command(s) to change the conversion mode.</li> </ul>                                                                                                                                                 |
|                 |            | Extended      | <ul style="list-style-type: none"> <li>Same as normal sampling except <math>\overline{CSTART}</math> starts each sampling and conversion when <math>\overline{CS}</math> is high.</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Repeat sweep    | 11         | Normal        | <ul style="list-style-type: none"> <li>Repeated conversions from a sequence of channels</li> <li><math>\overline{CS}</math> or <math>\overline{FS}</math> to start sampling/conversion</li> <li>One <math>\overline{INT}</math> generated after FIFO is filled up to the threshold</li> <li>Host must serve <math>\overline{INT}</math> by either 1) (FIFO read) reading out all of the FIFO contents up to the threshold, then repeat conversions from the same selected channel or 2) writing another command(s) to change the conversion mode. If the FIFO is not read when <math>\overline{INT}</math> is served it is cleared.</li> </ul> |
|                 |            | Extended      | <ul style="list-style-type: none"> <li>Same as normal sampling except <math>\overline{CSTART}</math> starts each sampling and conversion when <math>\overline{CS}</math> is high.</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                   |

- NOTES: 1. Programming the  $\overline{EOC}/\overline{INT}$  pin as the  $\overline{EOC}$  signal works for mode 00 only. The other three modes automatically generate an  $\overline{INT}$  signal irrespective of how  $\overline{EOC}/\overline{INT}$  is programmed.
2. Extended. Sampling mode using  $\overline{CSTART}$  as the trigger only works when internal reference is selected for conversion modes 01, 10, and 11.
3. When using  $\overline{CSTART}$  to sample in extended mode, the falling edge of the next  $\overline{CSTART}$  trigger should occur no more than 2.5  $\mu$ s after the falling  $\overline{CS}$  edge (or falling  $\overline{FS}$  edge if  $\overline{FS}$  is active) of the channel select cycle. This is to prevent an ongoing conversion from being canceled.

## timing diagrams

The timing diagrams can be categorized into two major groups: nonconversion and conversion. The nonconversion cycles are read and write (configuration). None of these cycles carry a conversion. Conversion cycles are those four modes of conversion.

### read cycle (read FIFO or read CFR)

#### read CFR cycle:

The read command is decoded in the first 4 clocks. SDO outputs the contents of the CFR after the 4th SCLK. This command works only when the device is programmed in the *single shot* mode (mode 00).




Figure 2. TLV2544/TLV2548 Read CFR Cycle (FS active)





Figure 3. TLV2544/TLV2548 Read CFR Cycle (FS = 1)

read cycle (read FIFO or read CFR) (continued)

**FIFO read cycle**

The first command in the active cycle after  $\overline{\text{INT}}$  is generated, if the FIFO is used, is assumed as the FIFO read command. The first FIFO content is output immediately before the command is decoded. If this command is not a FIFO read, then the output is terminated but the first data in the FIFO is retained until a valid FIFO read command is decoded. Use of more layers of the FIFO reduces the time taken to read multiple data. This is because the read cycle does not generate EOC or  $\overline{\text{INT}}$ , nor does it carry out any conversion.



These devices can perform continuous FIFO read cycles ( $\text{FS} = 1$ ) controlled by SCLK; SCLK can stop between each 16 SCLKs.

**Figure 4. TLV2544/TLV2548 FIFO Read Cycle ( $\text{FS} = 1$ )**

### write cycle (write CFR)

The write cycle is used to write to the configuration register CFR (with 12-bit register content). The write cycle does not generate an EOC or  $\overline{\text{INT}}$ , nor does it carry out any conversion (see power up and initialization requirements).




Figure 5. TLV2544/TLV2548 Write Cycle (FS Active)




Figure 6. TLV2544/TLV2548 Write Cycle (FS = 1)

# TLV2544, TLV2548

## 2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

### conversion cycles

#### DSP/normal sampling




Figure 7. Mode 00 Single Shot/Normal Sampling (FS Signal Used)





Figure 8. Mode 00 Single Shot/Normal Sampling (FS = 1, FS Signal not Used)


**conversion cycles (continued)**



† This is one of the single shot commands. Conversion starts on next rising edge of  $\overline{\text{CSTART}}$ .

**Figure 9. Mode 00 Single Shot/Extended Sampling (FS Signal Used, FS Pin Connected to TMS320 DSP)**

**modes using the FIFO: modes 01, 10, 11 timing**



† Command = Configure write for mode 01, FIFO threshold = 1/2

‡ Command = Read FIFO, first FIFO read

§ Command = Select ch2.

¶ Use any channel select command to trigger SDI input.


**Figure 10. TLV2544/TLV2548 Mode 01 DSP Serial Interface (Conversions Triggered by FS)**

# TLV2544, TLV2548

## 2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

### modes using the FIFO: modes 01, 10, 11 timing (continued)




† Command = Configure write for mode 01, FIFO threshold = 1/2

‡ Command = Read FIFO, first FIFO read

§ Command = Select ch2.

¶ Minimum  $\overline{\text{CS}}$  low time for select cycle is 6 SCLKs. The same amount of time is required between FS low to  $\overline{\text{CSTART}}$  for proper channel decoding. The low time of CSTART, not overlapped with  $\overline{\text{CS}}$  low time, is the valid sampling time for the select cycle (see Figure 18).

**Figure 11. TLV2544/TLV2548 Mode 01  $\mu\text{p/DSP}$  Serial Interface (Conversions Triggered by  $\overline{\text{CSTART}}$ )**



† Command = Configure write for mode 10 or 11, FIFO threshold = 1/2, sweep seq = 0–1–2–3.

‡ Command = Read FIFO


§ Use any channel select command to trigger SDI input.

**Figure 12. TLV2544/TLV2548 Mode 10/11 DSP Serial Interface (Conversions Triggered by FS)**

**TLV2544, TLV2548**  
**2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER**  
**SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003


modes using the FIFO: modes 01, 10, 11 timing (continued)



† Command = Configure write for mode 10 or 11, FIFO threshold = 1/2, sweep seq = 0–1–2–3.

‡ Command = Read FIFO

**Figure 13. TLV2544/TLV2548 Mode 10/11 DSP Serial Interface (Conversions Triggered by CSTART)**




† Command = Configure write for mode 10 or 11, FIFO threshold = 1/2, sweep seq = 0–1–2–3.

‡ Command = Read FIFO

§ Use any channel select command to trigger SDI input.

**Figure 14. TLV2544/TLV2548 Mode 10/11 μp Serial Interface (Conversions Triggered by CS)**

## FIFO operation



**Figure 15. TLV2544/TLV2548 FIFO**

The device has an 8-layer FIFO that can be programmed for different thresholds. An interrupt is sent to the host after the preprogrammed threshold is reached. The FIFO can be used to store data from either a fixed channel or a series of channels based on a preprogrammed sweep sequence. For example, an application may require eight measurements from channel 3. In this case, the FIFO is filled with eight data sequentially taken from channel 3. Another application may require data from channel 0, channel 2, channel 4, and channel 6 in an orderly manner. Therefore, the threshold is set for 1/2 and the sweep sequence 0–2–4–6–0–2–4–6 is chosen. An interrupt is sent to the host as soon as all four data are in the FIFO.

In single shot mode, the FIFO automatically uses a 1/8 FIFO depth. Therefore the CFR bits (D1,0) controlling FIFO depth are *don't care*.

## SCLK and conversion speed

There are two ways to adjust the conversion speed.

- The SCLK can be used as the source of the conversion clock to get the highest throughput of the device.


The minimum onboard OSC is 3.6 MHz and 14 conversion clocks are required to complete a conversion. (Corresponding 3.86  $\mu$ s conversion time) The devices can operate with an SCLK up to 20 MHz for the supply voltage range specified. When a more accurate conversion time is desired, the SCLK can be used as the source of the conversion clock. The clock divider provides speed options appropriate for an application where a high speed SCLK is used for faster I/O. The total conversion time is  $14 \times (\text{DIV}/f_{\text{SCLK}})$  where DIV is 1, 2, or 4. For example a 20 MHz SCLK with the divide by 4 option produces a  $\{14 \times (4/20 \text{ M})\} = 2.8 \mu$ s conversion time. When an external serial clock (SCLK) is used as the source of the conversion clock, the maximum equivalent conversion clock ( $f_{\text{SCLK}}/\text{DIV}$ ) should not exceed 6 MHz.

- Autopower down can be used to slow down the device at a reduced power consumption level. This mode is always used by the converter. If the device is not accessed (by  $\overline{\text{CS}}$  or  $\overline{\text{CSTART}}$ ), the converter is powered down to save power. The built-in reference is left on in order to quickly resume operation within one half SCLK period. This provides unlimited choices to trade speed with power savings.

## reference voltage

The device has a built-in reference with a programmable level of 2 V or 4 V. If the internal reference is used, REFP is set to 2 V or 4 V and REFM should be connected to the analog ground of the converter. An external reference can also be used through two reference input pins, REFP and REFM, if the reference source is programmed as external. The voltage levels applied to these pins establish the upper and lower limits of the analog inputs to produce a full-scale and zero-scale reading respectively. The values of REFP, REFM, and the analog input should not exceed the positive supply or be lower than GND consistent with the specified absolute maximum ratings. The digital output is at full scale when the input signal is equal to or higher than REFP and at zero when the input signal is equal to or lower than REFM.

### reference block equivalent circuit



- NOTES:
- A. If internal reference is used, tie REFM to analog ground and install a 10  $\mu$ F (or 4.7  $\mu$ F) internal reference compensation capacitor between REFP and REFM to store the charge as shown in the figure above.
  - B. If external reference is used, the 10  $\mu$ F (internal reference compensation) capacitor is optional. REFM can be connected to external REFM or AGND.
  - C. Internal reference voltage drift, due to temperature variations, is approximately  $\pm 10$  mV about the nominal 2 V (typically) from  $-10^{\circ}\text{C}$  to  $100^{\circ}\text{C}$ . The nominal value also varies approximately  $\pm 50$  mV across devices.
  - D. Internal reference leakage during low ON time: Leakage resistance is on the order of 100 M $\Omega$  or more. This means the time constant is about 1000 s with 10  $\mu$ F compensation capacitance. Since the REF voltage does not vary much, the reference comes up quickly after resuming from auto power down. At power up and power down the internal reference sees a glitch of about 500  $\mu$ V when 2 V internal reference is used (1 mV when 4 V internal reference is used). This glitch settles out after about 50  $\mu$ s.

### power down

The device has three power-down modes.

#### autopower-down mode

The device enters the autopower-down state at the end of a conversion.

In autopower-down, the power consumption reduces to about 1 mA when an internal reference is selected. The built-in reference is still on to allow the device to resume quickly. The resumption is fast enough (within 0.5 SCLK) for use between cycles. An active  $\overline{\text{CS}}$ , FS, or  $\overline{\text{CSTART}}$  resumes the device from power-down state. The power current is 1  $\mu$ A when an external reference is programmed and SCLK stops.

#### hardware/software power-down mode

Writing 8000h to the device puts the device into a software power down state, and the entire chip (including the built-in reference) is powered down. For a hardware power-down, the dedicated  $\overline{\text{PWDN}}$  pin provides another way to power down the device asynchronously. These two power-down modes power down the entire device including the built-in reference to save power. The power down current is reduced to about 1  $\mu$ A as the SCLK is stopped.

An active  $\overline{\text{CS}}$ , FS, or  $\overline{\text{CSTART}}$  restores the device. There is no time delay when an external reference is selected. However, if an internal reference is used, it takes about 20 ms to warm up. Deselect  $\overline{\text{PWDN}}$  pin to remove the device from the hardware power-down state. This requires about 20 ms to warm up if an internal reference is also selected.

The configuration register is not affected by any of the power down modes but the sweep operation sequence has to be started over again. All FIFO contents are cleared by the power-down modes.

**TLV2544, TLV2548****2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER  
SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

**absolute maximum ratings over operating free-air temperature (unless otherwise noted)<sup>†</sup>**

|                                                              |                            |
|--------------------------------------------------------------|----------------------------|
| Supply voltage range, GND to $V_{CC}$                        | –0.3 V to 6.5 V            |
| Analog input voltage range                                   | –0.3 V to $V_{CC} + 0.3$ V |
| Reference input voltage                                      | $V_{CC} + 0.3$ V           |
| Digital input voltage range                                  | –0.3 V to $V_{CC} + 0.3$ V |
| Operating virtual junction temperature range, $T_J$          | –55°C to 150°C             |
| Operating free-air temperature range, $T_A$ : TLV2544/48C    | 0°C to 70°C                |
| TLV2544/48I                                                  | –40°C to 85°C              |
| Storage temperature range, $T_{stg}$                         | –65°C to 150°C             |
| Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds | 260°C                      |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

**DISSIPATION RATING TABLE**

| PACKAGE | $T_A \leq 25^\circ\text{C}$<br>POWER RATING | DERATING FACTOR<br>ABOVE $T_A = 25^\circ\text{C}$ <sup>‡</sup> | $T_A = 70^\circ\text{C}$<br>POWER RATING | $T_A = 85^\circ\text{C}$<br>POWER RATING | $T_A = 125^\circ\text{C}$<br>POWER RATING |
|---------|---------------------------------------------|----------------------------------------------------------------|------------------------------------------|------------------------------------------|-------------------------------------------|
| D       | 1110 mW                                     | 8.9 mW/°C                                                      | 710 mW                                   | 577 mW                                   | 222 mW                                    |
| DW      | 1294 mW                                     | 10.4 mW/°C                                                     | 828 mW                                   | 673 mW                                   | 259 mW                                    |
| 16 PW   | 839 mW                                      | 6.7 mW/°C                                                      | 537 mW                                   | 437 mW                                   | —                                         |
| 20 PW   | 977 mW                                      | 7.8 mW/°C                                                      | 625 mW                                   | 508 mW                                   | —                                         |

<sup>‡</sup> This is the inverse of the traditional junction-to-ambient thermal resistance ( $R_{\theta JA}$ ). Thermal resistance is not production tested and the values given are for informational purposes only.

**recommended operating conditions**

|                                                                                                                                                                      | MIN                                        | NOM | MAX      | UNIT  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------|-----|----------|-------|
| Supply voltage, $V_{CC}$                                                                                                                                             | 2.7                                        | 3.3 | 5.5      | V     |
| Analog input voltage (see Note 4)                                                                                                                                    | 0                                          |     | $V_{CC}$ | V     |
| High level control input voltage, $V_{IH}$                                                                                                                           | 2.1                                        |     |          | V     |
| Low-level control input voltage, $V_{IL}$                                                                                                                            |                                            |     | 0.6      | V     |
| Delay time, delay from CS falling edge to FS rising edge, $t_d(\text{CSL-FSH})$<br>(See Figure 16)                                                                   | 0.5                                        |     |          | SCLKs |
| Delay time, delay time from 16th SCLK falling edge to CS rising edge (FS = 1), or<br>17th rising edge (FS is active) $t_d(\text{SCLK-CSH})$ (See Figures 16, and 19) | 0.5                                        |     |          | SCLKs |
| Setup time, FS rising edge before SCLK falling edge, $t_{su}(\text{FSH-SCLKL})$<br>(See Figure 16)                                                                   | 20                                         |     |          | ns    |
| Hold time, FS hold high after SCLK falling edge, $t_h(\text{FSH-SCLKL})$ (See Figure 16)                                                                             | 30                                         |     |          | ns    |
| Pulse width, CS high time, $t_{WH}(\text{CS})$ (See Figures 16 and 19)                                                                                               | 100                                        |     |          | ns    |
| Pulse width, FS high time, $t_{WH}(\text{FS})$ (See Figure 16)                                                                                                       | 0.75                                       |     | 1        | SCLKs |
| SCLK cycle time, $t_c(\text{SCLK})$<br>(See Figures 16, and 19)                                                                                                      | $V_{CC} = 2.7 \text{ V to } 3.6 \text{ V}$ |     | 75       | ns    |
|                                                                                                                                                                      | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$ |     | 10000    |       |

NOTE 4: When binary output format is used, analog input voltages greater than that applied to REFP convert as all ones (111111111111), while input voltages less than that applied to REFM convert as all zeros (000000000000). The device is functional with reference down to 1 V. ( $V_{REFP} - V_{REFM} - 1$ ); however, the electrical specifications are no longer applicable.



**TLV2544, TLV2548**

**2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER  
SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

**recommended operating conditions (continued)**

|                                                                                                                                                                                                                     |                   |             | MIN                | NOM | MAX           | UNIT        |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|-------------|--------------------|-----|---------------|-------------|
| Pulse width, SCLK low time, $t_{WL}(SCLK)$ (See Figures 16 and 19)                                                                                                                                                  |                   |             | 0.4                |     | 0.6           | SCLKs       |
| Pulse width, SCLK high time, $t_{WH}(SCLK)$ (See Figures 16 and 19)                                                                                                                                                 |                   |             | 0.4                |     | 0.6           | SCLKs       |
| Setup time, SDI valid before falling edge of SCLK (FS is active) or the rising edge of SCLK (FS=1), $t_{su}(DI-SCLK)$ (See Figures 16 and 19)                                                                       |                   |             | 25                 |     |               | ns          |
| Hold time, SDI hold valid after falling edge of SCLK (FS is active) or the rising edge of SCLK (FS=1), $t_h(DI-SCLK)$ (See Figure 16)                                                                               |                   |             | 5                  |     |               | ns          |
| Delay time, delay from CS falling edge to SDO valid, $t_d(CSL-DOV)$ (See Figures 16 and 19)                                                                                                                         |                   |             |                    |     | 25            | ns          |
| Delay time, delay from FS falling edge to SDO valid, $t_d(FSL-DOV)$ (See Figure 16)                                                                                                                                 |                   |             |                    |     | 25            | ns          |
| Delay time, delay from SCLK falling edge (FS is active) or SCLK rising edge (FS=1) to SDO valid, $t_d(SCLK-DOV)$ . (See Figures 16 and 19). For a date code later than xxx, see the date code information item (3). | VCC = 4.5 V       | SDO = 5 pF  | 0.5 SCLK           |     | 0.5 SCLK + 9  | ns          |
|                                                                                                                                                                                                                     |                   | SDO = 25 pF | 0.5 SCLK           |     | 0.5 SCLK + 10 |             |
|                                                                                                                                                                                                                     | VCC = 2.7 V       | SDO = 5 pF  | 0.5 SCLK           |     | 0.5 SCLK + 18 |             |
|                                                                                                                                                                                                                     |                   | SDO = 25 pF | 0.5 SCLK           |     | 0.5 SCLK + 19 |             |
| Delay time, delay from 17th SCLK rising edge (FS is active) or the 16th falling edge (FS=1) to EOC falling edge, $t_d(SCLK-EOCL)$ (See Figures 16 and 19)                                                           |                   |             | 45                 |     |               | ns          |
| Delay time, delay from 16th <u>SCLK</u> falling edge to <u>INT</u> falling edge (FS =1) <u>or</u> from the 17th rising edge SCLK to INT falling edge (when FS active), $t_d(SCLK-INTL)$ (See Figure 19)             |                   |             | Min $t_{(conv)}$   |     |               | $\mu s$     |
| Delay time, delay from CS falling edge or FS rising edge to INT rising edge, $t_d(CSL-INTH)$ or $t_d(FSH-INTH)$ . See Figures 16, 17, 18 and 19)                                                                    |                   |             | 1                  |     | 50            | ns          |
| Delay time, delay from CS rising edge to <u>CSTART</u> falling edge, $t_d(CSH-CSTARTL)$ (See Figures 17 and 18)                                                                                                     |                   |             | 100                |     |               | ns          |
| Delay time, delay from CSTART rising edge to EOC falling edge, $t_d(CSTARTH-EOCL)$ (See Figures 17 and 18)                                                                                                          |                   |             | 1                  |     | 50            | ns          |
| Pulse width, <u>CSTART</u> low time, $t_{WL}(\overline{CSTART})$ (See Figures 17 and 18)                                                                                                                            |                   |             | Min $t_{(sample)}$ |     |               | $\mu s$     |
| Delay time, delay from <u>CSTART</u> rising edge to <u>CSTART</u> falling edge, $t_d(CSTARTH-CSTARTL)$ (See Figure 18)                                                                                              |                   |             | Max $t_{(conv)}$   |     |               | $\mu s$     |
| Delay time, delay from <u>CSTART</u> rising edge to <u>INT</u> falling edge, $t_d(CSTARTH-INTL)$ (See Figures 17 and 18)                                                                                            |                   |             | Max $t_{(conv)}$   |     |               | $\mu s$     |
| Operating free-air temperature, $T_A$                                                                                                                                                                               | TLV2544C/TLV2548C |             | 0                  |     | 70            | $^{\circ}C$ |
|                                                                                                                                                                                                                     | TLV2544I/TLV2548I |             | -40                |     | 85            |             |

electrical characteristics over recommended operating free-air temperature range,  $V_{CC} = V_{REFP} = 2.7\text{ V}$  to  $5.5\text{ V}$ ,  $V_{REFM} = 0\text{ V}$ , SCLK frequency = 20 MHz at 5 V, 15 MHz at 3 V (unless otherwise noted)

| PARAMETER                 |                                                                                                                                    | TEST CONDITIONS                                                      |                                          | MIN              | TYP <sup>†</sup> | MAX                  | UNIT |
|---------------------------|------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------|------------------------------------------|------------------|------------------|----------------------|------|
| V <sub>OH</sub>           | High-level output voltage                                                                                                          | V <sub>CC</sub> = 5.5 V, I <sub>OH</sub> = −0.2 mA at 25 pF load     |                                          | 2.4              |                  | V <sub>CC</sub> −0.2 | V    |
|                           |                                                                                                                                    | V <sub>CC</sub> = 2.7 V, I <sub>OH</sub> = −20 μA at 25 pF load      |                                          |                  |                  |                      |      |
| V <sub>OL</sub>           | Low-level output voltage                                                                                                           | V <sub>CC</sub> = 5.5 V, I <sub>OL</sub> = 0.8 mA at 25 pF load      |                                          | 0.4              |                  | 0.1                  | V    |
|                           |                                                                                                                                    | V <sub>CC</sub> = 2.7 V, I <sub>OL</sub> = 20 μA at 25 pF load       |                                          |                  |                  |                      |      |
| I <sub>OZ</sub>           | Off-state output current (high-impedance-state)                                                                                    | V <sub>O</sub> = V <sub>CC</sub>                                     | $\overline{\text{CS}}$ = V <sub>CC</sub> | 1                | 2.5              |                      | μA   |
| I <sub>OZ</sub>           | Off-state output current (high-impedance-state)                                                                                    | V <sub>O</sub> = 0                                                   | $\overline{\text{CS}}$ = V <sub>CC</sub> | −2.5             | −1               |                      | μA   |
| I <sub>IH</sub>           | High-level input current                                                                                                           | V <sub>I</sub> = V <sub>CC</sub>                                     |                                          | 0.005            | 2.5              |                      | μA   |
| I <sub>IL</sub>           | Low-level input current                                                                                                            | V <sub>I</sub> = 0 V                                                 |                                          | −0.005           | 2.5              |                      | μA   |
| I <sub>CC</sub>           | Operating supply current, normal short sampling                                                                                    | $\overline{\text{CS}}$ at 0 V, Ext ref                               | V <sub>CC</sub> = 4.5 V to 5.5 V         | 1.1              |                  | mA                   |      |
|                           |                                                                                                                                    |                                                                      | V <sub>CC</sub> = 2.7 V to 3.3 V         | 1                |                  |                      |      |
|                           |                                                                                                                                    | $\overline{\text{CS}}$ at 0 V, Int ref                               | V <sub>CC</sub> = 4.5 V to 5.5 V         | 2.1              |                  | mA                   |      |
|                           |                                                                                                                                    |                                                                      | V <sub>CC</sub> = 2.7 V to 3.3 V         | 1.6              |                  |                      |      |
|                           | Operating supply current, extended sampling                                                                                        | $\overline{\text{CS}}$ at 0 V, Ext ref                               | V <sub>CC</sub> = 4.5 V to 5.5 V         | 1.1              |                  | mA                   |      |
|                           |                                                                                                                                    |                                                                      | V <sub>CC</sub> = 2.7 V to 3.3 V         | 1                |                  |                      |      |
|                           |                                                                                                                                    | $\overline{\text{CS}}$ at 0 V, Int ref                               | V <sub>CC</sub> = 4.5 V to 5.5 V         | 2.1              |                  | mA                   |      |
|                           |                                                                                                                                    |                                                                      | V <sub>CC</sub> = 2.7 V to 3.3 V         | 1.6              |                  |                      |      |
| I <sub>CC(PD)</sub>       | Power down supply current for all digital inputs, 0 ≤ V <sub>I</sub> ≤ 0.3 V or V <sub>I</sub> ≥ V <sub>CC</sub> − 0.3 V, SCLK = 0 | V <sub>CC</sub> = 4.5 V to 5.5 V, Ext clock                          |                                          | 0.1              | 1                | μA                   |      |
|                           |                                                                                                                                    | V <sub>CC</sub> = 2.7 V to 3.3 V, Ext clock                          |                                          | 0.1              | 1                |                      |      |
| I <sub>CC(AUTOPWDN)</sub> | Auto power-down current for all digital inputs, 0 ≤ V <sub>I</sub> ≤ 0.3 V or V <sub>I</sub> ≥ V <sub>CC</sub> − 0.3 V, SCLK = 0   | V <sub>CC</sub> = 4.5 V to 5.5 V, Ext clock, Ext ref                 |                                          | 1 <sup>‡</sup>   |                  | μA                   |      |
|                           |                                                                                                                                    | V <sub>CC</sub> = 2.7 V to 3.3 V, Ext ref, Ext clock                 |                                          | 1.0 <sup>§</sup> |                  |                      |      |
|                           | Selected channel leakage current                                                                                                   | Selected channel at V <sub>CC</sub>                                  |                                          | 1                |                  | μA                   |      |
|                           |                                                                                                                                    | Selected channel at 0 V                                              |                                          | 1                |                  |                      |      |
|                           | Maximum static analog reference current into REFP (use external reference)                                                         | V <sub>REFP</sub> = V <sub>CC</sub> = 5.5 V, V <sub>REFM</sub> = GND |                                          | 1                |                  | μA                   |      |
| C <sub>i</sub>            | Input capacitance                                                                                                                  | Analog inputs                                                        |                                          | 45               | 50               | pF                   |      |
|                           |                                                                                                                                    | Control Inputs                                                       |                                          | 5                | 25               |                      |      |
| Z <sub>i</sub>            | Input MUX ON resistance                                                                                                            | V <sub>CC</sub> = 4.5 V                                              |                                          | 500              |                  | Ω                    |      |
|                           |                                                                                                                                    | V <sub>CC</sub> = 2.7 V                                              |                                          | 600              |                  |                      |      |

<sup>†</sup> All typical values are at  $V_{CC} = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

<sup>‡</sup> 1.2 mA if internal reference is used, 165  $\mu\text{A}$  if internal clock is used.

<sup>§</sup> 0.8 mA if internal reference is used, 116  $\mu\text{A}$  if internal clock is used.

**TLV2544, TLV2548**

**2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER  
SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

electrical characteristics over recommended operating free-air temperature range,  $V_{CC} = V_{REFP} = 2.7\text{ V}$  to  $5.5\text{ V}$ ,  $V_{REFM} = 0\text{ V}$ , SCLK frequency = 20 MHz at 5 V, 15 MHz at 3 V (unless otherwise noted) (continued)

**ac specifications**

| PARAMETER           |                                   | TEST CONDITIONS                   |                | MIN | TYP  | MAX | UNIT |
|---------------------|-----------------------------------|-----------------------------------|----------------|-----|------|-----|------|
| SINAD               | Signal-to-noise ratio +distortion | $f_I = 12\text{ kHz}$ at 200 KSPS | C and I suffix | 69  | 70   |     | dB   |
| THD                 | Total harmonic distortion         | $f_I = 12\text{ kHz}$ at 200 KSPS |                |     | -82  | -76 | dB   |
| ENOB                | Effective number of bits          | $f_I = 12\text{ kHz}$ at 200 KSPS |                |     | 11.6 |     | Bits |
| SFDR                | Spurious free dynamic range       | $f_I = 12\text{ kHz}$ at 200 KSPS |                |     | -84  | -75 | dB   |
| <b>Analog input</b> |                                   |                                   |                |     |      |     |      |
|                     | Full power-bandwidth, -3 dB       |                                   |                |     | 1    |     | MHz  |
|                     | Full-power bandwidth, -1 dB       |                                   |                |     | 500  |     | kHz  |

**reference specifications<sup>†</sup> (0.1  $\mu\text{F}$  and 10  $\mu\text{F}$  between REFP and REFM pins)**

| PARAMETER                                     | TEST CONDITIONS                                                        |                            | MIN   | TYP | MAX             | UNIT                    |
|-----------------------------------------------|------------------------------------------------------------------------|----------------------------|-------|-----|-----------------|-------------------------|
| Positive reference input voltage, REFP        | $V_{CC} = 2.7\text{ V}$ to $5.5\text{ V}$                              |                            | 2     |     | $V_{CC}$        | V                       |
| Negative reference input voltage, REFM        | $V_{CC} = 2.7\text{ V}$ to $5.5\text{ V}$                              |                            | 0     |     | 2               | V                       |
| Reference Input impedance                     | $V_{CC} = 5.5\text{ V}$                                                | CS = 1, SCLK = 0, (off)    | 100   |     |                 | M $\Omega$              |
|                                               |                                                                        | CS = 0, SCLK = 20 MHz (on) | 20    | 25  |                 | k $\Omega$              |
|                                               | $V_{CC} = 2.7\text{ V}$                                                | CS = 1, SCLK = 0 (off)     | 100   |     |                 | M $\Omega$              |
|                                               |                                                                        | CS = 0, SCLK = 15 MHz (on) | 20    | 25  |                 | k $\Omega$              |
| Reference Input voltage difference, REFP-REFM | $V_{CC} = 2.7\text{ V}$ to $5.5\text{ V}$                              |                            | 2     |     | $V_{CC}$        | V                       |
| Internal reference voltage, REFP-REFM         | $V_{CC} = 5.5\text{ V}$                                                | VREF SELECT = 4 V          | 3.85  | 4   | 4.15            | V                       |
|                                               | $V_{CC} = 5.5\text{ V}$                                                | VREF SELECT = 2 V          | 1.925 | 2   | 2.075           | V                       |
|                                               | $V_{CC} = 2.7\text{ V}$                                                | VREF SELECT = 2 V          | 1.925 | 2   | 2.075           | V                       |
| Internal reference start-up time              | $V_{CC} = 5.5\text{ V}$ , 2.7 V with 10 $\mu\text{F}$ compensation cap |                            |       | 20  |                 | ms                      |
| Internal reference temperature coefficient    | $V_{CC} = 2.7\text{ V}$ to $5.5\text{ V}$                              |                            |       | 16  | 40 <sup>†</sup> | PPM/ $^{\circ}\text{C}$ |

<sup>†</sup> Specified by design



**TLV2544, TLV2548****2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER  
SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

operating characteristics over recommended operating free-air temperature range,  $V_{CC} = V_{REFP} = 2.7\text{ V}$  to  $5.5\text{ V}$ ,  $V_{REFM} = 0\text{ V}$ , SCLK frequency = 20 MHz at 5 V, 15 MHz at 3 V (unless otherwise noted)

| PARAMETER                                      |                                             | TEST CONDITIONS                                       | MIN  | TYP†                                             | MAX       | UNIT          |
|------------------------------------------------|---------------------------------------------|-------------------------------------------------------|------|--------------------------------------------------|-----------|---------------|
| $E_L$                                          | Integral linearity error (INL) (see Note 6) |                                                       |      |                                                  | $\pm 1$   | LSB           |
| $E_D$                                          | Differential linearity error (DNL)          | See Note 5                                            |      |                                                  | $\pm 1$   | LSB           |
| $E_O$                                          | Offset error (see Note 7)                   | See Note 5                                            |      |                                                  | $\pm 2.5$ | LSB           |
| $E_{FS}$                                       | Full scale error (see Note 7)               | See Note 5                                            | -1.6 |                                                  | +3.5      | LSB           |
| Self-test output code (see Table 1 and Note 8) |                                             | SDI = B000h                                           |      | 800h<br>(2048D)                                  |           |               |
|                                                |                                             | SDI = C000h                                           |      | 000h (0D)                                        |           |               |
|                                                |                                             | SDI = D000h                                           |      | FFFh<br>(4095D)                                  |           |               |
| $t_{(conv)}$                                   | Conversion time                             | Internal OSC                                          | 2.33 | 3.5                                              | 3.86      | $\mu\text{s}$ |
|                                                |                                             | External SCLK                                         |      | $\frac{(14 \times \text{DIV})}{f_{\text{SCLK}}}$ |           |               |
| $t_{(sample)}$                                 | Sampling time                               | With a maximum of 1-k $\Omega$ input source impedance | 600  |                                                  |           | ns            |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

- NOTES:
5. Analog input voltages greater than that applied to REFP convert as all ones (1111111111), while input voltages less than that applied to REFM convert as all zeros (000000000000).
  6. Linear error is the maximum deviation from the best straight line through the A/D transfer characteristics.
  7. Zero error is the difference between 000000000000 and the converted output for zero input voltage: full-scale error is the difference between 111111111111 and the converted output for full-scale input voltage.
  8. Both the input data and the output codes are expressed in positive logic.

## PARAMETER MEASUREMENT INFORMATION






Figure 16. Critical Timing, DSP Mode (Normal Sampling, FS is Active)

**PARAMETER MEASUREMENT INFORMATION**


† CSTART falling edge may come before the rising edge of CS but no sooner than the fifth SCLK of the SELECT CYCLE.

**Figure 17. Critical Timing (Extended Sampling, Single Shot)**


† CSTART falling edge may come before the rising edge of CS but no sooner than the fifth SCLK of the SELECT CYCLE. In this case, the actual sampling time is measured from the rising edge CS to the rising edge of CSTART.

**Figure 18. Critical Timing (Extended Sampling, Repeat/Sweep/Repeat Sweep)**

### PARAMETER MEASUREMENT INFORMATION




Figure 19. Critical Timing, Microprocessor Mode (Normal Sampling, FS = 1)

## TYPICAL CHARACTERISTICS




Figure 20




Figure 21




Figure 22




Figure 23

**TLV2544, TLV2548**

**2.7-V TO 5.5-V, 12-BIT, 200-KSPS, 4-/8-CHANNEL, LOW-POWER  
SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTOPOWER-DOWN**

SLAS198E – FEBRUARY 1999 – REVISED JUNE 2003

**TYPICAL CHARACTERISTICS**




Figure 24




Figure 25




Figure 26




Figure 27

## TYPICAL CHARACTERISTICS

### INTEGRAL NONLINEARITY VS SAMPLES




Figure 28

### DIFFERENTIAL NONLINEARITY VS SAMPLES




Figure 29

### INTEGRAL NONLINEARITY VS SAMPLES






Figure 30

## TYPICAL CHARACTERISTICS

### DIFFERENTIAL NONLINEARITY VS SAMPLES



**Figure 31**



**Figure 32**

## TYPICAL CHARACTERISTICS




Figure 33




Figure 34




Figure 35





Figure 36

## TYPICAL CHARACTERISTICS



## PRINCIPLES OF OPERATION




Figure 38. Typical Interface to a TMS320 DSP™

## DATA CODE INFORMATION

Parts with a date code earlier than 31xxxxx have the following discrepancies:

1. Earlier devices react to FS input irrespective of the state of the  $\overline{\text{CS}}$  signal
2. The earlier silicon was designed with SDO prereleased half clock ahead. This means in the microcontroller mode (FS=1) the SDO is changed on the rising edge of SCLK with a delay; and for DSP serial port (when FS is active) the SDO is changed on the falling edge of SCLK with a delay. This helps the setup time for processor input data, but may reduce the hold time for processor input data. It is recommended that a 100 pF capacitance be added to the SDO line of the ADC when interfacing with a slower processor that requires longer input data hold time.
3. For earlier silicon, the delay time is specified as:

|                                                                                                                                |                          |              | MIN | NOM | MAX | UNIT |
|--------------------------------------------------------------------------------------------------------------------------------|--------------------------|--------------|-----|-----|-----|------|
| Delay time, delay from SCLK falling edge (FS is active) or SCLK rising edge (FS=1) to next SDO valid, $t_d(\text{SCLK-DOV})$ . | $V_{CC} = 4.5 \text{ V}$ | SDO = 0 pF   | 16  |     |     | ns   |
|                                                                                                                                |                          | SDO = 100 pF | 20  |     |     |      |
|                                                                                                                                | $V_{CC} = 2.7 \text{ V}$ | SDO = 0 pF   | 24  |     |     |      |
|                                                                                                                                |                          | SDO = 100 pF | 30  |     |     |      |

This is because the SDO is changed at the rising edge in the up mode with a delay. This is the hold time required by the external digital host processor, therefore, a minimum value is specified. The newer silicon has been revised with SDO changed at the falling edge in the up mode with a delay. Since at least 0.5 SCLK exists as the hold time for the external host processor, the specified maximum value helps with the calculation of the setup time requirement of the external digital host processor.

For an explanation of the DSP mode, reverse the rising/falling edges in item (2) above.

## PACKAGING INFORMATION

| Orderable part number       | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TLV2544CD</a>   | Active        | Production           | SOIC (D)   16   | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 2544C               |
| TLV2544CD.A                 | Active        | Production           | SOIC (D)   16   | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 2544C               |
| <a href="#">TLV2544CDR</a>  | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 2544C               |
| TLV2544CDR.A                | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 2544C               |
| <a href="#">TLV2544CPW</a>  | Active        | Production           | TSSOP (PW)   16 | 90   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TV2544              |
| TLV2544CPW.A                | Active        | Production           | TSSOP (PW)   16 | 90   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TV2544              |
| <a href="#">TLV2544CPWR</a> | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TV2544              |
| TLV2544CPWR.A               | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TV2544              |
| <a href="#">TLV2544ID</a>   | Active        | Production           | SOIC (D)   16   | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 2544I               |
| TLV2544ID.A                 | Active        | Production           | SOIC (D)   16   | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 2544I               |
| <a href="#">TLV2544IDR</a>  | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 2544I               |
| TLV2544IDR.A                | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 2544I               |
| <a href="#">TLV2544IPW</a>  | Active        | Production           | TSSOP (PW)   16 | 90   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2544              |
| TLV2544IPW.A                | Active        | Production           | TSSOP (PW)   16 | 90   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2544              |
| <a href="#">TLV2544IPWR</a> | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2544              |
| TLV2544IPWR.A               | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2544              |
| <a href="#">TLV2548CDW</a>  | Active        | Production           | SOIC (DW)   20  | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 2548C               |
| TLV2548CDW.A                | Active        | Production           | SOIC (DW)   20  | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 2548C               |
| <a href="#">TLV2548CDWR</a> | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 2548C               |
| TLV2548CDWR.A               | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | 2548C               |
| <a href="#">TLV2548CPW</a>  | Active        | Production           | TSSOP (PW)   20 | 70   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TV2548              |
| TLV2548CPW.A                | Active        | Production           | TSSOP (PW)   20 | 70   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TV2548              |
| <a href="#">TLV2548CPWR</a> | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TV2548              |
| TLV2548CPWR.A               | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | TV2548              |
| <a href="#">TLV2548IDW</a>  | Active        | Production           | SOIC (DW)   20  | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 2548I               |
| TLV2548IDW.A                | Active        | Production           | SOIC (DW)   20  | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 2548I               |
| <a href="#">TLV2548IDWR</a> | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 2548I               |
| TLV2548IDWR.A               | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 2548I               |
| <a href="#">TLV2548IPW</a>  | Active        | Production           | TSSOP (PW)   20 | 70   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2548              |

| Orderable part number       | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TLV2548IPW.A                | Active        | Production           | TSSOP (PW)   20 | 70   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2548              |
| TLV2548IPWG4                | Active        | Production           | TSSOP (PW)   20 | 70   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2548              |
| <a href="#">TLV2548IPWR</a> | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2548              |
| TLV2548IPWR.A               | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | TY2548              |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## OTHER QUALIFIED VERSIONS OF TLV2548 :

- Enhanced Product : [TLV2548-EP](#)

- Military : [TLV2548M](#)

NOTE: Qualified Version Definitions:

- Enhanced Product - Supports Defense, Aerospace and Medical Applications
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device      | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TLV2544CDR  | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| TLV2544CPWR | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| TLV2544IDR  | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| TLV2544IPWR | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| TLV2548CDWR | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.8    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| TLV2548CPWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.1     | 1.6     | 8.0     | 16.0   | Q1            |
| TLV2548IDWR | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.8    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| TLV2548IPWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.1     | 1.6     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal



| Device      | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TLV2544CDR  | SOIC         | D               | 16   | 2500 | 350.0       | 350.0      | 43.0        |
| TLV2544CPWR | TSSOP        | PW              | 16   | 2000 | 350.0       | 350.0      | 43.0        |
| TLV2544IDR  | SOIC         | D               | 16   | 2500 | 350.0       | 350.0      | 43.0        |
| TLV2544IPWR | TSSOP        | PW              | 16   | 2000 | 350.0       | 350.0      | 43.0        |
| TLV2548CDWR | SOIC         | DW              | 20   | 2000 | 350.0       | 350.0      | 43.0        |
| TLV2548CPWR | TSSOP        | PW              | 20   | 2000 | 350.0       | 350.0      | 43.0        |
| TLV2548IDWR | SOIC         | DW              | 20   | 2000 | 350.0       | 350.0      | 43.0        |
| TLV2548IPWR | TSSOP        | PW              | 20   | 2000 | 350.0       | 350.0      | 43.0        |

## TUBE



\*All dimensions are nominal

| Device       | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|--------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TLV2544CD    | D            | SOIC         | 16   | 40  | 505.46 | 6.76   | 3810   | 4      |
| TLV2544CD.A  | D            | SOIC         | 16   | 40  | 505.46 | 6.76   | 3810   | 4      |
| TLV2544CPW   | PW           | TSSOP        | 16   | 90  | 530    | 10.2   | 3600   | 3.5    |
| TLV2544CPW.A | PW           | TSSOP        | 16   | 90  | 530    | 10.2   | 3600   | 3.5    |
| TLV2544ID    | D            | SOIC         | 16   | 40  | 505.46 | 6.76   | 3810   | 4      |
| TLV2544ID.A  | D            | SOIC         | 16   | 40  | 505.46 | 6.76   | 3810   | 4      |
| TLV2544IPW   | PW           | TSSOP        | 16   | 90  | 530    | 10.2   | 3600   | 3.5    |
| TLV2544IPW.A | PW           | TSSOP        | 16   | 90  | 530    | 10.2   | 3600   | 3.5    |
| TLV2548CDW   | DW           | SOIC         | 20   | 25  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV2548CDW.A | DW           | SOIC         | 20   | 25  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV2548CPW   | PW           | TSSOP        | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| TLV2548CPW.A | PW           | TSSOP        | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| TLV2548IDW   | DW           | SOIC         | 20   | 25  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV2548IDW.A | DW           | SOIC         | 20   | 25  | 506.98 | 12.7   | 4826   | 6.6    |
| TLV2548IPW   | PW           | TSSOP        | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| TLV2548IPW.A | PW           | TSSOP        | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| TLV2548IPWG4 | PW           | TSSOP        | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |



4220206/A 02/2017

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220206/A 02/2017

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X


4220206/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



## NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- $\triangle C$  Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- $\triangle D$  Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AC.



## NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.

# EXAMPLE BOARD LAYOUT



DW0020A

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE  
SCALE:6X



SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC





SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



4220204/B 12/2023

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220204/B 12/2023

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220204/B 12/2023

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated