



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A6	ECR-18-014557	14SEP18	L.P	T.D


SUGGESTED MATING TAB



TYPE A (When using tab shoulder for butting)



TYPE B(When using resin, etc. for butting)




NOTE:


- 1.HOUSING MATERIAL,NYLON 6/66,GLASS-FIBRE. UL94V-0.
- 2.GWT 750°C VERSION,ACCORDING TO IEC 60335-1.
- 3.CONTACT MATERIAL,TIN PLATED BRASS.



SECTION B-B
SCALE 4:1



5.8REF.	6.2	4.5REF.	4.5	3.40-5.08	14-12	2299282-3
4.9REF.	5.3	3.9REF.	3.5	3.0-4.0	18-14	2299282-2
4.9REF.	4.2	3.1REF.	2.6	2.2-3.0	22-18	2299282-1
DIM D	DIM C	DIM B	DIM A	INSULATION(mm)	WIRE SIZE(AWG)	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN LEI.PAN	14NOV2016	 TE Connectivity										
DIMENSIONS:			CHK TIM.DING	14NOV2016											
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD TIM.DING	14NOV2016	NAME POD-LOK 250 STR.ASSY.										
mm			PRODUCT SPEC 108-106262												
			APPLICATION SPEC 114-106262		SIZE A2		CAGE CODE -		DRAWING NO C-2299282		RESTRICTED TO -				
			WEIGHT -												
			MATERIAL			CUSTOMER DRAWING		SCALE		SHEET		OF		REV	
			-			-		5:1		1		A6			