

LIMITED WARRANTY

HARDWARE: 3Com Limited ("3Com") warrants its hardware products to be free from defects in workmanship and materials, under normal use and service, for the following lengths of time from the date of purchase from 3Com or its Authorized Reseller:

Internetworking products

Ethernet Stackable Hubs and Unmanaged Ethernet Fixed Port Repeaters

One year

Lifetime*

(One Year if not registered)

*Power supply and fans in these stackable hubs and unmanaged repeaters

One Year

Other hardware products

Spare parts and spares kits 90 days

One year

If a product does not operate as warranted during the applicable warranty period, 3Com shall, at its option and expense, repair the defective product or part, deliver to Customer an equivalent product or part to replace the defective item, or refund to Customer the purchase price paid for the defective product. All products that are replaced will become the property of 3Com. Replacement products may be new or reconditioned. Any replaced or repaired product or part has a ninety (90) day warranty or the remainder of the initial warranty period, whichever is longer.

3Com shall not be responsible for any software, firmware, information, or memory data of Customer contained in, stored on, or integrated with any products returned to 3Com pursuant to any warranty.

SOFTWARE: 3Com warrants that the software programs licensed from it will perform in substantial conformance to the program specifications therefor for a period of ninety (90) days from the date of purchase from 3Com or its Authorized Reseller. 3Com warrants the magnetic media containing software against failure during the warranty period. No updates are provided. 3Com's sole obligation hereunder shall be (at 3Com's discretion) to refund the purchase price paid by Customer for any defective software products, or to replace any defective media with software which substantially conforms to 3Com's applicable published specifications. Customer assumes responsibility for the selection of the appropriate applications program and associated reference materials. 3Com makes no warranty that its software products will work in combination with any hardware or applications software products provided by third parties, that the operation of the software products will be uninterrupted or error free, or that all defects in the software products will be corrected. For any third party products listed in the 3Com software product documentation or specifications as being compatible, 3Com will make reasonable efforts to provide compatibility, except where the non-compatibility is caused by a "bug" or defect in the third party's product.

STANDARD WARRANTY SERVICE: Standard warranty service for hardware products may be obtained by delivering the defective product, accompanied by a copy of the dated proof of purchase, to 3Com's Service Center or to an Authorized 3Com Service Center during the applicable warranty period. Standard warranty service for software products may be obtained by telephoning 3Com's Service Center or an Authorized 3Com Service Center, within the warranty period. Products returned to 3Com's Service Center must be pre-authorized by 3Com with a Return Material Authorization (RMA) number marked on the outside of the package, and sent prepaid, insured, and packaged appropriately for safe shipment. The repaired or replaced item will be shipped to Customer, at 3Com's expense, not later than thirty (30) days after receipt by 3Com.

WARRANTIES EXCLUSIVE: IF A 3COM PRODUCT DOES NOT OPERATE AS WARRANTED ABOVE, CUSTOMER'S SOLE REMEDY SHALL BE REPAIR, REPLACEMENT, OR REFUND OF THE PURCHASE PRICE PAID, AT 3COM'S OPTION. THE FOREGOING WARRANTIES AND REMEDIES ARE EXCLUSIVE AND ARE IN LIEU OF ALL OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, EITHER IN FACT OR BY OPERATION OF LAW, STATUTORY OR OTHERWISE, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. 3COM NEITHER ASSUMES NOR AUTHORIZES ANY OTHER PERSON TO ASSUME FOR IT ANY OTHER LIABILITY IN CONNECTION WITH THE SALE, INSTALLATION, MAINTENANCE OR USE OF ITS PRODUCTS.

3COM SHALL NOT BE LIABLE UNDER THIS WARRANTY IF ITS TESTING AND EXAMINATION DISCLOSE THAT THE ALLEGED DEFECT IN THE PRODUCT DOES NOT EXIST OR WAS CAUSED BY CUSTOMER'S OR ANY THIRD PERSON'S MISUSE, NEGLIGENCE, IMPROPER INSTALLATION OR TESTING, UNAUTHORIZED ATTEMPTS TO REPAIR, OR ANY OTHER CAUSE BEYOND THE RANGE OF THE INTENDED USE, OR BY ACCIDENT, FIRE, LIGHTNING, OR OTHER HAZARD.

LIMITATION OF LIABILITY. IN NO EVENT, WHETHER BASED IN CONTRACT OR TORT (INCLUDING NEGLIGENCE) SHALL 3COM BE LIABLE FOR INCIDENTAL, CONSEQUENTIAL, INDIRECT, SPECIAL, OR PUNITIVE DAMAGES OF ANY KIND, OR FOR LOSS OF REVENUE, LOSS OF BUSINESS, OR OTHER FINANCIAL LOSS ARISING OUT OF OR IN CONNECTION WITH THE SALE, INSTALLATION, MAINTENANCE, USE, PERFORMANCE, FAILURE, OR INTERRUPTION OF ITS PRODUCTS, EVEN IF 3COM OR ITS AUTHORIZED RESELLER HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. NOTHING HEREIN SHALL HAVE THE EFFECT OF LIMITING OR EXCLUDING 3COM'S LIABILITY FOR DEATH OR PERSONAL INJURY CAUSED BY NEGLIGENCE.

Some states do not allow the exclusion of implied warranties or the limitation of incidental or consequential damages for consumer products, so the above limitations and exclusions may not apply to you. This warranty gives you specific legal rights which may vary from state to state. Nothing in this warranty shall be taken to affect your statutory rights.

GOVERNING LAW: This Limited Warranty shall be governed by the laws of England.

3Com Limited, ISOLAN House, Brindley Way, London Road, Hemel Hempstead, Hertfordshire, HP3 9XJ, UK. 44(0)442 278000

23/12/93


LinkBuilder

How To Install and Use The

Female AUI Transceiver Module

3C12060

This manual provides a general description of the 3Com Female AUI Transceiver Module, 3C12060. Please retain this manual with your other 3Com manuals for future use.



1 Interworking Information

The 3Com[®] Female AUI Transceiver Module has been designed to the IEEE 802.3 specification for an AUI interface to provide external transceiver connectivity.

The Transceiver Module provides an extra port or connectivity to another medium on the following LinkBuilder[®] products:

- ECS modules (3C12076 and 3C12050/1)
- MSH modules (3C18110, 3C18120, 3C18124, 3C18146 and 3C18600)
- FMS Stackable Hubs (3C16250, 3C16265, 3C16271 and 3C16371)
- FMS II Stackable Hubs (3C16665, 3C16670 and 3C16671)
- Repeaters (3C16170, 3C16200, 3C16210 and 3C16505)

This product has the benefit of a "lifetime warranty": see page 4.

2 Installation




Only qualified personnel should install this device. Observe anti-static precautions! Use an earthed wrist-band!

The Transceiver Module provides a 15-pin female AUI connector (acting as a DTE port) at the external interface end. A 16-pin header and a 16-way edge connector are mounted at the other end of the Transceiver Module for connection to a Module, Stackable Hub or Repeater.

The Transceiver Module is connected to an external transceiver directly or with an AUI cable (transceiver cable or drop cable) with a maximum length of 50 metres (although in most cases 3 metres should be sufficient).

The Transceiver Module will enable the Module, Stackable Hub or Repeater to connect to a variety of transmission medium such as a fiber, UTP, STP or Thin Ethernet.

Example



Preparation

Before you install the Transceiver Module, you must remove the Module, Hub or Repeater from the network and all power sources. Modules must be removed from the Chassis (you do not need to power down the Chassis first). The 3C18146 Expansion Module must be separated from its mother module. See the relevant *User Guide* or '*How to Install and Use...*' manual.

Remove the blanking plate from the unit in which you are going to install the Transceiver Module. The relevant manual will tell you where to find the plate.

Keep the blanking plate in a safe place so that it can be replaced when the Transceiver Module is removed.

Installing in a Stackable Hub or Repeater

For FMS Stackables and Repeaters, hold the mounting panel with the pin header side of the board *down*.

For FMS II Stackables, hold the mounting panel with the pin header side of the board *up*.

Insert the edge connector end of the Transceiver Module into the rear of the mother device.

Slide the Transceiver Module in carefully to engage in the slot and push it fully home.

Fix the mounting panel of the Transceiver Module to the back panel using the two screws from the blanking plate.

Installing on an ECS or MSH Module

Position the Module on a flat surface with the 16-way socket facing up.

Hold the Transceiver Module by the mounting panel and board edge with the header pins facing down.

Pass the board of the Transceiver Module through the cut-out in the front panel.

Align the socket on the Module with the pins on the Transceiver Module and push down firmly to connect.

With the 3C18146 Expansion Module, you align the header and pins and press gently to engage the pins. Turn the pair over to rest on the Transceiver Module and press firmly close to the header to complete connection.

Fix the mounting panel of the Transceiver Module to the module using the two screws from the blanking plate.

Connection

Once the Transceiver Module is secured in place, attach an external transceiver, directly or with an AUI cable. Remember to engage the slidelocks at both ends of the AUI cable, if you use one.

3 Operation

Re-install the mother device into its chassis and/or network and power up. The Transceiver Module will operate correctly once power is applied.

4 Problems

If, after installing the Transceiver Module, no communication is possible, check the settings of the host unit and that it is receiving power. If no error is found, refer to the supplier of your 3Com Female AUI Transceiver Module for further advice.

Standards

The 3Com Female AUI Transceiver Module 3C12060 has been designed to conform to the following standards:

Safety	UL 478 EN 60950	CSA 22.2
Environmental	IEC 68	
R.F.I.	FCC Part 15 (Class A) VDE 0871 Level B	
Functional	ISO 8802/3, IEEE 802.3	

Radio Frequency Interference Statement

This equipment has been tested with a class A computing device and has been found to comply with part 15 of FCC Rules. Operation in a residential area may cause unacceptable interference to radio and TV receptions requiring the operator to take whatever steps are necessary to correct the interference.

This digital apparatus does not exceed the Class A limits for radio noise emissions from digital apparatus as set out in the interference-causing equipment standard entitled "Digital Apparatus", ICES-003 of the Department of Communications.

Cet appareil numérique respecte les limites de bruits radioélectriques applicables aux appareils numériques de Classe A prescrites dans la norme sur le matériel brouilleur : "Appareils Numériques", NMB-003 édictée par le ministre des Communications.

3Com and **LinkBuilder** are registered trademarks and **FMS**, **FMS II** and **MSH** are trademarks of the 3Com Corporation.

Disclaimer

Information in this document is subject to change without notice and does not represent a commitment on the part of 3Com. 3Com reserves the right to revise or change this document without obligation of 3Com to notify any person of the revisions or changes. Information contained in this document is believed to be accurate at the time of publication but no liability whatsoever can be accepted by 3Com arising out of any use of this information.

Document No: DUA1206-0AAA04
Revision: 00
Issued: August 1994
© 1994 3Com Ireland