






REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-19-009721	01JUL2019	M.G	D.Z



- NOTE;
- THIS HOUSING ACCEPTS TAB TERMINAL:
-TAB CONTACT: 177917-□ (AWG#16-#20)
177916-□ (AWG#22-#26)
 - MATING CONN. P/N
-PLUG HSG: 368571-□
-REC CONTACT: 177915-□ (AWG#16-#20)
: 177914-□ (AWG#22-#26)
 - APPLICABLE DOUBLE LOCK PLATE: 177919-1
*IT SHOULD BE USED CERTAINLY WHEN CABLE ASS'Y
 - GENERAL TOLERANCES: ±0.3
 - APPLICATOIN PANEL THICKNESS: 0.8~2.0 (SEE FIG 1.)
 - INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
 - EDGE OF THICKNESS MAY MUST NOT ROUND FOR MOLDED PANEL.
 - MATERIAL: PA66 UL94V-0
COMPLY WITH GLOW WIREREQUIREMENT FOR PARTS OF NON-METALLIC MATERIALSUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT).

2005250-9	BLACK
2005250-6	BLUE
2005250-4	YELLOW
2005250-2	RED
2005250-1	NATURAL
P/N	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SC KIM		TE TE Connectivity	
CHK BW KANG		APVD JK SONG			
PRODUCT SPEC 108-5410		NAME PDL 3P CAP HSG 3.96mm P/M (GWT)			
APPLICATION SPEC 114-5175		SIZE A3			
WEIGHT -		CAGE CODE 00779			
CUSTOMER DRAWING		DRAWING NO C-2005250			
SCALE 4:1		SHEET 1 OF 1			
REV B					