








view shown without plastic pin and grounding

PC card drilling dimensions(after plating)

(thickness 1.60 ± 0.25 mm)



	AtO.38	BtO.12	CtO.10	DtO.25	EuO.07	TIN LEAD PART NUMBER	TIN LEAD PART NUMBER	LEAD FREE PART NUMBER	LEAD FREE PART NUMBER
SHELL									
09	30.81	24.99	18.00	16.21	10.96	D09S80C4X00I	D09S80C6X00I	D09S80C4X00I	D09S80C6X00I
15	39.14	33.32	26.32	24.54	19.18	D15S80C4X00I	D15S80C6X00I	D15S80C4X00I	D15S80C6X00I
25	53.03	47.04	40.04	38.25	33.12	D25S80C4X00I	D25S80C6X00I	D25S80C4X00I	D25S80C6X00I
37	69.32	63.50	56.50	54.71	49.68	D37S80C4X00I	D37S80C6X00I	D37S80C4X00I	D37S80C6X00I
						Gold flash	0.76 » gold	Gold flash	0.76 » gold



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

Detail of grounding strip



mat'l. code				surface		tolerance		projection		product family	
-				ISO 1302		ISO 406 ISO 1101				D-SUB	
				Intolerances unless otherwise specified							
litr	ecn no	dr	date	angles	linear	.0±.0.1 .00±0.1					
H	EEX-17859	MP	2014/06/06								