

# TIGHT STABILITY INDUSTRIAL GRADE CRYSTAL OSCILLATOR

## ASET SERIES



**ESD Sensitive**



**RoHS/RoHS II compliant**



3.2 x 2.5 x 1.2mm

**Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable**

### FEATURES:

- Highly reliable seam-sealed package
- Low current consumption 7mA
- Low phase noise and jitter
- Industrial grade tight temperature stability available ( $\pm 10\text{ppm}$  /  $-40$  to  $+85^\circ\text{C}$ )
- Fast start-up time 0.2ms typical
- CMOS output with Tri-state function

### APPLICATIONS:

- Home networking by AC socket
- Wireless LAN
- Mobile communications
- PLC modem
- WiMax

### STANDARD SPECIFICATIONS:

| Parameters                   | Minimum                                                                                                   | Typical | Maximum  | Units            | Notes         |
|------------------------------|-----------------------------------------------------------------------------------------------------------|---------|----------|------------------|---------------|
| Frequency Range              | 4                                                                                                         |         | 54       | MHz              |               |
| Standard Frequencies         | 5, 10, 12, 16, 20, 24, 26, 27, 32, 40, 44                                                                 |         |          | MHz              |               |
| Operating Temperature        | -40                                                                                                       |         | +85      | $^\circ\text{C}$ |               |
| Storage Temperature          | -40                                                                                                       |         | +85      | $^\circ\text{C}$ |               |
| Overall Frequency Stability* | -15                                                                                                       |         | +15      | ppm              | See options   |
| Supply Voltage (Vdd)         | +2.7                                                                                                      | 3.0     | +3.3     | V                | See options   |
| Supply Current (Idd)         |                                                                                                           |         | 7.0      | mA               |               |
| Stand-by Current             |                                                                                                           |         | 10       | $\mu\text{A}$    |               |
| Symmetry                     | 45                                                                                                        |         | 55       | %                | @ 1/2Vdd      |
| Rise and Fall Time (Tr/Tf)   |                                                                                                           |         | 5.0      | ns               | 10%Vdd-90%Vdd |
| Output Load                  |                                                                                                           |         | 15       | pF               | CMOS          |
| Output Voltage (VOH)         | 0.9* Vdd                                                                                                  |         |          | V                |               |
| Output Voltage (VOL)         |                                                                                                           |         | 0.1* Vdd | V                |               |
| Start-up Time                |                                                                                                           | 0.2     | 3.0      | ms               |               |
| RMS Jitter                   |                                                                                                           | 3.0     |          | ps               |               |
| Tri-state function           | "1" ( $V_{IH} \geq 0.7 \cdot V_{dd}$ ) or Open: Oscillation<br>"0" ( $V_{IH} < 0.3 \cdot V_{dd}$ ) : Hi Z |         |          |                  |               |
| Phase Noise (@10kHz offset)  |                                                                                                           | -143    |          | dBc/Hz           |               |
| Aging@+25 $^\circ\text{C}$   | -2                                                                                                        |         | +2       | ppm              | First year    |
|                              | -7                                                                                                        |         | +7       |                  | 10 years      |

\* Overall frequency stability includes initial tolerance @ +25 $^\circ\text{C}$ , and temperature stability

### OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)

ASET-  -  MHz -  -

| Supply Voltage        |
|-----------------------|
| Blank: 3.0 $\pm 10\%$ |
| A: 2.7 $\pm 10\%$     |
| B: 3.3 $\pm 10\%$     |
| C: 2.8 $\pm 10\%$     |
| D: 2.5 $\pm 10\%$     |

| Frequency in MHz                                       |
|--------------------------------------------------------|
| Please specify the frequency in MHz.<br>e.g. 24.000MHz |

| Overall Freq. Stability   |
|---------------------------|
| Blank: $\pm 15\text{ppm}$ |
| Y: $\pm 10\text{ppm}$     |
| R7*: $\pm 7\text{ppm}$    |
| R5*: $\pm 5\text{ppm}$    |

| Packaging      |
|----------------|
| Blank: Bulk    |
| T: Tape & Reel |

\*Contact Abracon for availability



# TIGHT STABILITY INDUSTRIAL GRADE CRYSTAL OSCILLATOR

**ASET SERIES**




3.2 x 2.5 x 1.2mm




RoHS/RoHS II compliant

## OUTLINE DRAWING:



Recommended land pattern




| Pin | Function |
|-----|----------|
| 1   | OE       |
| 2   | NC       |
| 3   | GND      |
| 4   | Output   |
| 5   | NC       |
| 6   | Vdd      |

Note: Recommend using an approximately 0.01uF bypass capacitor between PIN 3 and 6.


Dimensions: Inches (mm)

## TAPE & REEL: T= tape and reel (1,000 pcs/reel)

Dimensions: mm



## REFLOW PROFILE



Need a test socket for the ASET Series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, [click here](#). P/N: AXS-3225-04-05

**ATTENTION:** Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS  
ISO 9001 :2008  
CERTIFIED



**ABRACON  
CORPORATION**

2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 12.09.14**

Ph. 949.546.8000 | Fax. 949.546.8001

Visit [www.abracon.com](http://www.abracon.com) for Terms and Conditions of Sale