



6.1 MAX
.24 MAX

- NOTE:
- 1 MATERIAL: BASE AND COVER: 30% GLASS FILLED POLYESTER FLAME RETARDANT PER UL-94-V0
COLOUR: SEE TABLE
STRAIN RELIEF: UNREINFORCED THERMOPLASTIC FLAME RETARDANT PER UL-94-V0
COLOUR: GREY
CONTACT: PHOSPHORE BRONZE
 - 2 PLATING: 0.38 μ m / 15 μ " Au OVER 1.27 μ m / 50 μ " Ni MIN IN CONTACT AREA REMAINDER OF PRODUCT (IDC PART)
1.5 μ m / 60 μ " TIN LEAD OVER 1.27 μ m / 50 μ " Ni
 - 3 COVER AND STRAIN RELIEF ARE LOOSE PIECES DELIVERED IN BOX
 - 4 DIM PRODUCT WITH COVER IN PRELOAD POSITION
13 $\pm$ 0.3 / .512 $\pm$ 0.008
 - 5 A DASH "A" AT THE END OF THE PART NUMBER TO INDICATE A SELECTIVE LOADED (SEE TABLE TO IDENTIFY MISSING TERMINALS POSITION), COLOR: BLUE SEE TABLE
 - 6 A DASH "K" AT THE END OF THE PART NUMBER TO INDICATE A SOLID CENTER KEY
 - 7 A DASH "L" AT THE END OF THE PART NUMBER TO INDICATE A NEW LATCH DESIGN SEE NOTE 7



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FCI ELECTRONICS	
ltr	ecr no	dr	date	linear				projection		title	
E	V50865	PNZ	95.07.20							RECEP. 2 PCS.	
F	F03019	DLE	03.01.23							0.38 μ m / 15 μ "	
				angles						product family	QUICKIE III
				dr	P NIZZI	95.07.20				code	213
				engr	JM PHAMVAN	95.07.20				size	dwg no
				chr	P NIZZI	95.07.20				A2	93699
				appd	JMP	95.07.20				scale	4:1
sheet index	revision	F	F								sheet 1 of 2

