

SPECIFICATION

1520

Description: 0-5VDC 3A, 6.3VAC 3A, -8V, +8VDC 100mA
-250V, -125V, +125V, +250V DC 10mA

Power supply

Input Voltage: 115VAC 60Hz

Environment Temperature: 25C°

	MIN.	TYP.	MAX.	UNIT
0-5VDC:				
Output Voltage Range	0		5	V
Min. Output Voltage			100	mV
Max. Output Voltage	5.5		6.5	V
Output Current		3		A
Voltage Regulation:				
Load (0-100% load)			500	mV
Line (105-125VAC Variation)			200	mV
Ripple & Noise			500	mVp-p
6.3VAC:				
Output Voltage No Load	6.5		8	V
Output Voltage Full Load	5.8			V
Output Current		3		A
-8VDC:				
Output Voltage No Load	-7.5		-8.8	V
Output Voltage Full Load	-7.3		-8.5	V
Output Current		100		mA
+8VDC:				
Output Voltage No Load	+7.5		+8.8	V
Output Voltage Full Load	+7.3		+8.5	V
Output Current		100		mA
-250VDC:				
Output Voltage No Load	-240		-300	V
Output Voltage Full Load	-220		-280	V
Output Current		10		mA
+250VDC:				
Output Voltage No Load	+240		+300	V
Output Voltage Full Load	+220		+280	V
Output Current		10		mA
+125VDC:				
Output Voltage No Load	+120		+160	V
Output Voltage Full Load	+110		+140	V
Output Current		10		mA
-125VDC:				
Output Voltage No Load	-120		-160	V

Output Voltage Full Load	-110	-160	V
Output Current	10		mA
No Load Input Current	120	180	mA
Full Load Input Current (All Rated Load)	0.55	1	A
Fuse	2		A

Dimensions (W X D X H): 7.24 x 7 x 4.33"

Weight: 6.61 LBS.

Operation:

Plug model 1520 into AC outlet. Turn power switch on, power light will come on. Adjust control knob to desired voltage.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[1520-NIST](#)