

1.0A Surface Mount Bridge Rectifier

Features

- Glass passivated chip junction
- Low forward voltage drop
- High surge current capability
- Ideal for printed circuit boards
- Designed for surface mount application
- High temperature soldering guaranteed: 260°C/10 seconds
0.375" (9.5mm) lead length at 5lbs.(2.3kg) tension
- RoHS compliant



DFS



Mechanical Data

Case:	DFS, Molded plastic body over passivated junction
Epoxy:	Plastic package has UL flammability classification 94V-0
Terminals:	Plated leads solderable per MIL-STD-202, method 208
Polarity:	As marked on body
Weight:	0.014 ounce, 0.4 grams

Maximum Ratings And Electrical Characteristics (T_{amb}=25°C)

Symbol	Description	DF 005S	DF 01S	DF 02S	DF 04S	DF 06S	DF 08S	DF 10S	DF 12S	Unit	Conditions
V_{RRM}	Maximum Repetitive Peak Reverse Voltage	50	100	200	400	600	800	1000	1200	V	
V_{RMS}	Maximum RMS Voltage	35	70	140	280	420	560	700	840	V	
V_{DC}	Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	1200	V	
I_{F(AV)}	Maximum Average Forward Rectified Current	1.0								A	T _A =40° C Note 1
I_{FSM}	Peak Forward Surge Current	50								A	8.3ms Single Sine-wave Superimposed on Rated Load (JEDEC Method)
I²_t	Rating for Fusing (t<8.3ms)	10								A ² sec	

1.0A Surface Mount Bridge Rectifier

DF005S – DF12S

Symbol	Description	DF 005S	DF 01S	DF 02S	DF 04S	DF 06S	DF 08S	DF 10S	DF 12S	Unit	Conditions
V _F	Maximum Instantaneous Forward Voltage Drop per leg	1.1								V	I _F =1.0A
I _R	Maximum DC Reverse Current at Rated DC Blocking Voltage per leg	5.0								μA	T _A =25°C
		500									T _A =125°C
C _J	Typical Junction Capacitance per leg	25								pF	V _R =4V, f=1MHz
R _{θJA}	Typical Thermal Resistance per leg	40								°C/W	Note 1
R _{θJL}		15									
T _J ,T _{STG}	Operating Junction and Storage Temperature Range	-55 to +150								°C	

Note: 1.Units mounted on P.C.B. with 0.51 x 0.51" (13 x 13mm) copper pads.

Rating and Characteristic Curves

Fig.1- Derating Curve Output Rectified Current





Fig.2-Maximum Non-Repetitive Peak Forward Surge Current per leg



1.0A Surface Mount Bridge Rectifier

DF005S – DF12S

Fig.3-Typical Forward Characteristics
per leg




Fig.4-Typical Reverse Leakage Characteristics
per leg






Fig.5- Typical Junction Capacitance per leg




1.0A Surface Mount Bridge Rectifier

DF005S – DF12S

Dimensions in inch (mm)



Mounting Pad Layout in inch (mm)



1.0A Surface Mount Bridge Rectifier

DF005S – DF12S

How to contact us:

US HEADQUARTERS

28040 WEST HARRISON PARKWAY, VALENCIA, CA 91355-4162

Tel: (800) TAITRON (800) 824-8766 (661) 257-6060

Fax: (800) TAITFAX (800) 824-8329 (661) 257-6415

Email: taitron@taitroncomponents.com

Http://www.taitroncomponents.com

TAITRON COMPONENTS MEXICO, S.A .DE C.V.

BOULEVARD CENTRAL 5000 INTERIOR 5 PARQUE INDUSTRIAL ATITALAQUIA, HIDALGO C.P.
42970 MEXICO

Tel: +52-55-5560-1519

Fax: +52-55-5560-2190

TAITRON COMPONENTS INCORPORATED REPRESENTAÇÕES DO BRASIL LTDA

RUA DOMINGOS DE MORAIS, 2777, 2.ANDAR, SALA 24 SAÚDE - SÃO PAULO-SP 04035-001 BRAZIL

Tel: +55-11-5574-7949

Fax: +55-11-5572-0052

TAITRON COMPONENTS INCORPORATED, SHANGHAI REPRESENTATIVE OFFICE

METROBANK PLAZA, 1160 WEST YAN' AN ROAD, SUITE 1503, SHANGHAI, 200052, CHINA

Tel: +86-21-5424-9942

Fax: +86-21-5424-9931