





used for: DIN 41617

Art.-Nr. Part-No.	Polzahl No. of pos.	A -0.3	B ± 0.1	C ± 0.1
102A10049X	13	45.8	40	12x2.5=30
102A10069X	21	65.8	60	20x2.5=50
102A10089X	31	90.8	85	30x2.5=75

siehe Bemerkung 3
SEE NOTE 3Leiterplattenbohrbild
P.C.B.-HOLE DRILLINGS (b)

Bemerkung:

1. Isolierkörper: PC GF UL 94 V-1, grau (C)
2. Kontakte: Cu-Legierung
Veredelung: Au über Ni
3. Bedruckung: Art.-Nr. CONEC ABC

NOTES:

1. INSULATOR: PC GF UL 94 V-1, GREY (C)
2. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
3. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC Gmbh
DO NOT ALTER CAD DRAWING BY HAND

2 x c	Ä4154	08.11.2011	K.H.	d-old
1 x b	Ä3723	18.08.2010	K.H.	
a	Original			
rev.	description	date	name	

tolerance



scale:

2:1

material:

SEE NOTES

title:

FEMALE CONNECTOR
13-31pos.
with straight solder pins

dwg no:

10K1A002

DIN-A

3
sh: 1/1

part no:

SEE TABLE

CONEC®