


Push Switch

3.8mm-travel Push-push Type

SPED3/SPED4/SPED5 Series



Smooth and linear operation feeling.



Typical Specifications

Items	Specifications
Rating (Resistive load)	1A 14.5V DC
Contact resistance (Initial performance/After Test)	100mΩ max./100mΩ max.
Operating force	4.17±0.74N
Operating life (With load)	30,000cycles
Circuit configuration	1-pole, 2-positions

Product Line

Changeover timing	Total travel (mm)	Mounting method	Poles	Operation	Terminal type	Minimum order unit (pcs.)	Product No.	Drawing No.
Non shorting	3.8	Connector	1	Alternate	—	2,500	SPED310200	1
		PC board			For PC board	1,120	SPED420200	2
		With wire			—	960	SPED53※	3

Packing Specifications

Bulk

Product No.	Number of packages (pcs.)		Export package measurements (mm)
	1 case /Japan	1 case /export packing	
SPED310200	500	2,500	400×270×290
SPED420200	280	1,120	555×375×223
SPED53※	240	960	400×270×290

Notes

- ※If the wire length and color are not specified, length (terminal (1) and (2): 125mm, common terminal: 45mm), color can be specified from black, white, and light green freely.
- Please place purchase orders per minimum order unit N (integer).

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

Horizontal
Type






Vertical
Type




Automotive
Use

Dimensions

Unit:mm

No.	Style	Reference dimension of connection terminal (T=0.5~0.65mm)
1		
2		PC board mounting hole dimensions (Viewed from the direction A) 
3		

Circuit Diagram (Viewed from direction A)



Note

Factory setting for contact points can be either ① or ②.

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

Horizontal
Type

Vertical
Type



Automotive
Use

List of Varieties

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

Horizontal
Type

Vertical
Type

Series		SPPH2	SPPH4	SPPH1	SPEC	SPED2	SPED3	SPED4	SPED5	SPEF	
Photo											
Travel (mm)		1	2.2	1.5	2.5	—				1.5	
Total travel (mm)		1.5	3	2.5	3.4	4.5	3.8			2.7	
Number of poles		2					1				
Dimensions (mm)	W	6.5	8.5	10	12	14			13.5	9.4	
	D	6	6.5	10		16.8	18		18.2	9	
	H	6.5	8.5		12.5	26.7	20.7	16.97	20.7	6.9	
Operating temperature range		−10°C to +60°C			−40°C to +85°C						
Automotive use		—		●	●	●	●	●	●	●	●
Rating (max.) (Resistive load)		0.1A 12V DC	0.1A 30V DC			1A 14.5V DC					
Rating (min.) (Resistive load)		50μA 3V DC									
Electrical performance	Initial contact resistance	30mΩ max.	100mΩ max.	20mΩ max.	30mΩ max.	100mΩ max.					
	Insulation resistance	100MΩ min. 500V DC				3MΩ min. 500V DC			3MΩ min. 100VDC		
	Voltage proof	500V AC for 1minute				100V AC for 1minute					
Mechanical performance	Terminal strength	5N for 1minute			3N for 1minute	—					
	Actuator strength	Operating direction	30N		50N					90N	
		Pulling direction	—	10N	—	50N	—			30N	
Durability	Operating life without load	10,000cycles 50mΩ max.	10,000cycles 100mΩ max.	10,000cycles 40mΩ max.	10,000cycles 50mΩ max.	30,000cycles 100mΩ max.					
	Operating life without load Load:as rating										
Environmental performance	Cold	−20±2°C for 96h				−40±2°C for 96h					
	Dry heat	85±2°C for 96h									
	Damp heat	40±2°C, 90 to 95%RH for 96h									
Soldering	Manual soldering	350°C max. 3s max.	350±10°C 3 ⁺¹ ₀ s			350±10°C 3±0.5s ※3	—	350±10°C 3±0.5s	—	350±5°C 3s max.	
	Dip soldering	260±5°C 5±1s		260±5°C 10±1s	260°C max. 5s max.	260±5°C 10±1s ※3	—	260±5°C 10±1s	—	260±5°C 10±1s ※4	
	Reflow soldering	—									Please see P.127
Page		115	117	118	120	121	122			124	

- Push Switches Attached Parts126
- Push Switches Products Caution128

Notes

- ※3. Applicable to SPED220200(PC board type) only.
- ※4. Applicable to dip soldering.
- marks in "Available for automotive use" indicate that all of the series products can work at the operating temperature range from -40°C to +85°C.