





OPTION G




I.D. SLOT CODE TO WIRE GAUGE CHART	
I.D. SLOT CODE	WIRE GAUGE
D	22 AWG.

PLATING CODE (STRIPE ON CARRIER STRIP)	
PLATING	COLOR
TIN	NONE

SECTION C-C



- NOTES:
- MATERIAL:
HOUSING: POLYESTER(PBT), GLASS FILLED, UL94 V-0,
COLOR: BLACK
TERMINAL: PHOSPHOR BRONZE
 - FINISH:
TIN: 3.81 MICROMETERS/150 MICROINCHES MINIMUM TIN
OVER NICKEL UNDERPLATE OVERALL
 - TO BE USED WITH 22 AWG STRANDED WIRE WITH (1.35)/.053
DIAMETER MAXIMUM INSULATION
 - SEE TABLE FOR AVAILABLE CIRCUIT SIZES
 - STANDARD PACKAGING PER PK-70873-0001. OPTIONAL PACKAGING
MAY BE AVAILABLE, REQUEST DRAWING PK-70400
 - PARTS STACKABLE END TO END ON (2.54)/.100 CENTERS
 - PRODUCT SPECIFICATION: PS-70400
 - SEE DRAWING SDA-70400-**** (SHEET 3) FOR OPTIONAL
HOUSING DETAILS
 - 4 CIRCUIT SHOWN, 3-25 CIRCUITS HAVE 2 RIBS
 - TO MATE WITH MOLEX PART NUMBERS: A-70373-****,
A-70375-****, A-70389-****, A-70391-****,
A-70107-****, A-70018-****, A-70543-****,
A-70553-****, A-70541-****, A-70551-****,
A-70545-****, A-70555-****
 - 2 CIRCUIT ASSEMBLIES SUPPLIED AS GROUPED PAIRS



CKT. SIZE	A	B	EDP. NO.
2	(2.54) .100	(5.05) .199	I4-56-7022
3	(5.08) .200	(7.59) .299	I4-56-7032
4	(7.62) .300	(10.13) .399	I4-56-7042
5	(10.16) .400	(12.67) .499	I4-56-7052
6	(12.70) .500	(15.21) .599	I4-56-7062
7	(15.24) .600	(17.75) .699	I4-56-7072
8	(17.78) .700	(20.29) .799	I4-56-7082
9	(20.32) .800	(22.83) .899	I4-56-7092
10	(22.86) .900	(25.37) .999	I4-56-7102
11	(25.54) 1.000	(27.91) 1.099	I4-56-7112
12	(27.94) 1.100	(30.45) 1.199	I4-56-7122
13	(30.48) 1.200	(32.99) 1.299	I4-56-7132
14	(33.02) 1.300	(35.53) 1.399	I4-56-7142
15	(35.56) 1.400	(38.07) 1.499	I4-56-7152
16	(38.01) 1.500	(40.61) 1.599	I4-56-7162
17	(40.64) 1.600	(43.15) 1.699	I4-56-7172
18	(43.18) 1.700	(45.69) 1.799	I4-56-7182
19	(45.72) 1.800	(48.23) 1.899	I4-56-7192
20	(48.26) 1.900	(50.77) 1.999	I4-56-7202
21	(50.80) 2.000	(53.31) 2.099	I4-56-7212
22	(53.34) 2.100	(55.85) 2.199	I4-56-7222
23	(55.88) 2.200	(58.39) 2.299	I4-56-7232
24	(58.42) 2.300	(60.93) 2.399	I4-56-7242
25	(60.96) 2.400	(63.47) 2.499	I4-56-7252

REMOVE ENG NO. EC NO: UCP2011-110 DRWN:MS BARRA 2010/10/19 CHKD:J MORGAN 2010/10/19 APPR:SMILLER 2010/11/24	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY MSI BARRA	DATE 2010/10/20	TITLE ASSEMBLY, SL CONNECTOR SINGLE ROW 2.54/.100 GRID				
			4 PLACES	± ---	± ---	CHECKED BY WAZ	DATE 1987/10/26	molex MOLEX INCORPORATED				
			3 PLACES	± ---	± .010	APPROVED BY SMILLER	DATE 2010/11/24					
			2 PLACES	± 0.25	± .014	MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-70400-3140-3163		SHEET NO. 1 OF 1		
H	REV		ANGULAR ±1/2°			SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									