

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , -

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

E

DIST

B

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

B2

ECR-15-012328

19AUG2015

KR

TN

HB01AE

MARKING
FACE

28.8 max

2.9

3.0 max

LEAD LENGTH 20mm MIN

HB01AS

MARKING
FACE

26.0 max

8.4 max

1.5 max

LEAD LENGTH 20mm MIN

DESCRIPTION:
LEAD MATERIAL:
LEAD CROSS-SECTION:
HYBRID PROTECTION:
MARKING:


HIGH VOLTAGE THICK FILM RESISTOR.
TINNED COPPER WIRE
0.6 +/-0.05 DIA
CONFORMAL EPOXY COATING
AS SHOWN BELOW ON MARKING FACE

DESCRIPTION:
LEAD MATERIAL:
LEAD CROSS-SECTION:
HYBRID PROTECTION:
MARKING:

HIGH VOLTAGE THICK FILM RESISTOR.
TINNED COPPER WIRE
0.6 +/-0.05 DIA
SCREEN PRINTED SILICONE COATING
AS SHOWN BELOW ON MARKING FACE

HB01A
VAL. TOL. TCR
DATE CODE

HB01A
VAL. TOL. TCR
DATE CODE



TYPICAL SCHEMATIC

FOR A SPECIFIC PN FOR A RESISTANCE VALUE
AND TOLERANCE, PLEASE REFER TO DMF.

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

0 PLC	\pm -
1 PLC	\pm -
2 PLC	\pm -
3 PLC	\pm -
4 PLC ANGLES	\pm -

MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

-

PRODUCT SPEC
—
APPLICATION SPEC

FINISH

-

WEIGHT

-

CUSTOMER DRAWING

DWN 31OCT2005

DAVE KENNEDY

CHK 01NOV05

J CATCHPOLE

APVD 01NOV05

J CATCHPOLE

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING



TE Connectivity

NAME HB01

—

—

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1625958

—

SCALE

NTS

SHEET

1 OF 2

REV

B2

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS		
		P	LTR	DESCRIPTION
E	B	-	-	SEE SHEET 1




DESCRIPTION: HIGH VOLTAGE THICK FILM RESISTOR.
 LEAD MATERIAL: TINNED COPPER WIRE
 LEAD CROSS-SECTION: 0.6 +/-0.05 DIA
 HYBRID PROTECTION: CONFORMAL EPOXY COATING
 MARKING: AS SHOWN BELOW ON MARKING FACE

HB01R
VAL. TOL. TCR
DATE CODE

DESCRIPTION: HIGH VOLTAGE THICK FILM RESISTOR.
 LEAD MATERIAL: TINNED COPPER WIRE
 LEAD CROSS-SECTION: 0.6 +/-0.05 DIA
 HYBRID PROTECTION: SCREEN PRINTED SILICONE COATING
 MARKING: AS SHOWN BELOW ON MARKING FACE

HB01R
VAL. TOL. TCR
DATE CODE



TYPICAL SCHEMATIC

FOR A SPECIFIC PN FOR A RESISTANCE VALUE
 AND TOLERANCE, PLEASE REFER TO DMF.

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVE KENNEDY CHK J CATCHPOLE APVD J CATCHPOLE	31OCT2005 01NOV05 01NOV05	TE Connectivity
DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	—	—	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES	± - ± - ± - ± - ± - ± -	PRODUCT SPEC —	APPLICATION SPEC —	
MATERIAL	FINISH	WEIGHT	DRAWING NO	RESTRICTED TO
-	-	-	A300779C-1625958	-
CUSTOMER DRAWING				SCALE NTS SHEET 2 OF 2 REV B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HB01RE-100M](#)