


BZT55C- Series



Features:

- Zener voltage range 2.0 to 75 volts.
- Mini-MELF package.
- Surface device type mounting.
- Hermetically sealed glass.
- Compression Bonded Construction.
- All external surfaces are corrosion resistant and terminals are readily solderable.
- RoHS compliant.
- Matte Tin (Sn) lead finish.
- Blue color band indicates negative polarity.


Maximum Ratings and Electrical Characteristics

Type Number	Symbol	Value	Units
Power Dissipation	P_D	500	mW
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to + 200	$^{\circ}\text{C}$


Notes : These ratings are limiting values above which the serviceability of the diode may be impaired.

Ratings and Characteristic Curves


Total Power Dissipation vs. Ambient Temperature




Temperature Coefficient of V_Z vs. Z-Voltage




Typical Change of Working Voltage under Operating Conditions at $T_{amb} = 25^{\circ}\text{C}$




Diode Capacitance vs. Z - Voltage




Typical Change of Working Voltage vs. Junction Temperature




Forward Current vs. Forward Voltage




Z-Current vs. Z-Voltage




Differential Z - Resistance vs. Z-Voltage



Z-Current vs. Z-Voltage



Thermal Response



Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

V _Z at I _{ZT} (Volts)		I _{ZT} mA	Z _{ZT} at I _{ZT} Ohms Maximum	I _{ZK} mA	Z _{ZK} at I _{ZK} Ohms	I _R at V _R uA Maximum	V _R V	Part Number
V _Z Minimum (V)	V _Z Maximum (V)							
9.4	10.6	5	15	1.0	70	0.1	7.5	BZT55C10
10.4	11.6		20		8.2		BZT55C11	
11.4	12.7		26		9.1		BZT55C12	
12.4	14.1		30		10		BZT55C13	
13.8	15.6		40		11		BZT55C15	
15.3	17.1		50		12		BZT55C16	
16.8	19.1		55		13		BZT55C18	
18.8	21.1		80		15		BZT55C20	
20.8	23.3		80		16		BZT55C22	
22.8	25.6		80		18		BZT55C24	
25.1	28.9	2	80	220	20	BZT55C27		
1.88	2.11	5	100	600	50	1.0	BZT55C2V0	
2.08	2.33		85				BZT55C2V2	
2.28	2.56		85		BZT55C2V4			
2.51	2.89		85		BZT55C2V7			
28	32	2	80	220	0.1	22	BZT55C30	
31	35					24	BZT55C33	
34	38					27	BZT55C36	
37	41		90	28		BZT55C39		
2.8	3.2	5	85	1.0	600	4	1.0	BZT55C3V0
3.1	3.5					2		BZT55C3V3
3.4	3.8							BZT55C3V6
3.7	4.1							BZT55C3V9
40	46	2	90	0.5	700	0.1	35	BZT55C43
44	50		110					BZT55C47
4.0	4.6	5	75	1.0	600	2	1.0	BZT55C4V3
4.4	5.0		60			0.5		BZT55C4V7
48	54	2	125	0.5	700	0.1	38	BZT55C51
52	60		135		1000		42	BZT55C56
4.8	5.4	5	35	1.0	550		1.0	BZT55C5V1
5.2	6.0		25		450			BZT55C5V6
58	66	2.5	150	0.5	1000		47	BZT55C62

BZT55C- Series



Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

V _Z at I _{ZT} (Volts)		I _{ZT} mA	Z _{ZT} at I _{ZT} Ohms Maximum	I _{ZK} mA	Z _{ZK} at I _{ZK} Ohms	I _R at V _R uA Maximum	V _R V	Part Number
V _Z Minimum (V)	V _Z Maximum (V)							
64	72	2.5	160	0.5	1000	0.1	51	BZT55C68
5.8	6.6	5	10	1.0	200		2.0	BZT55C6V2
6.4	7.2		8		150		3.0	BZT55C6V8
70	80	2.5	170	0.5	1000		56	BZT55C75
7.0	7.9	5	7	1.0	50		5.0	BZT55C7V5
7.7	8.7						6.2	BZT55C8V2
8.5	9.6		10				6.8	BZT55C9V1

V_F Forward Voltage = 1.0v Maximum at $I_F = 100\text{mA}$ for all types.

- Notes : 1. The type numbers listed have zener voltage min/max limits as shown.
 2. The zener impedance is derived from the 60-cycle ac voltage, which results when an ac current having an rms value equal to 10% of the dc zener current (I_{ZT} or I_{ZK}) is superimposed to I_{ZT} or I_{ZK} .



BZT55C- Series



Notes:

International Sales Offices:



AUSTRALIA - Farnell

Tel No: ++61 1300 361 005
Fax No: ++61 1300 361 225



FINLAND - Farnell

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



ITALY - Farnell

Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN - Farnell

Tel No: 901 20 20 80
Fax No: 901 20 20 90



AUSTRIA - Farnell

Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE - Farnell

Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



MALAYSIA - Farnell-Newark

Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN - Farnell

Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62



BELGIUM - Farnell

Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY - Farnell

Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NETHERLANDS - Farnell

Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND - Farnell

Tel No: ++ 44 204 64 64
Fax No: ++ 44 204 64 54



BRAZIL - Farnell-Newark

Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG - Farnell-Newark

Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



NEW ZEALAND - Farnell

Tel No: 0800 90 80 80
Fax No: 0800 90 80 81



UK - Farnell

Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



CHINA - Farnell-Newark

Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



HUNGARY - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



NORWAY - Farnell

Tel No: 800 146 70
Fax No: 800 146 76



UK - CPC

++ 44 8701 202 530
++ 44 8701 202 531



CZECH REPUBLIC - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



INDIA - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



PORTUGAL - Farnell

Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



USA - Newark

Tel No: 800 463 9275



DENMARK - Farnell

Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



IRELAND - Farnell

Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



RUSSIA - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



EXPORT - Farnell

Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



ESTONIA - Farnell

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



ISRAEL - Farnell

Tel No: ++ 180 937 0015
Fax No: ++ 180 937 0014



SINGAPORE - Farnell-Newark

Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300

<http://www.farnell.com>

<http://www.newark.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.

