



Normally closed
SOP6-pin type
of 400V load voltage

PhotoMOS[®]
GU SOP 1 Form B
(AQV414S)



mm inch




RoHS compliant

FEATURES


1. Miniature SOP6-pin package

The device comes in a small SOP measuring (W) 4.4 × (L) 6.3 × (H) 2.1 mm (W) .173 × (L) .248 × (H) .083 inch approx. 25% of the volume and 50% of the footprint size of DIP type.



2. Low on-resistance (typ. 26 Ω) for normally-closed type

This has been achieved thanks to the built-in MOSFET processed by our proprietary method, DSD (Double-Diffused and Selective Doping) method.



3. Controls low-level analog signals

PhotoMOS feature extremely low closed-circuit offset voltage to enable control of low-level analog signals without distortion.

4. Low-level off state leakage current of max. 1 μA

TYPICAL APPLICATIONS

- Telephones
- Measuring instruments
- Computers
- Industrial robots
- High-speed inspection machines

TYPES

| | Output rating* | | Package | Part No. | | | Packing quantity | |
|----------------|----------------|--------------|----------|--------------------|--------------------------------|--------------------------------|--|---------------|
| | Load voltage | Load current | | Tube packing style | Tape and reel packing style | | Tube | Tape and reel |
| | | | | | Picked from the 1/2/3-pin side | Picked from the 4/5/6-pin side | | |
| AC/DC dual use | 400V | 100mA | SOP6-pin | AQV414S | AQV414SX | AQV414SZ | 1 tube contains: 75 pcs. 1 batch contains: 1,500 pcs. | 1,000 pcs. |

* Indicate the peak AC and DC values.

Note: For space reasons, only "V41S" is marked on the product. The two initial letters of the part number "AQ" and the packing style indicator "X" or "Z" have been omitted.

RATING


1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)

| Item | | Symbol | Type of connection | AQV414S | Remarks |
|-----------------------|-------------------------|-------------------|--------------------|---------------------------------|---|
| Input | LED forward current | I _F | | 50 mA | |
| | LED reverse voltage | V _R | | 5 V | |
| | Peak forward current | I _{FP} | | 1 A | f = 100 Hz, Duty factor = 0.1% |
| | Power dissipation | P _{in} | | 75 mW | |
| Output | Load voltage (peak AC) | V _L | | 400 V | |
| | Continuous load current | I _L | A | 0.10 A | A connection: Peak AC, DC B, C connection: DC |
| | | | B | 0.11 A | |
| | | | C | 0.12 A | |
| | Peak load current | I _{peak} | | 0.3 A | A connection: 100 ms (1 shot) V _L = DC |
| | Power dissipation | P _{out} | | 450 mW | |
| | Total power dissipation | | | P _T | 500 mW |
| I/O isolation voltage | | V _{iso} | | 1,500 V AC | |
| Temperature limits | Operating | T _{opr} | | −40°C to +85°C −40°F to +185°F | Non-condensing at low temperatures |
| | Storage | T _{stg} | | −40°C to +100°C −40°F to +212°F | |

2. Electrical characteristics (Ambient temperature: 25°C 77°F)

| Item | | | Symbol | Type of connection | AQV414S | Remarks | |
|----------------------------------|---------------------------|---------------------|-------------------|--------------------|--|--|---|
| Input | LED operate (OFF) current | Typical | I_{Foff} | — | 0.6 mA | I_{L} = Max. | |
| | | Maximum | | | 3 mA | | |
| | LED reverse (ON) current | Minimum | I_{Fon} | — | 0.4 mA | I_{L} = Max. | |
| | | Typical | | | 0.55 mA | | |
| | LED dropout voltage | Typical | V_{F} | — | 1.25 V (1.14 V at I_{F} = 5 mA) | | I_{F} = 50 mA |
| | | Maximum | | | 1.5 V | | |
| Output | On resistance | Typical | R_{on} | A | 26 Ω | I_{F} = 0 mA I_{L} = Max. Within 1 s on time | |
| | | Maximum | | | 50 Ω | | |
| | | Typical | R_{on} | B | 20 Ω | I_{F} = 0 mA I_{L} = Max. Within 1 s on time | |
| | | Maximum | | | 25 Ω | | |
| | | Typical | R_{on} | C | 10 Ω | I_{F} = 0 mA I_{L} = Max. Within 1 s on time | |
| | | Maximum | | | 12.5 Ω | | |
| | Off state leakage current | Maximum | I_{Leak} | — | 1 μA | I_{F} = 5 mA, V_{L} = Max. | |
| | Transfer characteristics | Operate (OFF) time* | Typical | T_{off} | — | 0.47 ms | I_{F} = 0 mA \rightarrow 5 mA V_{L} = Max. |
| Maximum | | | 1.0 ms | | | | |
| Reverse (ON) time* | | Typical | T_{on} | — | 0.28 ms | I_{F} = 5 mA \rightarrow 0 mA V_{L} = Max. | |
| | | Maximum | | | 1.0 ms | | |
| I/O capacitance | | Typical | C_{iso} | — | 0.8 pF | f = 1 MHz V_{B} = 0 V | |
| | | Maximum | | | 1.5 pF | | |
| Initial I/C isolation resistance | Minimum | R_{iso} | — | 1,000 M Ω | 500 V DC | | |

*Operate/Reverse time



RECOMMENDED OPERATING CONDITIONS

Please obey the following conditions to ensure proper device operation and resetting.

| Item | Symbol | Recommended value | Unit |
|-------------------|----------------|-------------------|------|
| Input LED current | I _F | 5 | mA |

■ For Dimensions.

■ For Schematic and Wiring Diagrams.

■ For Cautions for Use.

■ These products are not designed for automotive use.

If you are considering to use these products for automotive applications, please contact your local Panasonic Corporation technical representative.

For more information.


GU SOP 1 Form B (AQV414S)

REFERENCE DATA

1. Load current vs. ambient temperature characteristics


Allowable ambient temperature: -40°C to $+85^{\circ}\text{C}$
 -40°F to $+185^{\circ}\text{F}$

Type of connection: A




2. On resistance vs. ambient temperature characteristics

Measured portion: between terminals 4 and 6;
 LED current: 0 mA;
 Continuous load current: 100 mA (DC)




3. Operate (OFF) time vs. ambient temperature characteristics

LED current: 5 mA;
 Load voltage: 400 V (DC);
 Continuous load current: 100 mA (DC)




4. Reverse (ON) time vs. ambient temperature characteristics

LED current: 50 mA;
 Load voltage: 400 V (DC);
 Continuous load current: 100 mA (DC)




5. LED operate (OFF) current vs. ambient temperature characteristics

Load voltage: 400 V (DC);
 Continuous load current: 100 mA (DC)




6. LED reverse (ON) current vs. ambient temperature characteristics

Load voltage: 400 V (DC);
 Continuous load current: 100 mA (DC)




7. LED dropout voltage vs. ambient temperature characteristics

LED current: 5 to 50 mA




8. Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 4 and 6;
 Ambient temperature: 25°C 77°F




9. Off state leakage current vs. load voltage characteristics

Measured portion: between terminals 4 and 6;
 LED current: 5 mA;
 Ambient temperature: 25°C 77°F




10. Operate (OFF) time vs. LED forward current characteristics

Measured portion: between terminals 4 and 6;
Load voltage: 400 V (DC); Continuous load current:
100 mA (DC); Ambient temperature: 25°C 77°F



11. Reverse (ON) time vs. LED forward current characteristics

Measured portion: between terminals 4 and 6;
Load voltage: 400 V (DC); Continuous load current:
100 mA (DC); Ambient temperature: 25°C 77°F



12. Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 4 and 6;
Frequency: 1 MHz;
Ambient temperature: 25°C 77°F

