




Telecommunication

HDSL Transformer





Transformers

DT31-2010AT
DT31-2010BT
DT31-2016AT
DT31-2005

• DT31-20XXXX
DELTAXXXX



XXXX : DATE CODE
WHITE DOT ON PIN1



DIMENSIONS IN mm

A	B	C	D	E	F	G
12.7 MAX.	2.79 MIN.	14.0 MAX.	14.0 MAX.	10.16 ±0.3	2.54 ±0.3	

ELECTRICAL CHARACTERISTICS

	DT31-2010AT	DT31-2010BT	DT31-2016AT	DT31-2005
T.R	(PRI:SEC): 2:1 ± 1% @10KHz 0.1V	(PRI:SEC): 2:1 ± 1% @10KHz 0.1V	(PRI:SEC): 1:1 ± 1% @10KHz 0.1V	(PRI:SEC): 2:1 ± 1% @10KHz 0.1V
L	PRI: 3.0mH ± 6% @10KHz 0.1V, Idc=160mA	PRI: 3.0mH ± 10% @10KHz 0.1V, Idc=160mA	PRI: 3.0mH ± 5% @10KHz 0.1V	PRI: 3.0mH ± 6% @10KHz 0.1V, Idc=100mA
L.K	PRI: 11uH Max. @100KHz 0.1V	PRI: 11uH Max. @100KHz 0.1V	PRI: 20uH Max. @100KHz 0.1V	PRI: 11uH Max. @100KHz 0.1V
D.C.R	PRI: 2.5 Ω Max. SEC: 1.0 Ω Max.	PRI: 2.5 Ω Max. SEC: 1.0 Ω Max.	N1: 0.95 Ω ± 10% N2: 0.95 Ω ± 10% N3: 1.87 Ω ± 10%	PRI: 2.5 Ω Max. SEC: 1.0 Ω Max.
HI-POT	1500 VAC 1 SEC	1500 VAC 1 SEC	1500 VAC 1 SEC	2050 VAC 1 SEC
C	-----	-----	-----	-----
I.L	0.4 dB Max. @200KHz	0.4 dB Max. @200KHz	-----	0.4 dB Max. @200KHz
L.B	53dB Min. @40KHz~200KHz	53dB Min. @40KHz~200KHz	53dB Min. @40KHz~300KHz	53dB Min. @40KHz~200KHz
FR	± 0.1 dB @40KHz~200KHz	± 0.1 dB @40KHz~200KHz	-----	± 0.1 dB @40KHz~200KHz
R.L	20 dB Min. @40KHz~200KHz	20 dB Min. @40KHz~200KHz	-----	20 dB Min. @40KHz~200KHz
T.H.D	-70 dB Max. @40KHz 14dBm	-70 dB Max. @40KHz 14dBm	-70 dB Max. @100KHz 5Vp-p	-70 dB Max. @40KHz 14dBm
SCHEMATIC	3	4	1	2

DELTA ELECTRONICS, INC.

(TAOYUAN PLANT CPBG) 31-1, SHIEN PAN ROAD, KUEI SAN INDUSTRIAL ZONE, TAOYUAN SHIEN, TAIWAN, R.O.C.
TEL: 886-3-3626301 FAX: 886-3-3618901
<http://www.deltaww.com>