

Product Summary

V _{BR} (Min)	I _{PP} (Max)	C _{in} /o (Typ)
5.5V	3.5A	0.45pF

Description

The D5V0FS4U10LP is a high-performance device suitable for protecting four high speed I/Os. These devices are assembled in U-DFN2510-10 package and have high ESD surge capability, low ESD clamping voltage and ultra-low capacitance.

Applications

Typically used at high-speed ports such as USB 3.0, USB 3.1, Serial ATA, Display port.

Features


- Clamping Voltage: 6V at 16A TLP
- IEC 61000-4-2 (ESD): Air — $\pm 8\text{kV}$, Contact — $\pm 8\text{kV}$
- IEC 61000-4-5 (Lightning): 3.5A (8/20 μs)
- 4 Channels of ESD Protection
- Ultra-Low Channel Input Capacitance of 0.45pF Typical
- TLP Dynamic Resistance: 0.25Ω
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- Halogen and Antimony Free. "Green" Device (Note 3)**

Mechanical Data


- Case: U-DFN2510-10
- Case Material: Molded Plastic, "Green" Molding Compound.
- UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: NiPdAu over Copper Leadframe (Lead Free Plating). Solderable per MIL-STD-202, Method 208 ^(e4)
- Weight: 0.038 grams (Approximate)

U-DFN2510-10

Pin #	Description
1, 2, 4, 5	I/O
6, 7, 9, 10	No Connection
3, 8	Vss



Pin Description (Top View)



Device Schematic

Ordering Information (Note 4)

Part Number	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity
D5V0FS4U10LP-7	Standard	NZ1	7	8	3,000/Tape & Reel

Notes:

- No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

Marking Information

U-DFN2510-10



NZ1 = Product Type Marking Code
 YM = Date Code Marking
 Y = Year (ex: E = 2017)
 M = Month (ex: 9 = September)

Date Code Key

Year	2017	2018	2019	2020	2021	2022
Code	E	F	G	H	I	J

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D

Maximum Ratings (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	Conditions
Peak Pulse Current, per IEC 61000-4-5	I_{PP}	3.5	A	I/O to V_{SS} , 8/20 μs
Peak Pulse Power, per IEC 61000-4-5	P_{PP}	20	W	I/O to V_{SS} , 8/20 μs
ESD Protection – Contact Discharge, per IEC 61000-4-2	$V_{ESD_CONTACT}$	± 8	kV	I/O to V_{SS}
ESD Protection – Air Discharge, per IEC 61000-4-2	V_{ESD_AIR}	± 8	kV	I/O to V_{SS}

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation Typical (Note 5)	P_D	350	mW
Thermal Resistance, Junction to Ambient Typical (Note 5)	$R_{\theta JA}$	360	°C/W
Operating and Storage Temperature Range	T_J, T_{STG}	-55 to +150	°C

Electrical Characteristics (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Conditions
Reverse Working Voltage	V_{RWM}	—	—	5	V	—
Reverse Current	I_R	—	—	1	μA	$V_R = 5\text{V}$, I/O to V_{SS}
Reverse Breakdown Voltage	V_{BR}	5.5	7.0	—	V	$I_R = 1\text{mA}$, I/O to V_{SS}
Forward Clamping Voltage	V_F	-1.0	-0.85	—	V	$I_F = -15\text{mA}$, I/O to V_{SS}
Holding Reverse Voltage	V_{HOLD}	—	1.19	—	V	I/O to V_{SS}
Holding Reverse Current	I_{HOLD}	—	90	—	mA	I/O to V_{SS}
Reverse Clamping Voltage (Note 6)	V_C	—	3	—	V	$I_{PP} = 3\text{A}$, I/O to V_{SS} , 8/20 μs
Clamping Voltage (Note 7)	V_C	—	6	—	V	TLP, 16A, $tp = 100\text{ns}$, I/O to V_{SS}
Clamping Voltage (Note 7)	V_C	—	4.5	—	V	TLP, -16A, $tp = 100\text{ns}$, I/O to V_{SS}
Dynamic Reverse Resistance	R_{DIF-R}	—	0.25	—	Ω	TLP, 10A, $tp = 100\text{ns}$, I/O to V_{SS}
Dynamic Forward Resistance	R_{DIF-F}	—	0.2	—	Ω	TLP, 10A, $tp = 100\text{ns}$, V_{SS} to I/O
Channel Input Capacitance	$C_{I/O}$	—	0.45	—	pF	$V_{I/O} = 0\text{V}$, $V_{SS} = 0\text{V}$, $f = 1\text{MHz}$

Notes:

5. Device mounted on FR-4 PCB pad layout (2oz copper) as shown on Diodes Incorporated's suggested pad layout, which can be found on our website at <http://www.diodes.com/package-outlines.html>.
6. Clamping voltage value is based on an 8x20 μs peak pulse current (I_{PP}) waveform.
7. Clamping voltage value is based on a TLP model. TLP conditions: $Z_0=50\Omega$, $tp = 100\text{ns}$, averaging window; $t1=70\text{ns}$ to $t2=90\text{ns}$.




Figure 1. Pulse Derating Curve




Figure 2. Input Capacitance vs. Input Voltage





Figure 3. Current vs. Voltage

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

U-DFN2510-10




U-DFN2510-10			
Dim	Min	Max	Typ
A	0.545	0.605	0.575
A1	0.00	0.05	0.03
A3	-	-	0.13
b	0.15	0.25	0.20
b1	0.35	0.45	0.40
D	2.450	2.575	2.500
e	-	-	0.50
E	0.950	1.075	1.000
L	0.325	0.425	0.375
z	-	-	0.150

All Dimensions in mm

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

U-DFN2510-10



Dimensions	Value (in mm)
C	0.500
X	0.250
X1	0.450
X2	2.250
Y	0.625
Y1	0.575
Y2	0.700
Y3	1.400

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com