

< IGBT MODULES >

CM400DY-34A

HIGH POWER SWITCHING USE
INSULATED TYPE



Dual (Half-Bridge)

Collector current I_C **400 A**
 Collector-emitter voltage V_{CES} **1700 V**
 Maximum junction temperature T_{jmax} **150 °C**


- Flat base Type
- Copper base plate (non-plating)
- RoHS Directive compliant
- UL Recognized under UL1557, File E323585

APPLICATION

AC Motor Control, Motion/Servo Control, Power supply, etc.

OUTLINE DRAWING & INTERNAL CONNECTION

Dimension in mm




TERMINAL SCREW HOLE DEPTH

	L	M
A	16	7
B	19	7
C	10	3.5

Tolerance otherwise specified

Division of Dimension	Tolerance
0.5 to 3	±0.2
over 3 to 6	±0.3
over 6 to 30	±0.5
over 30 to 120	±0.8
over 120 to 400	±1.2

INTERNAL CONNECTION



< IGBT MODULES >

CM400DY-34A

HIGH POWER SWITCHING USE
INSULATED TYPEABSOLUTE MAXIMUM RATINGS ($T_J=25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Symbol	Item	Conditions	Rating	Unit
V_{CES}	Collector-emitter voltage	G-E short-circuited	1700	V
V_{GES}	Gate-emitter voltage	C-E short-circuited	± 20	V
I_C	Collector current	DC, $T_C=107\text{ }^{\circ}\text{C}$ (Note.2, 4)	400	A
I_{CRM}		Pulse, Repetitive (Note.3)	800	
P_{tot}	Total power dissipation	$T_C=25\text{ }^{\circ}\text{C}$ (Note.2, 4)	3780	W
I_E (Note.1)	Emitter current	$T_C=25\text{ }^{\circ}\text{C}$ (Note.2, 4)	400	A
I_{ERM} (Note.1)		Pulse, Repetitive (Note.3)	800	
T_J	Junction temperature	-	$-40 \sim +150$	$^{\circ}\text{C}$
T_{stg}	Storage temperature	-	$-40 \sim +125$	
V_{isol}	Isolation voltage	Terminals to base plate, RMS, f=60 Hz, AC 1 min	3500	V

ELECTRICAL CHARACTERISTICS ($T_J=25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
I_{CES}	Collector-emitter cut-off current	$V_{CE}=V_{CES}$, G-E short-circuited	-	-	1.0	mA
I_{GES}	Gate-emitter leakage current	$V_{GE}=V_{GES}$, C-E short-circuited	-	-	2.0	μA
$V_{GE(th)}$	Gate-emitter threshold voltage	$I_C=40\text{ mA}$, $V_{CE}=10\text{ V}$	5.5	7.0	8.5	V
V_{CEsat}	Collector-emitter saturation voltage	$I_C=400\text{ A}$ (Note.5), $T_J=25\text{ }^{\circ}\text{C}$	-	2.2	2.8	V
		$V_{GE}=15\text{ V}$, $T_J=125\text{ }^{\circ}\text{C}$	-	2.45	-	
C_{ies}	Input capacitance	$V_{CE}=10\text{ V}$, G-E short-circuited	-	-	98.8	nF
C_{oes}	Output capacitance		-	-	11.2	
C_{res}	Reverse transfer capacitance		-	-	2.1	
Q_G	Gate charge	$V_{CC}=1000\text{ V}$, $I_C=400\text{ A}$, $V_{GE}=15\text{ V}$	-	2670	-	nC
$t_{d(on)}$	Turn-on delay time	$V_{CC}=1000\text{ V}$, $I_C=400\text{ A}$, $V_{GE}=\pm 15\text{ V}$, $R_G=1.2\text{ }\Omega$, Inductive load	-	-	950	ns
t_r	Rise time		-	-	300	
$t_{d(off)}$	Turn-off delay time		-	-	1000	
t_f	Fall time		-	-	350	
V_{EC} (Note.1)	Emitter-collector voltage	$I_E=400\text{ A}$ (Note.5), G-E short-circuited	-	2.3	3.0	V
t_{rr} (Note.1)	Reverse recovery time	$V_{CC}=1000\text{ V}$, $I_E=400\text{ A}$, $V_{GE}=\pm 15\text{ V}$, $R_G=1.2\text{ }\Omega$, Inductive load	-	-	450	ns
Q_{rr} (Note.1)	Reverse recovery charge	$R_G=1.2\text{ }\Omega$, Inductive load	-	40	-	μC
E_{on}	Turn-on switching energy per pulse	$V_{CC}=1000\text{ V}$, $I_C=I_E=400\text{ A}$, $V_{GE}=\pm 15\text{ V}$, $R_G=1.2\text{ }\Omega$, $T_J=125\text{ }^{\circ}\text{C}$,	-	197.3	-	mJ
E_{off}	Turn-off switching energy per pulse	Inductive load	-	117.9	-	
E_{rr} (Note.1)	Reverse recovery energy per pulse	Inductive load	-	98.5	-	mJ
r_g	Internal gate resistance	Per switch, $T_c=25\text{ }^{\circ}\text{C}$	-	3.7	-	Ω

THERMAL RESISTANCE CHARACTERISTICS

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
$R_{th(j-c)Q}$	Thermal resistance (Note.2)	Junction to case, per IGBT	-	-	33	K/kW
$R_{th(j-c)D}$		Junction to case, per FWDi	-	-	55	K/kW
$R_{th(c-s)}$	Contact thermal resistance (Note.2)	Case to heat sink, per 1/2 module, Thermal grease applied (Note.6)	-	19	-	K/kW

MECHANICAL CHARACTERISTICS

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
M_t	Mounting torque	Main terminals M 8 screw	8.8	9.7	10.8	N·m
		Auxiliary (G, E) terminals M 4 screw	1.3	1.5	1.7	
M_s		Mounting to heat sink M 6 screw	3.5	4.0	4.5	N·m
m	Weight	-	-	1200	-	g
e_c	Flatness of base plate	On the centerline X, Y (Note.7)	-100	-	+100	μm

Note1. Represent ratings and characteristics of the anti-parallel, emitter-collector free wheeling diode (FWDi).

2. Case temperature (T_c) and heat sink temperature (T_s) are defined on the each surface (mounting side) of base plate and heat sink just under the chips. Refer to the figure of chip location.

The heat sink thermal resistance should measure just under the chips.


3. Pulse width and repetition rate should be such that the device junction temperature (T_j) dose not exceed T_{jmax} rating.

4. Junction temperature (T_j) should not increase beyond T_{jmax} rating.

5. Pulse width and repetition rate should be such as to cause negligible temperature rise. Refer to the figure of test circuit.

6. Typical value is measured by using thermally conductive grease of $\lambda=0.9 \text{ W/(m}\cdot\text{K)}$.

7. Base plate (mounting side) flatness measurement points (X, Y) are as follows of the following figure.




RECOMMENDED OPERATING CONDITIONS

Symbol	Item	Conditions	Limits			Unit
			Min.	Typ.	Max.	
V_{CC}	(DC) Supply voltage	Applied across C1-E2	-	1000	1100	V
V_{GEon}	Gate (-emitter drive) voltage	Applied across G1-Es1/G2-Es2	13.5	15.0	16.5	V
R_G	External gate resistance	Per switch	1.2	-	12	Ω

CHIP LOCATION (Top view)


Dimension in mm, tolerance: $\pm 1 \text{ mm}$



Tr1/Tr2: IGBT, Di1/Di2: FWDi






< IGBT MODULES >
CM400DY-34A
HIGH POWER SWITCHING USE
INSULATED TYPE

TEST CIRCUIT AND WAVEFORMS



V_{CEsat} test circuit


V_{EC} test circuit




Turn-on / Turn-off switching energy and Reverse recovery energy test waveforms (Integral time instruction drawing)

PERFORMANCE CURVES


OUTPUT CHARACTERISTICS
(TYPICAL)




COLLECTOR-EMITTER SATURATION
VOLTAGE CHARACTERISTICS
(TYPICAL)







COLLECTOR-EMITTER SATURATION
VOLTAGE CHARACTERISTICS
(TYPICAL)







FREE WHEELING DIODE
FORWARD CHARACTERISTICS
(TYPICAL)



PERFORMANCE CURVES

HALF-BRIDGE
SWITCHING CHARACTERISTICS
(TYPICAL)
 $V_{CC}=1000\text{ V}$, $V_{GE}=\pm 15\text{ V}$, $R_G=1.2\ \Omega$,
 $T_J=125\text{ }^\circ\text{C}$, INDUCTIVE LOAD
HALF-BRIDGE
SWITCHING CHARACTERISTICS
(TYPICAL)
 $V_{CC}=1000\text{ V}$, $I_C=400\text{ A}$, $V_{GE}=\pm 15\text{ V}$,
 $T_J=125\text{ }^\circ\text{C}$, INDUCTIVE LOAD
HALF-BRIDGE
SWITCHING CHARACTERISTICS
(TYPICAL)
 $V_{CC}=1000\text{ V}$, $V_{GE}=\pm 15\text{ V}$, $R_G=1.2\ \Omega$, $T_J=125\text{ }^\circ\text{C}$
 INDUCTIVE LOAD, PER PULSE
HALF-BRIDGE
SWITCHING CHARACTERISTICS
(TYPICAL)
 $V_{CC}=1000\text{ V}$, $I_C/I_E=400\text{ A}$, $V_{GE}=\pm 15\text{ V}$, $T_J=125\text{ }^\circ\text{C}$
 INDUCTIVE LOAD, PER PULSE


PERFORMANCE CURVES

CAPACITANCE CHARACTERISTICS
(TYPICAL)G-E short-circuited, $T_j=25^\circ\text{C}$ FREE WHEELING DIODE
REVERSE RECOVERY CHARACTERISTICS
(TYPICAL) $V_{CC}=1000\text{ V}$, $V_{GE}=\pm 15\text{ V}$, $R_G=1.2\ \Omega$,
 $T_j=25^\circ\text{C}$, INDUCTIVE LOADGATE CHARGE CHARACTERISTICS
(TYPICAL) $I_C=400\text{ A}$, $T_j=25^\circ\text{C}$ TRANSIENT THERMAL IMPEDANCE CHARACTERISTICS
(MAXIMUM)Single pulse, $T_C=25^\circ\text{C}$
 $R_{th(j-c)Q}=33\text{ K/kW}$, $R_{th(j-c)D}=55\text{ K/kW}$ 

Keep safety first in your circuit designs!

Mitsubishi Electric Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- These materials are intended as a reference to assist our customers in the selection of the Mitsubishi semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Mitsubishi Electric Corporation by various means, including the Mitsubishi Semiconductor home page (www.MitsubishiElectric.com/semiconductors/).
- When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Mitsubishi Electric Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor for further details on these materials or the products contained therein.