

## FEED-THROUGH FLAT BASE Panel Mount

For wire-to-wire connections in HVAC, appliance, equipment, power distribution and other industrial applications with strict budget and space requirements. Easy to use double row terminal strips are a cost-effective alternative to barrier strips or other types of terminal blocks. Simply strip the wire, insert and tighten the screw. Eurostrips feature tubular screw clamps, with wire protectors, and recessed metal parts for finger protection. The stainless steel wire protectors exhibit excellent memory and the most effective connection.

Eurostrips described on this and the following page are available with a flat base for minimum clearance applications. They can be panel mounted or left to free float. Offered in easy-to-cut standard 12-pole strips, they can also be ordered precut with the required number of poles.

- Tubular screw clamp
- Panel mount or free float
- Housing material:
  - Polyamide 66/6
  - V-O flammability
- Color: opaque white
- Marking plates or factory imprinted application

|                        |
|------------------------|
| Pole Spacing           |
| Mounting Hole Diameter |
| Stripping Length       |
| Approvals              |
| Wire Range             |
| Voltage Rating         |
| Current Rating         |
| Torque                 |
| Other Approvals        |

| No. of Poles |
|--------------|
| 2            |
| 3            |
| 4            |
| 5            |
| 6            |
| 7            |
| 8            |
| 9            |
| 10           |
| 11           |
| 12           |



Flat base with wire protector

|           |
|-----------|
| 8 mm      |
| 3 mm      |
| 5 mm      |
|           |
| 24-12 AWG |
| 300 V     |
| 20 A      |
| 4.4 lb-in |
|           |


| Cat. No.  | Std. Pk. |
|-----------|----------|
| HE1WPR/02 | 100      |
| HE1WPR/03 | 100      |
| HE1WPR/04 | 100      |
| HE1WPR/05 | 100      |
| HE1WPR/06 | 50       |
| HE1WPR/07 | 50       |
| HE1WPR/08 | 50       |
| HE1WPR/09 | 50       |
| HE1WPR/10 | 50       |
| HE1WPR/11 | 50       |
| HE1WPR/12 | 50       |



Flat base with wire protector


|           |
|-----------|
| 10 mm     |
| 3.6 mm    |
| 6 mm      |
|           |
| 24-10 AWG |
| 300 V     |
| 30 A      |
| 7.0 lb-in |
|           |

| Cat. No.  | Std. Pk. |
|-----------|----------|
| HE4WPR/02 | 100      |
| HE4WPR/03 | 100      |
| HE4WPR/04 | 100      |
| HE4WPR/05 | 100      |
| HE4WPR/06 | 50       |
| HE4WPR/07 | 50       |
| HE4WPR/08 | 50       |
| HE4WPR/09 | 50       |
| HE4WPR/10 | 50       |
| HE4WPR/11 | 50       |
| HE4WPR/12 | 50       |




Dimensions mm

|          |                  |
|----------|------------------|
| A = 8.0  | H = Ø2.8         |
| B = M2.6 | I = 2.8          |
| C = 5.2  | J = 6.5          |
| D = 2.8  | K = 6.5          |
| E = Ø3   | L = 94 (12 pole) |
| F = Ø5   | M = 12.2         |
| G = 8.0  | N = 16.2         |



Dimensions mm

|          |                   |
|----------|-------------------|
| A = 10.0 | H = Ø3.6          |
| B = M3   | I = 3.2           |
| C = 6.4  | J = 8.5           |
| D = 3.5  | K = 7.9           |
| E = Ø3.6 | L = 117 (12 pole) |
| F = Ø5.7 | M = 14.9          |
| G = 10.0 | N = 20.0          |

**HE6**

*Flat base with wire protector*

12 mm

4.2 mm

7 mm



20-10 AWG


300 V

40 A

7.0 lb-in



| Cat. No.  | Std. Pk. |
|-----------|----------|
| HE6WPR/02 | 100      |
| HE6WPR/03 | 100      |
| HE6WPR/04 | 100      |
| HE6WPR/05 | 100      |
| HE6WPR/06 | 50       |
| HE6WPR/07 | 50       |
| HE6WPR/08 | 50       |
| HE6WPR/09 | 50       |
| HE6WPR/10 | 25       |
| HE6WPR/11 | 25       |
| HE6WPR/12 | 25       |

**HE10**

*Flat base with wire protector*

15 mm

4.3 / 5.7 mm

8.5 mm




18-8 AWG


300 V

50 A

10.6 lb-in



| Cat. No.   | Std. Pk. |
|------------|----------|
| HE10WPR/02 | 50       |
| HE10WPR/03 | 50       |
| HE10WPR/04 | 50       |
| HE10WPR/05 | 50       |
| HE10WPR/06 | 25       |
| HE10WPR/07 | 25       |
| HE10WPR/08 | 25       |
| HE10WPR/09 | 25       |
| HE10WPR/10 | 10       |
| HE10WPR/11 | 10       |
| HE10WPR/12 | 10       |

**HE16**

*Flat base with wire protector*

15 mm

4.3 / 5.7 mm

8.5 mm



18-6 AWG


300 V

63 A

17.7 lb-in




| Cat. No.   | Std. Pk. |
|------------|----------|
| HE16WPR/02 | 50       |
| HE16WPR/03 | 50       |
| HE16WPR/04 | 50       |
| HE16WPR/05 | 50       |
| HE16WPR/06 | 25       |
| HE16WPR/07 | 25       |
| HE16WPR/08 | 25       |
| HE16WPR/09 | 25       |
| HE16WPR/10 | 10       |
| HE16WPR/11 | 10       |
| HE16WPR/12 | 10       |




Dimensions mm

|          |                   |
|----------|-------------------|
| A = 12.0 | H = Ø4.1          |
| B = M3.5 | I = 4.0           |
| C = 7.7  | J = 9.5           |
| D = 4.3  | K = 8.9           |
| E = Ø4.2 | L = 140 (12 pole) |
| F = Ø6.3 | M = 16.8          |
| G = 12.0 | N = 22.6          |



Dimensions mm

|              |                   |
|--------------|-------------------|
| A = 15.0     | H = Ø5.0          |
| B = M4       | I = 4.8           |
| C = 9.3      | J = 11.3          |
| D = 5.7      | K = 11.6          |
| E = Ø4.3/5.7 | L = 175 (12 pole) |
| F = Ø8.2     | M = 21.9          |
| G = 15.0     | N = 25.1          |



Dimensions mm

|              |                   |
|--------------|-------------------|
| A = 15.0     | H = Ø5.6          |
| B = M5       | I = 4.8           |
| C = 9.3      | J = 11.3          |
| D = 5.7      | K = 11.6          |
| E = Ø4.3/5.7 | L = 175 (12 pole) |
| F = Ø8.2     | M = 21.9          |
| G = 15.0     | N = 25.1          |

## FEED-THROUGH STANDOFF FEET Panel Mount


For wire-to-wire connections in HVAC, appliance, equipment, power distribution and other industrial applications with restricted budget and space requirements.

Easy to use feed-through terminal strips are a cost-effective alternative to barrier strips or other types of terminal blocks. Simply strip the wire, insert, and tighten the screw. Eurostrips feature tubular screw clamps, with wire protectors, and recessed metal parts for finger protection. The stainless steel wire protectors exhibit excellent memory and the most effective connection.

Eurostrips described on this and the preceding page are available with standoff feet for increased wiring efficiency. They can be panel mounted or left to free float. Offered in easy-to-cut 12-pole strips, they can also be ordered precut with the required number of poles.


- Tubular screw clamp
- Panel mount or free float
- Housing material:
  - Polyamide 66/6
  - V-O flammability
- Color: opaque white
- Marking plates or factory imprinted

### HE1H



Standoff feet with wire protector


### HE4HN



Standoff feet with wire protector


|                        |                                                                                                                                                                     |                                                                                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Pole Spacing           | 8 mm                                                                                                                                                                | 10 mm                                                                                                                                                                   |
| Mounting Hole Diameter | 3 mm                                                                                                                                                                | 3.6 mm                                                                                                                                                                  |
| Stripping Length       | 5 mm                                                                                                                                                                | 6 mm                                                                                                                                                                    |
| Approvals              |                                                                                    |                                                                                      |
| Wire Range             | 24-12 AWG                                                                                                                                                           | 24-10 AWG                                                                                                                                                               |
| Voltage Rating         | 600 V                                                                                                                                                               | 600 V                                                                                                                                                                   |
| Current Rating         | 20 A                                                                                                                                                                | 30 A                                                                                                                                                                    |
| Torque                 | 4.4 lb-in                                                                                                                                                           | 7.0 lb-in                                                                                                                                                               |
| Other Approvals        |   |   |

| No. of Poles | Cat. No.   | Std. Pk. | Cat. No.    | Std. Pk. |
|--------------|------------|----------|-------------|----------|
| 2            | HE1HWPR/02 | 100      | HE4HNWPR/02 | 100      |
| 3            | HE1HWPR/03 | 100      | HE4HNWPR/03 | 100      |
| 4            | HE1HWPR/04 | 100      | HE4HNWPR/04 | 100      |
| 5            | HE1HWPR/05 | 100      | HE4HNWPR/05 | 100      |
| 6            | HE1HWPR/06 | 50       | HE4HNWPR/06 | 50       |
| 7            | HE1HWPR/07 | 50       | HE4HNWPR/07 | 50       |
| 8            | HE1HWPR/08 | 50       | HE4HNWPR/08 | 50       |
| 9            | HE1HWPR/09 | 50       | HE4HNWPR/09 | 50       |
| 10           | HE1HWPR/10 | 50       | HE4HNWPR/10 | 50       |
| 11           | HE1HWPR/11 | 50       | HE4HNWPR/11 | 50       |
| 12           | HE1HWPR/12 | 50       | HE4HNWPR/12 | 50       |



Dimensions mm


|          |                  |
|----------|------------------|
| A = 8.0  | I = 6.6          |
| B = M2.6 | J = 6.5          |
| C = 5.2  | K = 10.3         |
| D = 2.8  | L = 94 (12 pole) |
| E = Ø3   | M = 16           |
| F = Ø5   | N = 16.2         |
| G = 8.0  | O = 10.1         |
| H = Ø2.8 |                  |



Dimensions mm

|          |                   |
|----------|-------------------|
| A = 10.0 | I = 6.7           |
| B = M3   | J = 8.5           |
| C = 6.4  | K = 12.1          |
| D = 3.5  | L = 117 (12 pole) |
| E = Ø3.6 | M = 19.1          |
| F = Ø5.7 | N = 20            |
| G = 10.0 | O = 14.0          |
| H = Ø3.6 |                   |

HE6H



Standoff feet with wire protector

12 mm

4.2 mm

7 mm



20-10 AWG

600 V


40 A

7.0 lb-in



| Cat. No.   | Std. Pk. |
|------------|----------|
| HE6HWPR/02 | 100      |
| HE6HWPR/03 | 100      |
| HE6HWPR/04 | 100      |
| HE6HWPR/05 | 100      |
| HE6HWPR/06 | 50       |
| HE6HWPR/07 | 50       |
| HE6HWPR/08 | 50       |
| HE6HWPR/09 | 50       |
| HE6HWPR/10 | 25       |
| HE6HWPR/11 | 25       |
| HE6HWPR/12 | 25       |

HE10H



Standoff feet with wire protector

15 mm

4.3/5.7 mm

8.5 mm




18-8 AWG

600 V


50 A

10.6 lb-in



| Cat. No.    | Std. Pk. |
|-------------|----------|
| HE10HWPR/02 | 40       |
| HE10HWPR/03 | 40       |
| HE10HWPR/04 | 40       |
| HE10HWPR/05 | 40       |
| HE10HWPR/06 | 20       |
| HE10HWPR/07 | 20       |
| HE10HWPR/08 | 20       |
| HE10HWPR/09 | 10       |
| HE10HWPR/10 | 10       |
| HE10HWPR/11 | 10       |
| HE10HWPR/12 | 10       |

HE16H



Standoff feet with wire protector

15 mm

4.3/5.7 mm

8.5 mm



18-6 AWG


600 V

63 A

17.7 lb-in




| Cat. No.    | Std. Pk. |
|-------------|----------|
| HE16HWPR/02 | 40       |
| HE16HWPR/03 | 40       |
| HE16HWPR/04 | 40       |
| HE16HWPR/05 | 40       |
| HE16HWPR/06 | 20       |
| HE16HWPR/07 | 20       |
| HE16HWPR/08 | 20       |
| HE16HWPR/09 | 10       |
| HE16HWPR/10 | 10       |
| HE16HWPR/11 | 10       |
| HE16HWPR/12 | 10       |




Dimensions mm

|          |                   |
|----------|-------------------|
| A = 12.0 | I = 9             |
| B = M3.5 | J = 9.6           |
| C = 7.7  | K = 13.9          |
| D = 4.3  | L = 140 (12 pole) |
| E = Ø4.2 | M = 21.8          |
| F = Ø6.3 | N = 22.6          |
| G = 12.0 | O = 15            |
| H = Ø4.1 |                   |



Dimensions mm

|              |                   |
|--------------|-------------------|
| A = 15.0     | I = 10.7          |
| B = M4       | J = 11.3          |
| C = 9.3      | K = 17.5          |
| D = 5.7      | L = 175 (12 pole) |
| E = Ø4.3/5.7 | M = 27.8          |
| F = Ø8.2     | N = 25.1          |
| G = 15.0     | O = 16            |
| H = Ø5.0     |                   |



Dimensions mm

|              |                   |
|--------------|-------------------|
| A = 15.0     | I = 10.7          |
| B = M5       | J = 11.3          |
| C = 9.3      | K = 17.5          |
| D = 5.7      | L = 175 (12 pole) |
| E = Ø4.3/5.7 | M = 27.8          |
| F = Ø8.2     | N = 25.1          |
| G = 15.0     | O = 16            |
| H = Ø5.6     |                   |

## PLUGGABLE Panel Mount


For wire-to-wire connections in HVAC, appliance, equipment, power and other distribution applications. Pluggable Eurostrips® speed and simplify replacement of subassemblies, etc. They reduce downtime and misconnections.

Two-piece pluggable terminal strips feature tubular screw clamps, with recessed metal parts for finger protection. A spring loaded contact prevents inadvertent unplugging.


The headers and plugs are available with flat base or standoff feet and can be panel mounted or free float. Offered in easy-to cut 12-pole strips, they can also be orderd precut with the required number of poles.

- Tubular Screw Clamp
- Panel Mount or Free Float
- Housing material:
  - Polyamide 66/6
  - V-O flammability
- Color: Opaque White

### FLAT BASE





|                        |                                                                                                                                                                     |                                                                                                                                                                         |           |          |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|----------|
| Pole Spacing           | 10 mm                                                                                                                                                               | 10 mm                                                                                                                                                                   |           |          |
| Mounting Hole Diameter | 3.5 mm                                                                                                                                                              | 3.5 mm                                                                                                                                                                  |           |          |
| Stripping Length       | 3.6 mm                                                                                                                                                              | 3.6 mm                                                                                                                                                                  |           |          |
| Approvals              |  US<br>E211022                                                                     |  US<br>E211022                                                                       |           |          |
| Wire Range             | 24-10AWG                                                                                                                                                            | 24-10AWG                                                                                                                                                                |           |          |
| Voltage Rating         | 300V                                                                                                                                                                | 300V                                                                                                                                                                    |           |          |
| Current Rating         | 20A                                                                                                                                                                 | 20A                                                                                                                                                                     |           |          |
| Torque                 | 7.2 lb-in                                                                                                                                                           | 7.2 lb-in                                                                                                                                                               |           |          |
| Other Approvals        |   |   |           |          |
| No. of Poles           | Cat. No.                                                                                                                                                            | Std. Pk.                                                                                                                                                                | Cat. No.  | Std. Pk. |
| 2                      | HE42ST/02                                                                                                                                                           | 100                                                                                                                                                                     | HE42BU/02 | 100      |
| 3                      | HE42ST/03                                                                                                                                                           | 100                                                                                                                                                                     | HE42BU/03 | 100      |
| 4                      | HE42ST/04                                                                                                                                                           | 100                                                                                                                                                                     | HE42BU/04 | 100      |
| 5                      | HE42ST/05                                                                                                                                                           | 100                                                                                                                                                                     | HE42BU/05 | 100      |
| 6                      | HE42ST/06                                                                                                                                                           | 50                                                                                                                                                                      | HE42BU/06 | 50       |
| 7                      | HE42ST/07                                                                                                                                                           | 50                                                                                                                                                                      | HE42BU/07 | 50       |
| 8                      | HE42ST/08                                                                                                                                                           | 50                                                                                                                                                                      | HE42BU/08 | 50       |
| 9                      | HE42ST/09                                                                                                                                                           | 50                                                                                                                                                                      | HE42BU/09 | 50       |
| 10                     | HE42ST/10                                                                                                                                                           | 50                                                                                                                                                                      | HE42BU/10 | 50       |
| 11                     | HE42ST/11                                                                                                                                                           | 50                                                                                                                                                                      | HE42BU/11 | 50       |
| 12                     | HE42ST/12                                                                                                                                                           | 50                                                                                                                                                                      | HE42BU/12 | 50       |



#### Dimensions mm



|          |          |
|----------|----------|
| A = 10.0 | J = 15.2 |
| B = M3   | K = 7.9  |
| C = 6.4  | L = 117  |
| D = 3.6  | M = 14.9 |
| E = Ø3.5 | N = 34.4 |
| F = Ø5.7 | O = 9.2  |
| G = 10.0 | P = 20   |
| H = Ø3.5 | Q = 14.4 |
| I = 3.2  | R = 7    |




STANDOFF  
FEET

HE42SST

HE42SBU



|                        |                                                                                                                                                                     |                                                                                                                                                                         |            |          |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|----------|
| Pole Spacing           | 10 mm                                                                                                                                                               | 10 mm                                                                                                                                                                   |            |          |
| Mounting Hole Diameter | 3.5 mm                                                                                                                                                              | 3.5 mm                                                                                                                                                                  |            |          |
| Stripping Length       | 3.6 mm                                                                                                                                                              | 3.6 mm                                                                                                                                                                  |            |          |
| Approvals              |                                                                                   |                                                                                      |            |          |
| Wire Range             | 24-10AWG                                                                                                                                                            | 24-10AWG                                                                                                                                                                |            |          |
| Voltage Rating         | 600V                                                                                                                                                                | 600V                                                                                                                                                                    |            |          |
| Current Rating         | 20A                                                                                                                                                                 | 20A                                                                                                                                                                     |            |          |
| Torque                 | 7.2 lb-in                                                                                                                                                           | 7.2 lb-in                                                                                                                                                               |            |          |
| Other Approvals        |   |   |            |          |
| No. of Poles           | Cat. No.                                                                                                                                                            | Std. Pk.                                                                                                                                                                | Cat. No.   | Std. Pk. |
| 2                      | HE42SST/02                                                                                                                                                          | 100                                                                                                                                                                     | HE42SBU/02 | 100      |
| 3                      | HE42SST/03                                                                                                                                                          | 100                                                                                                                                                                     | HE42SBU/03 | 100      |
| 4                      | HE42SST/04                                                                                                                                                          | 100                                                                                                                                                                     | HE42SBU/04 | 100      |
| 5                      | HE42SST/05                                                                                                                                                          | 100                                                                                                                                                                     | HE42SBU/05 | 100      |
| 6                      | HE42SST/06                                                                                                                                                          | 50                                                                                                                                                                      | HE42SBU/06 | 50       |
| 7                      | HE42SST/07                                                                                                                                                          | 50                                                                                                                                                                      | HE42SBU/07 | 50       |
| 8                      | HE42SST/08                                                                                                                                                          | 50                                                                                                                                                                      | HE42SBU/08 | 50       |
| 9                      | HE42SST/09                                                                                                                                                          | 50                                                                                                                                                                      | HE42SBU/09 | 50       |
| 10                     | HE42SST/10                                                                                                                                                          | 50                                                                                                                                                                      | HE42SBU/10 | 50       |
| 11                     | HE42SST/11                                                                                                                                                          | 50                                                                                                                                                                      | HE42SBU/11 | 50       |
| 12                     | HE42SST/12                                                                                                                                                          | 50                                                                                                                                                                      | HE42SBU/12 | 50       |



Dimensions mm

|          |          |
|----------|----------|
| A = 10.0 | J = 15.2 |
| B = M3   | K = 11.5 |
| C = 6.4  | L = 117  |
| D = 3.6  | M = 18.5 |
| E = Ø3.5 | N = 34.4 |
| F = Ø5.7 | O = 9.2  |
| G = 10.0 | P = 20   |
| H = Ø3.5 | Q = 14.4 |
| I = 6.8  | R = 7    |

