


ZMA Series

Subminiature Snap-acting Switches



Features/Benefits

- **Reliable snap-acting mechanism**
- **Long electrical and mechanical life**
- **Compact size—Ideal when space is limited**
- **Various PCB terminals and actuators**
- **RoHS compatible & compliant**

Typical Applications

- **PCB detection switch**
- **Communication devices**
- **Testing equipment**
- **Security/Alarm systems**
- **Consumer electronics**

UL61058-1



Specifications

CONTACT RATING: 3A @ 125 / 250 V AC 24 V DC
1 A @125 / 250 V AC 24 V DC
0.1A @ 125 / 250 V AC 24 V DC
ELECTRICAL LIFE: 300,000 cycles @ 0.1A / 10,000 cycles @ 3A.
MECHANICAL LIFE: 1,000,000 cycles.
INSULATION RESISTANCE: 100 M ohm min.
DIELECTRIC STRENGTH: 500 Vrms.
OPERATING TEMPERATURE: -40°C to 85°C
OPERATING FORCE: 80 or 150 grams.

* Low Level=conditions where no arcing occurs during switching, i.e., 0.4 VA max.
@ 20 V AC or DC max.


Materials

CASE/COVER: PBT
ACTUATOR: Button nylon 6/6
MOVABLE CONTACTS: Silver alloy or gold plated
STATIONARY CONTACTS: Silver alloy or gold plated
TERMINALS: Brass, silver plated.

NOTE: Specifications and materials listed above are for switches with standard options.
For information on specific and custom switches, consult Customer Service Center.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages J-37 and J-38. For additional options not shown in catalog, consult Customer Service Center.



Silver Contacts

Option Code	UL 1054	UL 61058-1	E4	E15
00A	0.1A 60 V DC 0.1A 125 / 250 V AC			
03A	3 A 125 / 250 V AC	3 A 125 / 250 V AC 3 A 24 V DC	0.1A 3A 125/250 V AC	
01A		1 A 24 V DC 1 A 125 / 250 V AC		1 A 24 V DC 1 A 125 / 250 V AC

Gold Plated Contacts

Option Code	UL 1054	UL 61058-1	E4	E15
G00	0.1A 60 V DC 0.1A 125 / 250 V AC			
G03	3 A 125 / 250 V AC	3 A 125 / 250 V AC 3 A 24 V DC	0.1A 3A 125/250 V AC	
G01		1 A 24 V DC 1 A 125 / 250 V AC		1 A 24 V DC 1 A 125 / 250 V AC



Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change

SERIES **Z** **M**

Technical drawing of the 1-64 mounting screw, showing side and front views with dimensions in inches and millimeters.

Side View Dimensions:

- Top flange width: .114 (2,9)
- Thread length: .024 (0,6)
- Total length: .228 (5,8)

Front View Dimensions:

- UL/CSA LOGO MARK
- MODEL NO./RATING MARK & DATE CODE
- Top flange width: .205 (5,2)
- Top flange thickness: 0.044 (1,12)
- Thread length: .081 (2,05)
- Total length: .260 (6,6)
- OPER. POS. (Operating Position)
- FREE POS. (Free Position)
- Thread diameter: $\phi .087$ (2,2 ϕ)
- Thread length: .256 (6,5)
- Thread diameter: $\phi .079$ ($\phi 2,05$)
- Thread length: .035 TYP. (0,9)
- Thread diameter: .138 (3,5)
- Thread length: .200 (5,08)
- Thread diameter: .200 (5,08)
- Thread length: .504 (12,8)

PC MOUNTING:

- 3X $\phi .048$ (1,22)
- Thread diameter: .200 (5,08)
- Thread length: .200 (5,08)

Mounting Screws Size 1-64

ELECTRICAL RATING

Snap-acting


Gold Plated Contacts

Option Code	UL cUL _{us} 1054	UL cUL _{us} 61058-1			Option Code	UL cUL _{us} 1054	UL cUL _{us} 61058-1		
00A	0.1A 60 V DC 0.1A 125 / 250 V AC				G00	0.1A 60 V DC 0.1A 125 / 250 V AC			
03A	3 A 125 / 250 V AC	3 A 125 / 250 V AC 3 A 24 V DC	0.1A 3A 125/250 V AC		G03	3 A 125 / 250 V AC	3 A 125 / 250 V AC 3 A 24 V DC	0.1A 3A 125/250 V AC	
01A		1 A 24 V DC 1 A 125 / 250 V AC		1 A 24 V DC 1 A 125 / 250 V AC	G01		1 A 24 V DC 1 A 125 / 250 V AC		1 A 24 V DC 1 A 125 / 250 V AC

Consult Customer Service center for availability and delivery of nonstandard ratings.

OPERATING FORCE

OPTION CODE	BASIC SWITCH OPERATING FORCE (OZ./GRAMS)
150	5.29 150
080	2.82 80




ZMA Series


Subminiature Snap-acting Switches

ACTUATOR 


P00 PIN PLUNGER




L08 LEVER
3.95MM




S03 SIMULATED ROLLER
5.8MM




A03 ROLLER
1.3MM




L30 LEVER
20.5MM




L04 LEVER
3.49MM





L11 LEVER
7.2MM



S06 SIMULATED ROLLER
2.03MM



S07 SIMULATED ROLLER
0.75MM



Third Angle
Projection

Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change

www.ck-components.com




Snap-acting

ZMA Series Subminiature Snap-acting Switches


SWITCH CHARACTERISTICS

CODE	OPER. FORCE MAX. (GRAMS)		REL. FORCE MIN. (GRAMS)		'A' FP MAX. (MM)	'B' OP MAX. (MM)	'C' PT MAX. (MM)	'D' OT MIN. (MM)	'E' MIN. (MM)
P00	80	150	21	35	7.35	6.9 ±0.2	0.62	0.2	
S03	25	43	5	7	14.2	9.8 ±0.9	3.5	0.7	5.4
L30 (80gf)	13	21	2	3	16.8	9.5 ±1.9	6.9	0.55	20.15
L30 (150 gf)	13	21	2	3	16.8	9.25 ±1.9	6.9	0.55	20.15
L11	25	39	4	6	11.7	8.68 ±1	4.4	0.6	7.33
L08	27	48	3	8	13.5	10.75 ±0.8	3.5	0.3	3.82
A03	34	65	6	10	16.55	13.65 ±1	3.9	0.5	0.56
L04	30	50	5	8	10.1	7.9 ±0.8	3.0	0.6	3.49
S06	33	49	5	11	12.43	10.7 ±0.8	1.43	1.25	1.97
S07	40	65	2	5	13.0	9.7 ±1	4.3	0.5	0.49




TERMINATIONS


P PC THRU-HOLE




L LEFT FOOTED, PC THRU-HOLE




R RIGHT FOOTED, PC THRU-HOLE



E SOLDER



K PC THRU-HOLE WITH RETENTION FEATURE



Dimensions are shown: Inches (mm)
Specifications and dimensions subject to change



Snap-acting