







参考基板レイアウト (マウント面)

P.C.BOARD PATTERN DIMENSION(REF.)
(MOUNT AREA)

適合FPC推奨寸法

APPLICABLE FPC
RECOMMENDED DIMENSION

(仕上がり厚さ: 0.3±0.03)
(THICKNESS: 0.3±0.03)

N: 極数
N: CIRCUITS

適合FPC推奨寸法

APPLICABLE FPC
RECOMMENDED DIMENSION

(仕上がり厚さ: 0.3±0.03)
(THICKNESS: 0.3±0.03)

N: 極数
N: CIRCUITS

FPCについて:

打抜き方向は導体側から補強板側を推奨致します。

補強フィルム材質はポリイミドを推奨致します。

接着剤は熱硬化接着剤を推奨致します。

ABOUT FPC:

RECOMMENDED


PUNCHER DIRECTION : FROM CONDUCTOR SIDE TO STIFFENER BOARD SIDE.

RECOMMENDED MATERIAL:

STIFFENER FILM : POLYIMIDE


BONDING AGENT : THERMOSETTING BONDING AGENT

REVISED	EC NO.: J2005-0620 DRAWN: HSH MOYA CHKD: HIRATA APPR: HIRATA	2004/09/01 2004/09/01 2004/09/06	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				10 UNDER	±0.2	DRAWN BY M. NABEI	DATE 2004/02/18	TITLE 0.5 FPC CONN. HS'G ASS'Y EASY ON / STRAGIHT -LEAD FREE-			
				10 OVER 30 UNDER	±0.25	CHECKED BY M. SASAO	DATE 2004/02/18				
				30 OVER	±0.3	APPROVED BY M. SASAO	DATE 2004/02/18	MOLEX INCORPORATED			
				ANGULAR ±1 °		MATERIAL NO.					DOCUMENT NO.
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-51374-020			
REV				SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							




注) NOTES

- 製品番号 51374-**-39 詳細寸法については、製品単体図面を参照下さい。
IN THE PACKAGE PART NUMBER 51374-**-39 DETAILED DIMENSIONS, SEE SALES DRAWING FOR CONNECTOR.
- 梱包数量：2000個/リール
NUMBER OF CONNECTORS:2000 PCS/REEL.
- リードテープ長さ
LEAD TAPE LENGTH



- トップテープの剥離強度：(剥離方向は下図参照)
PEELING OFF FORCE OF TOP TAPE (PELLING DIRECTION AS SHOWN IN FOLLOWING FIGURE.)
0.1~1.3N {10~130gf}

尚、本規格値は、出荷時に適用。
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
(但し、輸送時に剥離が発生しない事。)
(PEEL OFF SHOULD NOT BE ALLOWED,DURING TRANSPORTATION.)




- 材料
MATERIAL
キャリアテープ：ポリプロピレン (PP)
CARRIER TAPE:POLYPROPYLENE(PP)
トップテープ：PET, PE, PEF
TOP TAPE:PET,PE,PEF
リール：ポリスチレン
REEL : POLYSTYRENE

- 本製品は51374-**-93/-**-90の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 51374-**-93/-**-90.

REVISED	EC NO: J2005-0620 DRAWN: HSHIMOTA CHK: HHIIRATA APP: HHIIRATA	2004/09/01 2004/09/06 2004/09/06	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				10 UNDER	±0.2	DRAWN BY M. NABEI	DATE 2004/02/18	TITLE 51374-**39 TAPING PACKAGE -LEAD FREE-			
				10 OVER 30 UNDER	±0.25	CHECKED BY M. SASAO	DATE 2004/02/18				
				30 OVER	±0.3	APPROVED BY M. SASAO	DATE 2004/02/18	MOLEX INCORPORATED			
				ANGULAR	±1 °	MATERIAL NO.					DOCUMENT NO.
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-51374-021			1 OF 2

	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
---	--	--	--



61.4	57.4	56±0.3	52.4	34.1	26.2	33.1	51374-6073	60
49.4	45.4	44±0.3	40.4	29.1	20.2	28.1	51374-5073	50
				26.6		25.6	51374-4573	45
				24.1		23.1	51374-4073	40
				20.6		19.6	51374-3373	33
37.4	33.4	32±0.3	28.4	19.1	14.2	18.1	51374-3073	30
				17.1		16.1	51374-2673	26
				16.1		15.1	51374-2473	24
				14.1		13.1	51374-2073	20
29.4	25.4	24±0.3	—	11.6	11.5	10.6	51374-1573	15
				10.6		9.6	51374-1373	13
				9.1		8.1	51374-1073	10
G	F	E キャリアテープ幅 CARRIER TAPE WIDTH	D	(C)	(B)	(A)	製品番号 MATERIAL NO.	極数 CIRCUITS

REVISED EC NO: J2005-0620 DRAWN: SHIMOYA CHKD: HIRATA APPR: HIRATA REV B	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				DRAWN BY DATE M. NABEI 2004/02/18		TITLE 51374-**39 TAPING PACKAGE -LEAD FREE-			
				CHECKED BY DATE M. SASAO 2004/02/18					
		10 UNDER 30 UNDER ±0.25		APPROVED BY DATE M. SASAO 2004/02/18		 MOLEX INCORPORATED			
		30 OVER ±0.3							
		ANGULAR ±1 °		MATERIAL NO.					DOCUMENT NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		SEE TABLE SD-51374-021			2 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									