





REV.	DATE	DESCRIPTION
A	01/30/04	UPDATE DRAWING FORMAT
B	05/22/05	MODIFY PLATING SPEC
C	07/08/07	REVISE STRIPPING DIMS AND FERRULE



RECOMMENDED
CABLE STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .429"
 2. CRIMPED CONTACT PIN HEX CRIMP SIZE .100"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex									
8						DRAWN	G.R.S.						07/08/07				
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	CHECKED							PART DESCRIPTION N CRIMP PLUG (FOR RG-214/U CABLE)				
6						ISSUED											
5	FERRULE	COPPER	NECOTE	1				PART NO. 172166									
4	CONTACT PIN	BRASS	GOLD	1		SHEET	1 OF 1										
3	INSULATOR	TEFLON	NATURAL	1				DWG. NO. 172166.DWG									
2	BARREL	BRASS	NEXCOTE	1													
1	BODY	BRASS	NEXCOTE	1				REV. C									
	DESCRIPTION	MATERIAL	FINISH	QTY													
					DO NOT SCALE DRAWING	C:/172/172166.DWG		SCALE NA									
								SIZE A									