





P/N: *-2834011-*

COLOR CODE:

--	--	--


PIN No:

SERIES CODE

2=2 POSN

	SERIES	CODE
1=GREEN	2=2	POSN
2=BLUE	3=3	POSN
3=BROWN	4=4	POSN
4=ORANGE	5=5	POSN
5=GREY	6=6	POSN
6=RED	7=7	POSN
7=YELLOW	8=8	POSN
8=PURPLE		
9=WHITE		
0=BLACK		

REMARK: THE DIFFERENT COLORS COULD BE COMBINED TO THE NEW CONNECTOR P/Ns FOR CUSTOMER REQUEST.



RECOMMEND PCB Layout

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APV/
		A	FIRST VERSION	08/02/04	GF	SM	
		B	ADD PART No.	27/04/2005	GF	SM	

REVISIONS

DESCRIPTION		DATE	DWN	APV/V
A	FIRST VERSION	01DEC2014	GF	SM
B	ADD PART No.	27MAR2015	GF	SM

NOTES :

⚠ MATERIALS AND FINISH:

2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
 - CONTACTS: COPPER ALLOY, FINISH: TIN OVER NICKEL UNDERPLATE
3. WIRE TYPES AND SIZES ACCEPTED
WIRE RANGE: 14AWG~20AWG(SOLID&STRANDED)
STRIP LENGTH: 7.5mm~8.5mm
4. PACKAGED IN TRAY.
5. CURRENT RATING: 6Amp AC300V.
6. OPERATION TEMPERATURE: -40°C TO +105°C

P/N: *-2834011-*

④	CONTACT
③	LEVER(orange)
②	COVER
①	HOUSING
29.5	8 POSN
26	7 POSN
22.5	6 POSN
19	5 POSN
15.5	4 POSN
12	3 POSN
8.5	2 POSN
A	NO. OF POSITIONS

NO. OF POSITIONS

[illegible]