

2589-ID-10

NOTES:

- 1. THESE MOUNTING CLIPS ARE FOR HOLDING THE 2481 SERIES HOUSINGS TO THE MAIN PANEL TOPS OF ELECTRIC RANGES.
- 2. SCREW SIZE INDICATION.
- 3. .015/(.38) MAXIMUM CUT OFF.
- 4. .010/(.25) MAXIMUM MISMATCH.
- 5. THREAD FORM FOR A #10-32 SCREW.
- 6. THIS SURFACE MAY BE FORMED IN THIS DIRECTION A MAXIMUM OF 5°.

MATERIAL:

STEEL, STAINLESS, TYPE 301, .020/(.5) THICK.

AC	OBSOLETE P/N
AB2	REMOVED NOTCH
AB1	REV. RADII
AB	REVISED
AA	REVISED
Z	REVISED
Y	REVISED
X	REDRAWN & REDIM.
I	AC
2	Z
3	AB

REVISIONS


REVISE ONLY ON CAD SYSTEM

DIMENSIONS SHOWN (METRIC) INCH		UNLESS OTHERWISE SPECIFIED TOLERANCES ANGULAR ± .006 5°	
INCH		METRIC	
5 PLACE	± .010	---	
2 PLACE	± .014	± 0.25	
1 PLACE	---	± 0.35	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			
DRW'G. BY	RHR	CHK'D. BY	ESS
APP'D. BY	RAS	SCALE	2: 1
FILE NAME		SD2589X1	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DIV. CP	
PART NO.		DRWG. NO.	
SEE SHEET 3		SD-2589-*	
SHEET NO.		DATE	
1 of 3		11/20/92	
MOLEX INCORPORATED		U.S.A.	
135E,ILL.		60532	

NO P.S.



13	12	11	10	9	8	7	6	2589	4	3	2	1
----	----	----	----	---	---	---	---	------	---	---	---	---

	PART NO.	ENG. NO.	DIMENSION	
			A	
J	089-00-2006	2589-ID-10	.48±.025 (12.2±.64)	
	089-00-2022	2589-2C	.53±.025 (13.5±.64)	
	089-00-2025	2589-2H	.656±.025 (16.66±.64)	
	089-00-2027	2589-2J-10	.562±.025 (14.27±.64)	
I	089-00-2041	2589-3B	.48±.025 (12.2±.64)	
	089-00-2047	2589-6F	.375±.015 (9.53±.38)	
	089-00-2100	2589-10C	.48±.025 (12.2±.64)	
	089-00-2101	2589-21A	.62±.025 (15.7±.64)	OBSOLETE
H	089-00-2103	2589-23	.62±.025 (15.7±.64)	




FOR THE REMAINDER
OF DIMENSIONS AND
DETAILS SEE SHEET I

2589-23



FOR THE REMAINDER
OF DIMENSIONS AND
DETAILS SEE SHEET I

2589-21A OBSOLETE



		AA	SEE SHEET I	DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 5°		▽ = 0 ▼ = 0		REVISE ONLY ON CAD SYSTEM													
		Z	SEE SHEET I	<table><tr><th></th><th>INCH</th><th>METRIC</th></tr><tr><td>3 PLACE</td><td>± .010</td><td>---</td></tr><tr><td>2 PLACE</td><td>± .014</td><td>± 0.25</td></tr><tr><td>1 PLACE</td><td>---</td><td>± 0.35</td></tr></table>			INCH	METRIC	3 PLACE	± .010	---	2 PLACE	± .014	± 0.25	1 PLACE	---	± 0.35	TITLE MOUNTING CLIP			
	INCH	METRIC																			
3 PLACE	± .010	---																			
2 PLACE	± .014	± 0.25																			
1 PLACE	---	± 0.35																			
AB		SEE SHEET I	X	SEE SHEET I	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		<table><tr><td rowspan="2">MOLEX INCORPORATED L15LEJLL 60532 U.S.A.</td><td>SHEET NO.</td><td>DATE</td></tr><tr><td>3</td><td>2/24/93</td></tr></table>			MOLEX INCORPORATED L15LEJLL 60532 U.S.A.	SHEET NO.	DATE	3	2/24/93							
MOLEX INCORPORATED L15LEJLL 60532 U.S.A.	SHEET NO.	DATE																			
	3	2/24/93																			
				DRWG. BY: RHR APP'D. BY: RAS	CHK'D. BY: ESS SCALE: 2:1	PART NO. SEE CHART		DRWG. NO. SD-2589-•													
LTR.	REVISIONS	LTR.	REVISIONS	FILE NAME SD589X3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				DIV. CP	SIZE C										