






REV.	DATE	DESCRIPTION
NC	02/04/03	UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	G.R.S.	02/04/03											
7	HEAT SHRINK TUBING					CHECKED													
6	FERRULE	COPPER	GOLD	1			ISSUED				PART DESCRIPTION								
5	CONTACT PIN	BRASS	GOLD	1			SHEET	1 OF 1			SMA CRIMP PLUG (RG–174/U, 188A/U, 316/U)								
4	GASKET	SILICONE	RED	1							PART NO.								
3	RETAINER RING	BER. COPPER	NATURAL	1							132114								
2	INSULATOR	TEFLON	NATURAL	1		CAD FILE		C:/132/132114.DWG		DWG. NO.		132114.DWG		REV.	NC	SIZE	A	SCALE	NA
1	SHELL/BODY	BRASS	GOLD	1															
	DESCRIPTION	MATERIAL	FINISH	QTY															